

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562443

Luminaire Tested: **SQ4-PW1-125U-125D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562443
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-125U-125D-92765-1D-UNV-STD-W-4 (4000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10634.5 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 97.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562443
CATALOG NUMBER: SQ4-PW1-125U-125D-92765-1D-UNV-STD-W-4 (4000K)

Luminous Intensity Polar Plot





TEST NUMBER: P562443

CATALOG NUMBER: SQ4-PW1-125U-125D-92765-1D-UNV-STD-W-4 (4000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	97	93	89	86	89	86	82	79	72	70	67	59	58	56	48	47	46	40
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	39	34
3	81	72	64	58	74	66	60	55	56	51	47	46	43	40	37	35	33	29
4	74	63	55	49	68	59	52	46	50	44	40	41	37	34	33	31	28	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	25	22	19	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	13
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18284	18284	18284
5°	18402	18257	18177
10°	18256	18108	18010
15°	18062	17863	17796
20°	17847	17572	17537
25°	17597	17277	17225
30°	17226	16965	16853
35°	16736	16500	16401
40°	16214	15962	15898
45°	15583	15378	15310
50°	14938	14811	14711
55°	14240	14240	14015
60°	13371	13629	13145
65°	12236	12845	11931
70°	10788	11823	10504
75°	9211	10580	8962
80°	7141	8905	7237
85°	4626	6838	6097



TEST NUMBER: P562443

CATALOG NUMBER: SQ4-PW1-125U-125D-92765-1D-UNV-STD-W-4 (4000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.6	1.8
10°-20°	526.9	5.0
20°-30°	781.5	7.3
30°-40°	914.5	8.6
40°-50°	910.4	8.6
50°-60°	786.2	7.4
60°-70°	565.9	5.3
70°-80°	296.7	2.8
80°-90°	73.6	0.7
90°-100°	410.2	3.9
100°-110°	1167.3	11.0
110°-120°	1118.4	10.5
120°-130°	885.2	8.3
130°-140°	710.5	6.7
140°-150°	556.2	5.2
150°-160°	407.0	3.8
160°-170°	252.1	2.4
170°-180°	85.5	0.8
0°-30°	1495.0	14.1
0°-40°	2409.5	22.7
0°-60°	4106.0	38.6
0°-90°	5042.2	47.4
90°-120°	2695.9	25.4
90°-150°	4847.7	45.6
90°-180°	5592.0	52.6
0°-180°	10634.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1982	1982	1982	1982	1982	
5°	1987	1965	1971	1966	1963	188
15°	1891	1867	1870	1866	1863	533
25°	1729	1700	1697	1687	1692	795
35°	1486	1465	1465	1451	1456	929
45°	1194	1184	1179	1175	1173	921
55°	885	884	885	873	871	790
65°	560	578	588	565	546	555
75°	258	282	297	277	251	277
85°	44	57	65	61	58	58
90°	0	0	0	0	0	3
95°	44	177	794	275	169	51
105°	181	275	1190	2101	1997	192
115°	337	408	902	1911	2244	332
125°	476	528	861	1429	1708	426
135°	582	630	851	1207	1364	449
145°	686	722	858	1044	1138	429
155°	784	802	878	944	982	362
165°	866	869	888	907	921	244
175°	907	902	899	893	887	86
180°	900	900	900	900	900	

TEST NUMBER: P562443

CATALOG NUMBER: SQ4-PW1-125U-125D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1981.8	1981.8	1981.8	1981.8	1981.8
2.5°	1993.0	1976.6	1981.8	1977.4	1967.8
5°	1987.0	1964.8	1971.3	1966.0	1962.6
7.5°	1966.8	1946.3	1951.1	1945.4	1943.4
10°	1948.6	1928.1	1932.9	1925.8	1922.4
12.5°	1927.7	1905.8	1910.6	1903.5	1901.5
15°	1891.0	1867.1	1870.1	1866.5	1863.1
17.5°	1848.4	1824.2	1824.7	1819.0	1818.4
20°	1817.7	1792.1	1789.7	1782.8	1786.2
22.5°	1784.1	1757.2	1754.8	1745.1	1749.9
25°	1728.6	1699.6	1697.2	1686.8	1692.0
27.5°	1664.4	1635.7	1635.7	1621.2	1626.6
30°	1616.9	1589.6	1592.4	1575.1	1581.9
32.5°	1566.6	1542.0	1543.5	1526.2	1533.1
35°	1485.9	1465.4	1465.0	1451.1	1456.2
37.5°	1403.5	1385.4	1382.5	1374.5	1375.9
40°	1346.2	1330.9	1325.3	1320.0	1320.0
42.5°	1286.2	1272.2	1266.6	1262.7	1261.4
45°	1194.3	1184.1	1178.6	1175.1	1173.4
47.5°	1103.5	1094.0	1089.2	1086.7	1085.0
50°	1040.7	1033.8	1031.9	1026.7	1024.9
52.5°	977.8	973.7	971.9	965.2	963.5
55°	885.3	883.6	885.3	873.0	871.3
57.5°	788.9	791.6	797.3	780.8	776.7
60°	724.6	731.5	738.6	719.2	712.4
62.5°	659.0	669.9	679.9	657.7	648.1
65°	560.5	577.6	588.4	565.3	546.5
67.5°	465.5	486.7	499.7	474.8	453.6
70°	399.9	423.8	438.3	413.3	389.4
72.5°	342.6	369.2	381.0	357.4	333.5
75°	258.4	282.3	296.8	277.0	251.4
77.5°	183.3	205.9	217.9	200.7	179.5
80°	134.4	158.3	167.6	153.3	136.2
82.5°	95.3	115.1	121.5	112.9	101.3
85°	43.7	57.3	64.6	61.0	57.6
87.5°	11.2	20.7	26.5	26.6	27.9
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.7	72.6	168.4	49.0	37.0
95°	44.5	176.7	794.2	274.9	169.4
97.5°	81.8	207.0	1223.1	875.2	599.7
100°	107.8	225.0	1316.2	1333.2	1026.9
102.5°	136.6	244.4	1295.7	1706.5	1439.1
105°	181.4	275.1	1189.5	2101.2	1997.4
107.5°	227.0	311.0	1065.6	2212.4	2304.8
110°	258.4	337.1	994.4	2169.9	2377.4

TEST NUMBER: P562443

CATALOG NUMBER: SQ4-PW1-125U-125D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	288.6	363.2	946.5	2069.2	2365.0
115°	337.2	407.5	902.0	1910.8	2243.9
117.5°	380.0	445.9	875.6	1737.7	2090.5
120°	414.2	469.4	872.9	1638.8	1976.9
122.5°	441.6	496.8	866.1	1552.0	1866.0
125°	475.8	527.7	860.9	1428.7	1708.1
127.5°	513.1	561.7	858.2	1355.0	1585.3
130°	532.3	580.8	854.1	1303.6	1504.5
132.5°	552.8	600.0	854.1	1263.6	1448.3
135°	581.9	630.5	850.7	1206.8	1364.1
137.5°	609.3	656.5	850.3	1158.7	1294.6
140°	629.9	678.4	848.9	1118.9	1249.4
142.5°	653.1	693.6	853.0	1087.1	1204.3
145°	686.3	721.5	857.5	1044.5	1138.2
147.5°	714.8	748.9	865.0	1001.4	1082.4
150°	739.4	762.8	867.8	987.2	1044.1
152.5°	758.6	783.3	870.5	967.9	1020.8
155°	783.9	802.3	878.0	943.9	982.4
157.5°	815.4	826.4	879.7	933.1	960.5
160°	831.8	840.2	886.6	924.8	948.2
162.5°	841.4	851.1	888.0	917.8	935.9
165°	866.1	869.4	888.3	907.4	920.8
167.5°	882.8	879.8	896.2	904.9	910.2
170°	888.3	886.6	893.4	895.3	902.0
172.5°	900.6	894.9	897.5	892.5	897.9
175°	907.1	902.1	898.6	893.3	886.6
177.5°	909.9	901.8	897.5	892.1	893.4
180°	900.3	900.3	900.3	900.3	900.3

(END OF REPORT)