

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562471

Luminaire Tested: **SQ4-PW1-150U-075D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562471  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-150U-075D-92765-1D-UNV-STD-W-4 (5000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10036.6 lumens  
Efficiency: N/A  
Efficacy: 121.1 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562471  
CATALOG NUMBER: SQ4-PW1-150U-075D-92765-1D-UNV-STD-W-4 (5000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562471

CATALOG NUMBER: SQ4-PW1-150U-075D-92765-1D-UNV-STD-W-4 (5000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	89	86	82	84	81	77	75	64	62	60	48	47	46	34	33	33	26
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28	22
3	78	69	62	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	33	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10
9	48	36	29	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11286	11286	11286
5°	11360	11270	11220
10°	11269	11179	11118
15°	11150	11026	10984
20°	11016	10847	10826
25°	10863	10666	10632
30°	10633	10472	10403
35°	10331	10185	10124
40°	10009	9853	9813
45°	9619	9492	9451
50°	9221	9143	9081
55°	8791	8791	8651
60°	8254	8412	8115
65°	7554	7929	7366
70°	6658	7297	6485
75°	5686	6531	5532
80°	4410	5499	4468
85°	2848	4224	3769



TEST NUMBER: P562471

CATALOG NUMBER: SQ4-PW1-150U-075D-92765-1D-UNV-STD-W-4 (5000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	115.2	1.1
10°-20°	325.2	3.2
20°-30°	482.4	4.8
30°-40°	564.5	5.6
40°-50°	562.0	5.6
50°-60°	485.3	4.8
60°-70°	349.3	3.5
70°-80°	183.2	1.8
80°-90°	45.4	0.5
90°-100°	507.9	5.1
100°-110°	1445.2	14.4
110°-120°	1384.7	13.8
120°-130°	1095.9	10.9
130°-140°	879.7	8.8
140°-150°	688.7	6.9
150°-160°	503.9	5.0
160°-170°	312.1	3.1
170°-180°	105.9	1.1
0°-30°	922.9	9.2
0°-40°	1487.3	14.8
0°-60°	2534.6	25.3
0°-90°	3112.5	31.0
90°-120°	3337.9	33.3
90°-150°	6002.1	59.8
90°-180°	6924.0	69.0
0°-180°	10036.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1223	1223	1223	1223	1223	
5°	1227	1213	1217	1214	1212	116
15°	1167	1152	1154	1152	1150	329
25°	1067	1049	1048	1041	1044	491
35°	917	905	904	896	899	573
45°	737	731	728	725	724	569
55°	546	545	546	539	538	488
65°	346	356	363	349	337	343
75°	160	174	183	171	155	171
85°	27	35	40	38	36	36
90°	0	0	0	0	0	3
95°	55	219	983	340	210	63
105°	225	341	1473	2602	2473	238
115°	418	504	1117	2366	2778	411
125°	589	653	1066	1769	2115	527
135°	720	781	1053	1494	1689	556
145°	850	893	1062	1293	1409	531
155°	971	993	1087	1169	1216	449
165°	1072	1076	1100	1124	1140	302
175°	1123	1117	1113	1106	1098	106
180°	1115	1115	1115	1115	1115	

TEST NUMBER: P562471

CATALOG NUMBER: SQ4-PW1-150U-075D-92765-1D-UNV-STD-W-4 (5000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1223.3	1223.3	1223.3	1223.3	1223.3
2.5°	1230.2	1220.1	1223.3	1220.6	1214.7
5°	1226.6	1212.9	1216.9	1213.6	1211.5
7.5°	1214.1	1201.4	1204.4	1200.9	1199.6
10°	1202.9	1190.2	1193.2	1188.8	1186.7
12.5°	1189.9	1176.4	1179.4	1175.0	1173.8
15°	1167.3	1152.5	1154.4	1152.2	1150.0
17.5°	1141.0	1126.0	1126.3	1122.9	1122.5
20°	1122.0	1106.2	1104.8	1100.5	1102.6
22.5°	1101.3	1084.7	1083.2	1077.3	1080.2
25°	1067.1	1049.1	1047.7	1041.3	1044.4
27.5°	1027.4	1009.7	1009.7	1000.7	1004.1
30°	998.1	981.2	983.0	972.3	976.5
32.5°	967.0	951.9	952.8	942.1	946.3
35°	917.2	904.6	904.3	895.7	898.9
37.5°	866.4	855.2	853.4	848.5	849.3
40°	831.0	821.5	818.1	814.8	814.8
42.5°	793.9	785.3	781.9	779.5	778.6
45°	737.2	730.9	727.5	725.4	724.3
47.5°	681.2	675.3	672.4	670.8	669.8
50°	642.4	638.2	637.0	633.7	632.7
52.5°	603.6	601.1	599.9	595.8	594.7
55°	546.5	545.4	546.5	538.9	537.8
57.5°	487.0	488.6	492.1	481.9	479.4
60°	447.3	451.5	455.9	444.0	439.8
62.5°	406.8	413.5	419.7	406.0	400.1
65°	346.0	356.5	363.2	349.0	337.4
67.5°	287.3	300.4	308.5	293.1	280.0
70°	246.8	261.6	270.5	255.1	240.4
72.5°	211.5	227.9	235.2	220.6	205.9
75°	159.5	174.3	183.2	171.0	155.2
77.5°	113.2	127.1	134.5	123.9	110.8
80°	83.0	97.7	103.5	94.6	84.1
82.5°	58.8	71.1	75.0	69.7	62.5
85°	26.9	35.4	39.9	37.7	35.6
87.5°	6.9	12.8	16.4	16.4	17.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	17.0	89.9	208.5	60.7	45.8
95°	55.1	218.8	983.3	340.3	209.8
97.5°	101.3	256.3	1514.4	1083.6	742.6
100°	133.5	278.6	1629.6	1650.7	1271.5
102.5°	169.1	302.6	1604.2	2112.9	1781.8
105°	224.6	340.7	1472.8	2601.5	2473.1
107.5°	281.0	385.0	1319.4	2739.3	2853.7
110°	320.0	417.4	1231.2	2686.6	2943.5

TEST NUMBER: P562471

CATALOG NUMBER: SQ4-PW1-150U-075D-92765-1D-UNV-STD-W-4 (5000K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	357.3	449.7	1171.9	2561.9	2928.3
115°	417.5	504.5	1116.8	2365.9	2778.2
117.5°	470.5	552.1	1084.2	2151.6	2588.3
120°	512.8	581.2	1080.8	2029.1	2447.6
122.5°	546.7	615.1	1072.3	1921.6	2310.3
125°	589.1	653.4	1065.9	1768.9	2114.9
127.5°	635.3	695.4	1062.5	1677.6	1962.8
130°	659.1	719.1	1057.5	1614.1	1862.7
132.5°	684.5	742.9	1057.5	1564.5	1793.2
135°	720.5	780.6	1053.2	1494.2	1689.0
137.5°	754.4	812.9	1052.8	1434.7	1602.9
140°	779.9	839.9	1051.1	1385.4	1547.0
142.5°	808.7	858.8	1056.2	1346.0	1491.0
145°	849.8	893.3	1061.7	1293.2	1409.2
147.5°	885.0	927.2	1071.0	1239.9	1340.2
150°	915.5	944.5	1074.4	1222.2	1292.7
152.5°	939.2	969.9	1077.8	1198.4	1263.9
155°	970.6	993.4	1087.1	1168.7	1216.4
157.5°	1009.6	1023.2	1089.2	1155.3	1189.3
160°	1029.9	1040.3	1097.7	1145.0	1174.0
162.5°	1041.8	1053.8	1099.4	1136.4	1158.8
165°	1072.3	1076.4	1099.8	1123.5	1140.1
167.5°	1093.1	1089.3	1109.6	1120.3	1127.0
170°	1099.8	1097.8	1106.2	1108.5	1116.8
172.5°	1115.1	1108.1	1111.3	1105.1	1111.7
175°	1123.2	1116.9	1112.6	1106.0	1097.7
177.5°	1126.5	1116.6	1111.3	1104.5	1106.2
180°	1114.7	1114.7	1114.7	1114.7	1114.7

(END OF REPORT)