

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562482

Luminaire Tested: **SQ4-PW1-150U-100D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562482
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-150U-100D-92765-1D-UNV-STD-W-4 (4000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10722.2 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 93.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562482
CATALOG NUMBER: SQ4-PW1-150U-100D-92765-1D-UNV-STD-W-4 (4000K)

Luminous Intensity Polar Plot





TEST NUMBER: P562482

CATALOG NUMBER: SQ4-PW1-150U-100D-92765-1D-UNV-STD-W-4 (4000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	37
1	95	91	87	84	86	82	79	76	67	65	63	52	51	50	39	38	38	31
2	87	79	73	68	78	72	67	63	59	55	52	46	44	42	35	33	32	26
3	79	70	63	57	71	63	57	52	52	47	44	41	38	35	31	29	27	22
4	72	62	54	48	65	56	50	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	36	31	51	41	34	29	33	28	24	27	23	20	20	18	16	13
8	52	40	33	27	47	37	30	25	30	25	22	24	21	18	19	16	14	12
9	48	37	29	24	44	34	27	23	28	23	19	22	19	16	17	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14442	14442	14442
5°	14536	14420	14356
10°	14419	14303	14225
15°	14266	14108	14055
20°	14096	13879	13853
25°	13899	13646	13605
30°	13606	13400	13312
35°	13218	13033	12955
40°	12806	12608	12557
45°	12308	12146	12093
50°	11799	11699	11621
55°	11247	11247	11070
60°	10560	10765	10383
65°	9665	10147	9424
70°	8519	9339	8295
75°	7276	8359	7080
80°	5643	7035	5717
85°	3652	5399	4817



TEST NUMBER: P562482

CATALOG NUMBER: SQ4-PW1-150U-100D-92765-1D-UNV-STD-W-4 (4000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.4	1.4
10°-20°	416.1	3.9
20°-30°	617.3	5.8
30°-40°	722.3	6.7
40°-50°	719.1	6.7
50°-60°	620.9	5.8
60°-70°	447.0	4.2
70°-80°	234.4	2.2
80°-90°	58.1	0.5
90°-100°	494.4	4.6
100°-110°	1406.7	13.1
110°-120°	1347.8	12.6
120°-130°	1066.7	9.9
130°-140°	856.2	8.0
140°-150°	670.3	6.3
150°-160°	490.5	4.6
160°-170°	303.8	2.8
170°-180°	103.1	1.0
0°-30°	1180.8	11.0
0°-40°	1903.1	17.7
0°-60°	3243.1	30.2
0°-90°	3982.6	37.1
90°-120°	3249.0	30.3
90°-150°	5842.2	54.5
90°-180°	6740.0	62.9
0°-180°	10722.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1565	1565	1565	1565	1565	
5°	1570	1552	1557	1553	1550	149
15°	1494	1475	1477	1474	1472	421
25°	1365	1342	1340	1332	1336	628
35°	1174	1158	1157	1146	1150	734
45°	943	935	931	928	927	728
55°	699	698	699	690	688	624
65°	443	456	465	446	432	439
75°	204	223	234	219	199	219
85°	34	45	51	48	46	45
90°	0	0	0	0	0	3
95°	54	213	957	331	204	61
105°	219	332	1434	2532	2407	231
115°	406	491	1087	2303	2704	400
125°	573	636	1038	1722	2059	513
135°	701	760	1025	1454	1644	541
145°	827	870	1033	1259	1372	517
155°	945	967	1058	1138	1184	437
165°	1044	1048	1070	1094	1110	294
175°	1093	1087	1083	1076	1068	104
180°	1085	1085	1085	1085	1085	



TEST NUMBER: P562482

CATALOG NUMBER: SQ4-PW1-150U-100D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1565.3	1565.3	1565.3	1565.3	1565.3
2.5°	1574.1	1561.2	1565.3	1561.8	1554.3
5°	1569.5	1551.9	1557.0	1552.8	1550.1
7.5°	1553.5	1537.3	1541.0	1536.6	1535.0
10°	1539.1	1522.9	1526.7	1521.1	1518.4
12.5°	1522.6	1505.3	1509.0	1503.5	1501.9
15°	1493.6	1474.7	1477.0	1474.2	1471.5
17.5°	1459.9	1440.8	1441.2	1436.8	1436.2
20°	1435.7	1415.4	1413.6	1408.2	1410.9
22.5°	1409.2	1387.9	1386.0	1378.4	1382.2
25°	1365.3	1342.4	1340.5	1332.3	1336.4
27.5°	1314.6	1291.9	1292.0	1280.5	1284.8
30°	1277.1	1255.5	1257.8	1244.1	1249.5
32.5°	1237.4	1217.9	1219.2	1205.5	1210.9
35°	1173.6	1157.5	1157.1	1146.2	1150.2
37.5°	1108.5	1094.3	1092.0	1085.7	1086.8
40°	1063.3	1051.2	1046.8	1042.6	1042.6
42.5°	1015.9	1004.8	1000.4	997.4	996.3
45°	943.3	935.2	930.9	928.1	926.8
47.5°	871.6	864.1	860.3	858.3	857.0
50°	822.0	816.6	815.1	810.9	809.6
52.5°	772.3	769.1	767.6	762.4	761.0
55°	699.2	697.9	699.2	689.5	688.2
57.5°	623.1	625.2	629.7	616.7	613.4
60°	572.3	577.7	583.4	568.1	562.7
62.5°	520.5	529.1	537.0	519.5	511.9
65°	442.7	456.2	464.8	446.5	431.7
67.5°	367.7	384.4	394.7	375.0	358.3
70°	315.8	334.7	346.2	326.4	307.5
72.5°	270.6	291.6	300.9	282.3	263.4
75°	204.1	223.0	234.5	218.8	198.6
77.5°	144.8	162.6	172.1	158.5	141.8
80°	106.2	125.1	132.4	121.1	107.6
82.5°	75.3	90.9	96.0	89.2	80.0
85°	34.5	45.3	51.0	48.2	45.5
87.5°	8.8	16.4	21.0	21.0	22.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	16.5	87.5	203.0	59.1	44.6
95°	53.6	213.0	957.1	331.3	204.2
97.5°	98.6	249.5	1474.0	1054.7	722.8
100°	129.9	271.1	1586.2	1606.7	1237.6
102.5°	164.6	294.5	1561.5	2056.6	1734.3
105°	218.6	331.6	1433.6	2532.2	2407.2
107.5°	273.5	374.8	1284.2	2666.3	2777.6
110°	311.5	406.3	1198.4	2615.0	2865.1

TEST NUMBER: P562482

CATALOG NUMBER: SQ4-PW1-150U-100D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	347.8	437.7	1140.7	2493.7	2850.2
115°	406.4	491.1	1087.0	2302.8	2704.2
117.5°	457.9	537.4	1055.3	2094.2	2519.4
120°	499.2	565.7	1052.0	1975.0	2382.4
122.5°	532.2	598.7	1043.7	1870.4	2248.8
125°	573.4	636.0	1037.5	1721.8	2058.6
127.5°	618.4	676.9	1034.2	1632.9	1910.5
130°	641.5	700.0	1029.3	1571.1	1813.1
132.5°	666.3	723.1	1029.3	1522.8	1745.5
135°	701.3	759.8	1025.2	1454.4	1644.0
137.5°	734.3	791.2	1024.7	1396.5	1560.2
140°	759.1	817.6	1023.1	1348.5	1505.8
142.5°	787.1	835.9	1028.0	1310.1	1451.3
145°	827.1	869.5	1033.4	1258.7	1371.7
147.5°	861.4	902.5	1042.5	1206.8	1304.4
150°	891.1	919.3	1045.8	1189.7	1258.2
152.5°	914.2	944.0	1049.1	1166.5	1230.2
155°	944.7	966.9	1058.2	1137.6	1184.0
157.5°	982.7	996.0	1060.2	1124.5	1157.6
160°	1002.5	1012.6	1068.5	1114.5	1142.7
162.5°	1014.0	1025.7	1070.1	1106.1	1127.9
165°	1043.7	1047.8	1070.5	1093.6	1109.7
167.5°	1063.9	1060.3	1080.0	1090.5	1096.9
170°	1070.5	1068.5	1076.7	1079.0	1087.0
172.5°	1085.4	1078.5	1081.7	1075.6	1082.1
175°	1093.2	1087.2	1082.9	1076.5	1068.5
177.5°	1096.5	1086.8	1081.7	1075.1	1076.7
180°	1085.0	1085.0	1085.0	1085.0	1085.0

(END OF REPORT)