

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562456

Luminaire Tested: **SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562456
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (4000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8762.5 lumens
Efficiency: N/A
Efficacy: 121.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 71.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562456
CATALOG NUMBER: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (4000K)

Luminous Intensity Polar Plot





TEST NUMBER: P562456

CATALOG NUMBER: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (4000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	23		
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27	20		
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22	16		
3	76	67	60	55	67	60	54	49	46	42	39	33	31	29	22	20	19	14		
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	19	18	16	12		
5	64	53	45	39	56	47	41	36	37	32	28	27	24	21	17	16	14	10		
6	59	47	39	34	52	42	36	31	33	28	25	24	21	18	16	14	13	9		
7	54	42	35	29	48	38	31	27	30	25	21	22	19	16	14	13	11	8		
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10	7		
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	7		
10	43	32	25	20	38	29	23	18	22	18	15	17	14	11	11	9	8	6		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7336	7336	7336
5°	7383	7325	7292
10°	7324	7265	7226
15°	7247	7167	7139
20°	7160	7050	7036
25°	7060	6932	6910
30°	6911	6807	6762
35°	6714	6619	6580
40°	6505	6404	6378
45°	6253	6169	6142
50°	5993	5942	5902
55°	5714	5714	5623
60°	5364	5467	5274
65°	4910	5154	4788
70°	4327	4742	4214
75°	3697	4246	3597
80°	2864	3570	2901
85°	1853	2742	2445



TEST NUMBER: P562456

CATALOG NUMBER: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (4000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.9	0.9
10°-20°	211.4	2.4
20°-30°	313.5	3.6
30°-40°	366.9	4.2
40°-50°	365.2	4.2
50°-60°	315.4	3.6
60°-70°	227.0	2.6
70°-80°	119.1	1.4
80°-90°	29.5	0.3
90°-100°	494.4	5.6
100°-110°	1406.7	16.1
110°-120°	1347.8	15.4
120°-130°	1066.7	12.2
130°-140°	856.2	9.8
140°-150°	670.3	7.6
150°-160°	490.5	5.6
160°-170°	303.8	3.5
170°-180°	103.1	1.2
0°-30°	599.8	6.8
0°-40°	966.7	11.0
0°-60°	1647.3	18.8
0°-90°	2022.9	23.1
90°-120°	3249.0	37.1
90°-150°	5842.2	66.7
90°-180°	6740.0	76.9
0°-180°	8762.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	795	795	795	795	795	
5°	797	788	791	789	787	76
15°	759	749	750	749	747	214
25°	694	682	681	677	679	319
35°	596	588	588	582	584	373
45°	479	475	473	471	471	370
55°	355	354	355	350	350	317
65°	225	232	236	227	219	223
75°	104	113	119	111	101	111
85°	18	23	26	24	23	23
90°	0	0	0	0	0	3
95°	54	213	957	331	204	61
105°	219	332	1434	2532	2407	231
115°	406	491	1087	2303	2704	400
125°	573	636	1038	1722	2059	513
135°	701	760	1025	1454	1644	541
145°	827	870	1033	1259	1372	517
155°	945	967	1058	1138	1184	437
165°	1044	1048	1070	1094	1110	294
175°	1093	1087	1083	1076	1068	104
180°	1085	1085	1085	1085	1085	



TEST NUMBER: P562456

CATALOG NUMBER: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	795.1	795.1	795.1	795.1	795.1
2.5°	799.6	793.0	795.1	793.3	789.5
5°	797.2	788.3	790.9	788.7	787.4
7.5°	789.1	780.8	782.8	780.5	779.7
10°	781.8	773.6	775.5	772.6	771.3
12.5°	773.4	764.6	766.5	763.7	762.9
15°	758.7	749.1	750.3	748.8	747.4
17.5°	741.6	731.8	732.0	729.8	729.5
20°	729.2	719.0	718.0	715.3	716.6
22.5°	715.8	705.0	704.0	700.1	702.1
25°	693.5	681.9	680.9	676.7	678.8
27.5°	667.7	656.2	656.2	650.4	652.6
30°	648.7	637.7	638.9	631.9	634.7
32.5°	628.5	618.6	619.3	612.3	615.1
35°	596.1	587.9	587.7	582.2	584.2
37.5°	563.1	555.8	554.7	551.5	552.0
40°	540.1	533.9	531.7	529.6	529.6
42.5°	516.0	510.4	508.2	506.6	506.1
45°	479.2	475.0	472.8	471.4	470.7
47.5°	442.7	438.9	437.0	436.0	435.3
50°	417.5	414.8	414.0	411.9	411.2
52.5°	392.3	390.6	389.9	387.2	386.5
55°	355.2	354.5	355.2	350.2	349.6
57.5°	316.5	317.6	319.9	313.2	311.6
60°	290.7	293.5	296.3	288.5	285.8
62.5°	264.4	268.8	272.8	263.9	260.0
65°	224.9	231.7	236.1	226.8	219.3
67.5°	186.8	195.3	200.5	190.5	182.0
70°	160.4	170.0	175.8	165.8	156.2
72.5°	137.4	148.1	152.9	143.4	133.8
75°	103.7	113.3	119.1	111.1	100.9
77.5°	73.6	82.6	87.4	80.5	72.0
80°	53.9	63.5	67.2	61.5	54.6
82.5°	38.2	46.2	48.8	45.3	40.6
85°	17.5	23.0	25.9	24.5	23.1
87.5°	4.5	8.3	10.6	10.7	11.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	16.5	87.5	203.0	59.1	44.6
95°	53.6	213.0	957.1	331.3	204.2
97.5°	98.6	249.5	1474.0	1054.7	722.8
100°	129.9	271.1	1586.2	1606.7	1237.6
102.5°	164.6	294.5	1561.5	2056.6	1734.3
105°	218.6	331.6	1433.6	2532.2	2407.2
107.5°	273.5	374.8	1284.2	2666.3	2777.6
110°	311.5	406.3	1198.4	2615.0	2865.1

TEST NUMBER: P562456

CATALOG NUMBER: SQ4-PW1-150U-050D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	347.8	437.7	1140.7	2493.7	2850.2
115°	406.4	491.1	1087.0	2302.8	2704.2
117.5°	457.9	537.4	1055.3	2094.2	2519.4
120°	499.2	565.7	1052.0	1975.0	2382.4
122.5°	532.2	598.7	1043.7	1870.4	2248.8
125°	573.4	636.0	1037.5	1721.8	2058.6
127.5°	618.4	676.9	1034.2	1632.9	1910.5
130°	641.5	700.0	1029.3	1571.1	1813.1
132.5°	666.3	723.1	1029.3	1522.8	1745.5
135°	701.3	759.8	1025.2	1454.4	1644.0
137.5°	734.3	791.2	1024.7	1396.5	1560.2
140°	759.1	817.6	1023.1	1348.5	1505.8
142.5°	787.1	835.9	1028.0	1310.1	1451.3
145°	827.1	869.5	1033.4	1258.7	1371.7
147.5°	861.4	902.5	1042.5	1206.8	1304.4
150°	891.1	919.3	1045.8	1189.7	1258.2
152.5°	914.2	944.0	1049.1	1166.5	1230.2
155°	944.7	966.9	1058.2	1137.6	1184.0
157.5°	982.7	996.0	1060.2	1124.5	1157.6
160°	1002.5	1012.6	1068.5	1114.5	1142.7
162.5°	1014.0	1025.7	1070.1	1106.1	1127.9
165°	1043.7	1047.8	1070.5	1093.6	1109.7
167.5°	1063.9	1060.3	1080.0	1090.5	1096.9
170°	1070.5	1068.5	1076.7	1079.0	1087.0
172.5°	1085.4	1078.5	1081.7	1075.6	1082.1
175°	1093.2	1087.2	1082.9	1076.5	1068.5
177.5°	1096.5	1086.8	1081.7	1075.1	1076.7
180°	1085.0	1085.0	1085.0	1085.0	1085.0

(END OF REPORT)