

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562492

Luminaire Tested: **SQ4-PW1-150U-125D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562492
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-150U-125D-92765-1D-UNV-STD-W-4 (2700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11069.5 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 106.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562492
CATALOG NUMBER: SQ4-PW1-150U-125D-92765-1D-UNV-STD-W-4 (2700K)

Luminous Intensity Polar Plot





TEST NUMBER: P562492

CATALOG NUMBER: SQ4-PW1-150U-125D-92765-1D-UNV-STD-W-4 (2700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36
2	88	80	74	69	80	74	69	64	61	57	54	49	47	45	39	37	35	30
3	80	71	64	58	73	65	59	54	54	49	46	44	40	38	34	32	30	26
4	73	63	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26	22
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17179	17179	17179
5°	17290	17154	17078
10°	17152	17014	16921
15°	16970	16782	16719
20°	16768	16510	16478
25°	16533	16233	16183
30°	16184	15940	15834
35°	15724	15503	15410
40°	15233	14997	14937
45°	14641	14449	14384
50°	14035	13917	13822
55°	13378	13378	13168
60°	12562	12804	12350
65°	11496	12070	11210
70°	10135	11109	9868
75°	8655	9942	8420
80°	6711	8368	6801
85°	4340	6426	5727



TEST NUMBER: P562492

CATALOG NUMBER: SQ4-PW1-150U-125D-92765-1D-UNV-STD-W-4 (2700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.3	1.6
10°-20°	495.0	4.5
20°-30°	734.3	6.6
30°-40°	859.2	7.8
40°-50°	855.3	7.7
50°-60°	738.6	6.7
60°-70°	531.7	4.8
70°-80°	278.8	2.5
80°-90°	69.1	0.6
90°-100°	464.5	4.2
100°-110°	1321.7	11.9
110°-120°	1266.3	11.4
120°-130°	1002.2	9.1
130°-140°	804.5	7.3
140°-150°	629.8	5.7
150°-160°	460.8	4.2
160°-170°	285.4	2.6
170°-180°	96.9	0.9
0°-30°	1404.6	12.7
0°-40°	2263.8	20.5
0°-60°	3857.8	34.9
0°-90°	4737.4	42.8
90°-120°	3052.5	27.6
90°-150°	5489.0	49.6
90°-180°	6332.0	57.2
0°-180°	11069.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1862	1862	1862	1862	1862	
5°	1867	1846	1852	1847	1844	177
15°	1777	1754	1757	1754	1750	501
25°	1624	1597	1595	1585	1590	747
35°	1396	1377	1376	1363	1368	873
45°	1122	1112	1107	1104	1102	866
55°	832	830	832	820	819	742
65°	527	543	553	531	514	522
75°	243	265	279	260	236	260
85°	41	54	61	57	54	54
90°	0	0	0	0	0	4
95°	50	200	899	311	192	58
105°	205	312	1347	2379	2262	217
115°	382	461	1021	2164	2541	376
125°	539	598	975	1618	1934	482
135°	659	714	963	1366	1545	508
145°	777	817	971	1183	1289	485
155°	888	908	994	1069	1112	410
165°	981	984	1006	1028	1043	276
175°	1027	1022	1018	1012	1004	97
180°	1019	1019	1019	1019	1019	

TEST NUMBER: P562492

CATALOG NUMBER: SQ4-PW1-150U-125D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1862.0	1862.0	1862.0	1862.0	1862.0
2.5°	1872.5	1857.1	1862.0	1857.9	1848.9
5°	1866.9	1846.1	1852.2	1847.2	1844.0
7.5°	1847.9	1828.6	1833.1	1827.8	1825.9
10°	1830.8	1811.6	1816.1	1809.4	1806.2
12.5°	1811.1	1790.6	1795.1	1788.5	1786.5
15°	1776.7	1754.2	1757.0	1753.7	1750.4
17.5°	1736.7	1713.9	1714.4	1709.1	1708.4
20°	1707.8	1683.7	1681.5	1675.1	1678.3
22.5°	1676.3	1650.9	1648.7	1639.6	1644.1
25°	1624.1	1596.9	1594.6	1584.9	1589.7
27.5°	1563.8	1536.8	1536.8	1523.2	1528.3
30°	1519.1	1493.5	1496.2	1479.9	1486.3
32.5°	1471.9	1448.8	1450.2	1434.0	1440.4
35°	1396.1	1376.8	1376.4	1363.4	1368.2
37.5°	1318.7	1301.7	1299.0	1291.5	1292.7
40°	1264.8	1250.4	1245.2	1240.2	1240.2
42.5°	1208.4	1195.3	1190.0	1186.4	1185.1
45°	1122.1	1112.5	1107.4	1104.0	1102.4
47.5°	1036.8	1027.8	1023.4	1021.0	1019.4
50°	977.8	971.3	969.6	964.6	963.0
52.5°	918.7	914.8	913.1	906.8	905.2
55°	831.7	830.1	831.7	820.2	818.6
57.5°	741.2	743.8	749.1	733.6	729.7
60°	680.8	687.2	693.9	675.8	669.3
62.5°	619.1	629.4	638.8	617.9	609.0
65°	526.6	542.6	552.9	531.1	513.5
67.5°	437.4	457.3	469.5	446.1	426.2
70°	375.7	398.1	411.8	388.3	365.8
72.5°	321.9	346.9	358.0	335.8	313.3
75°	242.8	265.3	278.9	260.3	236.2
77.5°	172.3	193.4	204.7	188.5	168.6
80°	126.3	148.8	157.5	144.0	128.0
82.5°	89.6	108.2	114.2	106.1	95.2
85°	41.0	53.8	60.7	57.3	54.1
87.5°	10.5	19.5	24.9	25.0	26.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	15.5	82.2	190.7	55.5	41.9
95°	50.4	200.1	899.2	311.2	191.9
97.5°	92.6	234.4	1384.9	991.0	679.1
100°	122.1	254.7	1490.3	1509.6	1162.8
102.5°	154.7	276.7	1467.1	1932.3	1629.5
105°	205.4	311.5	1346.9	2379.1	2261.7
107.5°	257.0	352.1	1206.6	2505.1	2609.7
110°	292.6	381.7	1126.0	2456.9	2691.9



TEST NUMBER: P562492

CATALOG NUMBER: SQ4-PW1-150U-125D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	326.7	411.3	1071.7	2342.9	2677.9
115°	381.8	461.4	1021.3	2163.6	2540.7
117.5°	430.2	504.9	991.5	1967.6	2367.1
120°	469.0	531.5	988.4	1855.6	2238.4
122.5°	500.0	562.5	980.6	1757.3	2112.8
125°	538.8	597.5	974.8	1617.7	1934.1
127.5°	581.0	636.0	971.7	1534.2	1795.0
130°	602.7	657.7	967.1	1476.1	1703.5
132.5°	626.0	679.4	967.1	1430.7	1639.9
135°	658.9	713.9	963.2	1366.5	1544.6
137.5°	689.9	743.4	962.8	1312.0	1465.9
140°	713.2	768.1	961.3	1266.9	1414.7
142.5°	739.5	785.4	965.9	1230.9	1363.6
145°	777.1	816.9	970.9	1182.7	1288.8
147.5°	809.3	848.0	979.5	1133.9	1225.6
150°	837.2	863.7	982.6	1117.8	1182.2
152.5°	858.9	887.0	985.7	1095.9	1155.8
155°	887.6	908.5	994.2	1068.8	1112.4
157.5°	923.3	935.8	996.1	1056.5	1087.6
160°	941.9	951.3	1003.9	1047.1	1073.7
162.5°	952.7	963.7	1005.4	1039.2	1059.7
165°	980.6	984.4	1005.8	1027.5	1042.6
167.5°	999.6	996.2	1014.7	1024.6	1030.6
170°	1005.8	1003.9	1011.6	1013.7	1021.3
172.5°	1019.8	1013.3	1016.3	1010.6	1016.7
175°	1027.1	1021.5	1017.5	1011.5	1003.9
177.5°	1030.2	1021.1	1016.3	1010.1	1011.6
180°	1019.4	1019.4	1019.4	1019.4	1019.4

(END OF REPORT)