

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562498

Luminaire Tested: **SQ4-PW1-150U-125D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562498
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-150U-125D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12276.7 lumens
Efficiency: N/A
Efficacy: 115.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 106.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562498

CATALOG NUMBER: SQ4-PW1-150U-125D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P562498

CATALOG NUMBER: SQ4-PW1-150U-125D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43				
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36				
2	88	80	74	69	80	74	69	64	61	57	54	49	47	45	39	37	35	30				
3	80	71	64	58	73	65	59	54	54	49	46	44	40	38	34	32	30	26				
4	73	63	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26	22				
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	28	25	23	19				
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20	17				
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15				
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13				
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12				
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19053	19053	19053
5°	19176	19024	18940
10°	19023	18869	18767
15°	18821	18612	18543
20°	18596	18310	18275
25°	18336	18003	17947
30°	17949	17677	17561
35°	17439	17193	17091
40°	16895	16631	16566
45°	16238	16024	15954
50°	15565	15434	15329
55°	14839	14839	14604
60°	13933	14201	13697
65°	12749	13385	12433
70°	11238	12320	10944
75°	9600	11026	9340
80°	7444	9282	7539
85°	4817	7124	6352



TEST NUMBER: P562498

CATALOG NUMBER: SQ4-PW1-150U-125D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.5	1.6
10°-20°	549.0	4.5
20°-30°	814.4	6.6
30°-40°	952.9	7.8
40°-50°	948.6	7.7
50°-60°	819.2	6.7
60°-70°	589.6	4.8
70°-80°	309.2	2.5
80°-90°	76.7	0.6
90°-100°	515.2	4.2
100°-110°	1465.8	11.9
110°-120°	1404.4	11.4
120°-130°	1111.5	9.1
130°-140°	892.2	7.3
140°-150°	698.5	5.7
150°-160°	511.1	4.2
160°-170°	316.6	2.6
170°-180°	107.4	0.9
0°-30°	1557.8	12.7
0°-40°	2510.7	20.5
0°-60°	4278.5	34.9
0°-90°	5254.0	42.8
90°-120°	3385.4	27.6
90°-150°	6087.6	49.6
90°-180°	7023.0	57.2
0°-180°	12276.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2065	2065	2065	2065	2065	
5°	2070	2047	2054	2049	2045	196
15°	1970	1946	1949	1945	1941	555
25°	1801	1771	1768	1758	1763	828
35°	1548	1527	1526	1512	1517	968
45°	1244	1234	1228	1224	1223	960
55°	922	921	922	910	908	823
65°	584	602	613	589	570	579
75°	269	294	309	289	262	289
85°	46	60	67	64	60	60
90°	0	0	0	0	0	4
95°	56	222	997	345	213	64
105°	228	346	1494	2639	2508	241
115°	423	512	1133	2400	2818	417
125°	598	663	1081	1794	2145	535
135°	731	792	1068	1516	1713	564
145°	862	906	1077	1312	1429	538
155°	984	1008	1103	1185	1234	455
165°	1088	1092	1116	1140	1156	306
175°	1139	1133	1128	1122	1113	108
180°	1131	1131	1131	1131	1131	



TEST NUMBER: P562498

CATALOG NUMBER: SQ4-PW1-150U-125D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2065.1	2065.1	2065.1	2065.1	2065.1
2.5°	2076.7	2059.6	2065.1	2060.5	2050.5
5°	2070.5	2047.4	2054.1	2048.6	2045.0
7.5°	2049.4	2028.1	2033.0	2027.2	2025.0
10°	2030.5	2009.1	2014.1	2006.7	2003.2
12.5°	2008.6	1985.9	1990.8	1983.5	1981.4
15°	1970.4	1945.5	1948.6	1944.9	1941.3
17.5°	1926.0	1900.8	1901.3	1895.5	1894.8
20°	1894.0	1867.3	1864.9	1857.7	1861.3
22.5°	1859.1	1831.0	1828.5	1818.4	1823.4
25°	1801.2	1771.0	1768.5	1757.7	1763.0
27.5°	1734.3	1704.4	1704.4	1689.3	1695.0
30°	1684.8	1656.3	1659.3	1641.3	1648.4
32.5°	1632.4	1606.8	1608.4	1590.3	1597.5
35°	1548.3	1527.0	1526.5	1512.1	1517.4
37.5°	1462.5	1443.6	1440.6	1432.3	1433.7
40°	1402.8	1386.8	1380.9	1375.5	1375.5
42.5°	1340.2	1325.6	1319.8	1315.8	1314.4
45°	1244.5	1233.8	1228.1	1224.4	1222.7
47.5°	1149.9	1139.9	1135.0	1132.4	1130.6
50°	1084.4	1077.3	1075.3	1069.8	1068.0
52.5°	1018.9	1014.6	1012.7	1005.7	1004.0
55°	922.5	920.7	922.5	909.7	907.9
57.5°	822.0	824.9	830.8	813.6	809.3
60°	755.1	762.2	769.6	749.4	742.3
62.5°	686.7	698.0	708.5	685.3	675.4
65°	584.0	601.8	613.1	589.1	569.5
67.5°	485.1	507.1	520.7	494.7	472.7
70°	416.6	441.6	456.7	430.6	405.7
72.5°	357.0	384.7	397.0	372.4	347.5
75°	269.3	294.2	309.3	288.7	262.0
77.5°	191.0	214.5	227.1	209.1	187.0
80°	140.1	165.0	174.7	159.7	141.9
82.5°	99.3	120.0	126.6	117.6	105.5
85°	45.5	59.7	67.3	63.6	60.0
87.5°	11.6	21.6	27.7	27.7	29.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	17.2	91.2	211.5	61.6	46.4
95°	55.9	221.9	997.3	345.2	212.8
97.5°	102.7	259.9	1535.9	1099.1	753.1
100°	135.4	282.5	1652.8	1674.2	1289.6
102.5°	171.5	306.9	1627.1	2143.0	1807.2
105°	227.8	345.5	1493.8	2638.6	2508.3
107.5°	285.0	390.5	1338.2	2778.3	2894.3
110°	324.6	423.3	1248.8	2724.8	2985.4

TEST NUMBER: P562498

CATALOG NUMBER: SQ4-PW1-150U-125D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	362.4	456.1	1188.6	2598.4	2970.0
115°	423.4	511.7	1132.7	2399.6	2817.8
117.5°	477.2	560.0	1099.6	2182.2	2625.2
120°	520.1	589.5	1096.2	2058.0	2482.5
122.5°	554.5	623.9	1087.6	1949.0	2343.2
125°	597.5	662.7	1081.1	1794.1	2145.0
127.5°	644.4	705.3	1077.7	1701.5	1990.7
130°	668.4	729.4	1072.5	1637.1	1889.3
132.5°	694.2	753.5	1072.5	1586.8	1818.8
135°	730.8	791.7	1068.2	1515.5	1713.0
137.5°	765.2	824.4	1067.8	1455.1	1625.8
140°	791.0	851.9	1066.1	1405.1	1569.0
142.5°	820.2	871.0	1071.2	1365.2	1512.3
145°	861.9	906.0	1076.8	1311.6	1429.3
147.5°	897.6	940.4	1086.3	1257.5	1359.2
150°	928.5	957.9	1089.7	1239.6	1311.1
152.5°	952.6	983.7	1093.2	1215.5	1281.9
155°	984.4	1007.5	1102.6	1185.4	1233.7
157.5°	1023.9	1037.8	1104.8	1171.7	1206.2
160°	1044.6	1055.1	1113.4	1161.3	1190.7
162.5°	1056.6	1068.8	1115.1	1152.6	1175.3
165°	1087.6	1091.8	1115.5	1139.5	1156.3
167.5°	1108.6	1104.8	1125.4	1136.3	1143.0
170°	1115.5	1113.4	1122.0	1124.3	1132.7
172.5°	1131.0	1123.8	1127.1	1120.8	1127.5
175°	1139.2	1132.8	1128.4	1121.8	1113.4
177.5°	1142.6	1132.5	1127.1	1120.3	1122.0
180°	1130.6	1130.6	1130.6	1130.6	1130.6

(END OF REPORT)