

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521717

Luminaire Tested: **SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 5/5/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P521717  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,  
Test Lab: INNOVATION CENTER  
Issue Date: 5/5/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (2700K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4350.5 lumens  
Efficiency: N/A  
Efficacy: 95.0 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 45.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P521717

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (2700K)

### Luminous Intensity Polar Plot





TEST NUMBER: P521717

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (2700K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57		
1	101	97	93	90	94	91	88	85	79	76	75	68	66	65	58	57	56	51		
2	93	86	81	76	86	81	76	72	71	67	64	61	59	56	52	51	49	45		
3	86	77	70	65	80	72	67	62	64	59	55	55	52	49	48	45	43	40		
4	79	69	62	56	74	65	59	54	57	52	49	50	47	44	44	41	39	35		
5	73	62	55	49	68	59	52	47	52	47	43	46	42	39	40	37	35	32		
6	68	57	49	44	63	54	47	42	48	42	38	42	38	35	37	34	31	29		
7	63	52	44	39	59	49	42	38	44	38	34	39	35	31	34	31	28	26		
8	59	47	40	35	55	45	38	34	40	35	31	36	32	29	32	28	26	24		
9	55	44	37	32	52	42	35	31	37	32	28	33	29	26	30	26	24	22		
10	52	40	34	29	49	38	32	28	35	30	26	31	27	24	28	24	22	20		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15813	15813	15813
5°	15616	15560	15651
10°	14754	14888	15233
15°	13620	13936	14561
20°	12368	12834	13683
25°	11093	11699	12747
30°	9919	10568	11777
35°	8674	9301	10630
40°	7301	7880	9203
45°	6025	6545	7684
50°	5031	5483	6402
55°	4271	4707	5287
60°	3650	4080	4218
65°	2906	3432	2725
70°	2576	2679	1664
75°	2385	2171	1020
80°	2200	1998	877
85°	1990	1831	720



TEST NUMBER: P521717

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (2700K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	157.2	3.6
10°-20°	408.9	9.4
20°-30°	529.7	12.2
30°-40°	518.7	11.9
40°-50°	397.0	9.1
50°-60°	264.5	6.1
60°-70°	144.4	3.3
70°-80°	60.1	1.4
80°-90°	17.0	0.4
90°-100°	135.9	3.1
100°-110°	386.8	8.9
110°-120°	370.6	8.5
120°-130°	293.3	6.7
130°-140°	235.4	5.4
140°-150°	184.3	4.2
150°-160°	134.8	3.1
160°-170°	83.5	1.9
170°-180°	28.3	0.7
0°-30°	1095.8	25.2
0°-40°	1614.4	37.1
0°-60°	2276.0	52.3
0°-90°	2497.5	57.4
90°-120°	893.2	20.5
90°-150°	1606.2	36.9
90°-180°	1853.0	42.6
0°-180°	4350.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1714	1714	1714	1714	1714	
5°	1686	1669	1680	1684	1690	157
15°	1426	1421	1459	1499	1524	398
25°	1090	1093	1149	1199	1252	501
35°	770	774	826	881	944	479
45°	462	471	502	540	589	360
55°	266	276	293	304	329	241
65°	133	144	157	137	125	138
75°	67	67	61	42	29	71
85°	19	19	17	11	7	20
90°	0	0	0	0	0	2
95°	15	59	263	91	56	17
105°	60	91	394	696	662	64
115°	112	135	299	633	744	110
125°	158	175	285	473	566	141
135°	193	209	282	400	452	149
145°	227	239	284	346	377	142
155°	260	266	291	313	326	120
165°	287	288	294	301	305	81
175°	301	299	298	296	294	28
180°	298	298	298	298	298	

TEST NUMBER: P521717

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (2700K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1713.9	1713.9	1713.9	1713.9	1713.9
2.5°	1718.2	1702.9	1706.7	1706.6	1701.9
5°	1686.1	1669.2	1680.1	1684.0	1689.9
7.5°	1623.6	1610.8	1630.6	1645.3	1657.2
10°	1574.8	1563.8	1589.1	1610.5	1626.0
12.5°	1518.3	1509.0	1540.4	1569.1	1589.3
15°	1425.9	1420.8	1459.0	1498.7	1524.4
17.5°	1327.1	1324.6	1368.5	1414.8	1447.7
20°	1259.7	1259.0	1307.1	1355.3	1393.6
22.5°	1191.7	1193.3	1243.9	1294.1	1337.6
25°	1089.7	1092.7	1149.2	1199.2	1252.2
27.5°	995.4	996.8	1055.1	1108.0	1164.5
30°	931.1	934.7	992.0	1046.7	1105.5
32.5°	866.7	870.9	927.0	983.6	1043.6
35°	770.1	773.8	825.8	881.3	943.8
37.5°	670.5	675.5	721.7	774.2	835.7
40°	606.2	613.5	654.3	703.8	764.1
42.5°	544.2	553.3	591.1	638.1	692.5
45°	461.8	470.6	501.6	539.6	588.9
47.5°	390.8	400.9	424.8	457.5	499.5
50°	350.5	360.0	382.0	406.3	446.0
52.5°	315.0	324.5	344.1	362.8	396.6
55°	265.5	276.5	292.6	303.6	328.7
57.5°	224.9	235.5	248.2	253.2	268.3
60°	197.8	209.6	221.1	220.5	228.6
62.5°	173.1	183.1	194.6	186.7	187.1
65°	133.1	144.1	157.2	137.3	124.8
67.5°	107.5	109.9	123.3	95.8	80.9
70°	95.5	95.5	99.3	74.2	61.7
72.5°	84.1	84.1	80.6	60.3	47.2
75°	66.9	66.9	60.9	41.8	28.6
77.5°	51.6	51.0	46.6	31.2	20.8
80°	41.4	41.4	37.6	24.6	16.5
82.5°	32.3	32.3	29.2	19.2	12.3
85°	18.8	18.8	17.3	11.2	6.8
87.5°	6.6	6.6	6.0	3.6	3.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.5	24.1	55.8	16.2	12.2
95°	14.7	58.6	263.1	91.1	56.1
97.5°	27.1	68.6	405.3	290.0	198.7
100°	35.7	74.5	436.1	441.7	340.3
102.5°	45.3	81.0	429.3	565.4	476.8
105°	60.1	91.2	394.1	696.2	661.8
107.5°	75.2	103.0	353.1	733.1	763.7
110°	85.6	111.7	329.5	719.0	787.7

TEST NUMBER: P521717

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (2700K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	95.6	120.3	313.6	685.6	783.6
115°	111.7	135.0	298.9	633.1	743.5
117.5°	125.9	147.7	290.1	575.8	692.7
120°	137.2	155.5	289.2	543.0	655.0
122.5°	146.3	164.6	287.0	514.2	618.3
125°	157.7	174.8	285.3	473.4	566.0
127.5°	170.0	186.1	284.3	449.0	525.3
130°	176.4	192.5	283.0	431.9	498.5
132.5°	183.2	198.8	283.0	418.7	479.9
135°	192.8	208.9	281.9	399.9	452.0
137.5°	201.9	217.5	281.7	383.9	429.0
140°	208.7	224.8	281.3	370.7	414.0
142.5°	216.4	229.8	282.6	360.2	399.0
145°	227.4	239.1	284.1	346.1	377.1
147.5°	236.8	248.1	286.6	331.8	358.6
150°	245.0	252.8	287.5	327.1	345.9
152.5°	251.3	259.6	288.4	320.7	338.2
155°	259.7	265.8	290.9	312.8	325.5
157.5°	270.2	273.8	291.5	309.2	318.3
160°	275.6	278.4	293.8	306.4	314.2
162.5°	278.8	282.0	294.2	304.1	310.1
165°	287.0	288.1	294.3	300.7	305.1
167.5°	292.5	291.5	296.9	299.8	301.6
170°	294.3	293.8	296.0	296.6	298.9
172.5°	298.4	296.5	297.4	295.7	297.5
175°	300.6	298.9	297.7	296.0	293.8
177.5°	301.5	298.8	297.4	295.6	296.0
180°	298.3	298.3	298.3	298.3	298.3

(END OF REPORT)