

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521705

Luminaire Tested: **SQ4-WB-025U-050D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521705
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-025U-050D-92765-1D-UNV-STD-W-4 (3000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3593.6 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 34.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521705
CATALOG NUMBER: SQ4-WB-025U-050D-92765-1D-UNV-STD-W-4 (3000K)

Luminous Intensity Polar Plot





TEST NUMBER: P521705

CATALOG NUMBER: SQ4-WB-025U-050D-92765-1D-UNV-STD-W-4 (3000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47	47	47	47	
1	98	94	91	88	90	87	84	81	73	71	69	61	59	58	49	48	47	42	42	42	42	
2	90	84	78	74	83	77	73	69	66	62	59	55	52	50	45	43	42	37	37	37	37	
3	83	75	68	63	76	69	63	59	59	55	51	49	46	44	41	39	37	33	33	33	33	
4	77	67	60	54	71	62	56	51	53	48	45	45	41	39	37	35	33	29	29	29	29	
5	71	60	53	47	65	56	49	45	48	43	39	41	37	34	34	31	29	26	26	26	26	
6	66	54	47	42	61	51	44	39	44	39	35	37	34	31	31	29	26	24	24	24	24	
7	61	50	42	37	56	46	40	35	40	35	31	34	31	28	29	26	24	21	21	21	21	
8	57	45	38	33	53	42	36	31	37	32	28	32	28	25	27	24	22	20	20	20	20	
9	53	42	35	30	49	39	33	28	34	29	26	29	26	23	25	22	20	18	18	18	18	
10	50	38	32	27	46	36	30	26	32	27	23	27	24	21	23	21	19	17	17	17	17	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10778	10778	10778
5°	10643	10605	10667
10°	10055	10147	10382
15°	9282	9498	9924
20°	8430	8747	9325
25°	7561	7973	8688
30°	6761	7203	8027
35°	5912	6339	7246
40°	4975	5370	6272
45°	4106	4461	5236
50°	3429	3738	4363
55°	2910	3207	3603
60°	2487	2781	2875
65°	1980	2338	1858
70°	1756	1826	1133
75°	1626	1479	695
80°	1498	1360	600
85°	1355	1249	487



TEST NUMBER: P521705

CATALOG NUMBER: SQ4-WB-025U-050D-92765-1D-UNV-STD-W-4 (3000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.1	3.0
10°-20°	278.7	7.8
20°-30°	361.0	10.0
30°-40°	353.5	9.8
40°-50°	270.6	7.5
50°-60°	180.3	5.0
60°-70°	98.4	2.7
70°-80°	41.0	1.1
80°-90°	11.6	0.3
90°-100°	138.8	3.9
100°-110°	394.8	11.0
110°-120°	378.2	10.5
120°-130°	299.4	8.3
130°-140°	240.3	6.7
140°-150°	188.1	5.2
150°-160°	137.6	3.8
160°-170°	85.3	2.4
170°-180°	28.9	0.8
0°-30°	746.8	20.8
0°-40°	1100.3	30.6
0°-60°	1551.2	43.2
0°-90°	1702.2	47.4
90°-120°	911.8	25.4
90°-150°	1639.5	45.6
90°-180°	1891.0	52.6
0°-180°	3593.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1168	1168	1168	1168	1168	
5°	1149	1138	1145	1148	1152	107
15°	972	968	994	1021	1039	271
25°	743	745	783	817	853	342
35°	525	527	563	601	643	326
45°	315	321	342	368	401	245
55°	181	188	199	207	224	164
65°	91	98	107	94	85	94
75°	46	46	42	28	20	49
85°	13	13	12	8	5	14
90°	0	0	0	0	0	1
95°	15	60	269	93	57	17
105°	61	93	402	711	676	65
115°	114	138	305	646	759	112
125°	161	178	291	483	578	144
135°	197	213	288	408	461	152
145°	232	244	290	353	385	145
155°	265	271	297	319	332	123
165°	293	294	300	307	311	82
175°	307	305	304	302	300	29
180°	304	304	304	304	304	

TEST NUMBER: P521705

CATALOG NUMBER: SQ4-WB-025U-050D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1168.2	1168.2	1168.2	1168.2	1168.2
2.5°	1171.0	1160.6	1163.2	1163.2	1160.0
5°	1149.2	1137.7	1145.1	1147.7	1151.8
7.5°	1106.5	1097.8	1111.4	1121.4	1129.5
10°	1073.3	1065.8	1083.1	1097.7	1108.2
12.5°	1034.8	1028.5	1049.9	1069.4	1083.2
15°	971.8	968.3	994.4	1021.4	1039.0
17.5°	904.5	902.8	932.7	964.3	986.7
20°	858.6	858.1	890.9	923.7	949.8
22.5°	812.2	813.3	847.8	882.0	911.7
25°	742.7	744.7	783.2	817.4	853.4
27.5°	678.4	679.3	719.1	755.2	793.7
30°	634.6	637.1	676.1	713.4	753.5
32.5°	590.7	593.6	631.8	670.4	711.2
35°	524.9	527.4	562.8	600.7	643.3
37.5°	457.0	460.4	491.9	527.7	569.6
40°	413.1	418.1	445.9	479.7	520.8
42.5°	370.9	377.1	402.9	434.9	472.0
45°	314.7	320.7	341.9	367.8	401.3
47.5°	266.3	273.3	289.5	311.8	340.5
50°	238.9	245.4	260.4	276.9	304.0
52.5°	214.7	221.2	234.6	247.3	270.3
55°	180.9	188.5	199.4	207.0	224.0
57.5°	153.3	160.5	169.1	172.6	182.9
60°	134.8	142.8	150.7	150.3	155.8
62.5°	118.0	124.8	132.7	127.2	127.5
65°	90.7	98.2	107.1	93.6	85.1
67.5°	73.3	74.9	84.1	65.3	55.2
70°	65.1	65.1	67.7	50.6	42.0
72.5°	57.3	57.3	54.9	41.1	32.2
75°	45.6	45.6	41.5	28.5	19.5
77.5°	35.2	34.8	31.8	21.3	14.1
80°	28.2	28.2	25.6	16.8	11.3
82.5°	22.0	22.0	19.9	13.1	8.4
85°	12.8	12.8	11.8	7.6	4.6
87.5°	4.5	4.5	4.1	2.5	2.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.6	24.6	57.0	16.6	12.5
95°	15.1	59.8	268.6	93.0	57.3
97.5°	27.7	70.0	413.7	296.0	202.8
100°	36.5	76.1	445.1	450.9	347.3
102.5°	46.2	82.6	438.2	577.2	486.7
105°	61.4	93.1	402.3	710.6	675.5
107.5°	76.8	105.2	360.4	748.3	779.5
110°	87.4	114.0	336.3	733.9	804.0

TEST NUMBER: P521705

CATALOG NUMBER: SQ4-WB-025U-050D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	97.6	122.8	320.1	699.8	799.9
115°	114.0	137.8	305.1	646.3	758.9
117.5°	128.5	150.8	296.1	587.7	707.0
120°	140.1	158.8	295.2	554.3	668.6
122.5°	149.3	168.0	292.9	524.9	631.1
125°	160.9	178.5	291.2	483.2	577.7
127.5°	173.5	190.0	290.2	458.3	536.1
130°	180.0	196.4	288.9	440.9	508.8
132.5°	187.0	202.9	288.9	427.3	489.8
135°	196.8	213.2	287.7	408.2	461.4
137.5°	206.1	222.0	287.6	391.9	437.9
140°	213.0	229.4	287.1	378.4	422.6
142.5°	220.9	234.6	288.5	367.7	407.3
145°	232.1	244.0	290.0	353.2	384.9
147.5°	241.7	253.3	292.6	338.7	366.1
150°	250.1	258.0	293.5	333.9	353.1
152.5°	256.6	264.9	294.4	327.3	345.2
155°	265.1	271.3	297.0	319.3	332.3
157.5°	275.8	279.5	297.5	315.6	324.9
160°	281.3	284.2	299.9	312.8	320.7
162.5°	284.6	287.9	300.3	310.4	316.5
165°	292.9	294.0	300.4	306.9	311.4
167.5°	298.6	297.6	303.1	306.0	307.8
170°	300.4	299.9	302.2	302.8	305.1
172.5°	304.6	302.7	303.6	301.9	303.7
175°	306.8	305.1	303.9	302.1	299.9
177.5°	307.7	305.0	303.6	301.7	302.2
180°	304.5	304.5	304.5	304.5	304.5

(END OF REPORT)