

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521719

Luminaire Tested: **SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 5/5/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P521719  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,  
Test Lab: INNOVATION CENTER  
Issue Date: 5/5/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (3500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4547.2 lumens  
Efficiency: N/A  
Efficacy: 99.1 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P521719

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (3500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P521719

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (3500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57																												
1	101	97	93	90	94	91	88	85	79	76	75	68	66	65	58	57	56	51																												
2	93	86	81	76	86	81	76	72	71	67	64	61	59	56	52	51	49	45																												
3	86	77	70	65	80	72	67	62	64	59	55	55	52	49	48	45	43	40																												
4	79	69	62	56	74	65	59	54	57	52	49	50	47	44	44	41	39	35																												
5	73	62	55	49	68	59	52	47	52	47	43	46	42	39	40	37	35	32																												
6	68	57	49	44	63	54	47	42	48	42	38	42	38	35	37	34	31	29																												
7	63	52	44	39	59	49	42	38	44	38	34	39	35	31	34	31	28	26																												
8	59	47	40	35	55	45	38	34	40	35	31	36	32	29	32	28	26	24																												
9	55	44	37	32	52	42	35	31	37	32	28	33	29	26	30	26	24	22																												
10	52	40	34	29	49	38	32	28	35	30	26	31	27	24	28	24	22	20																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16529	16529	16529
5°	16322	16264	16358
10°	15421	15561	15922
15°	14236	14566	15220
20°	12928	13414	14301
25°	11595	12227	13324
30°	10368	11046	12310
35°	9066	9721	11111
40°	7631	8237	9618
45°	6297	6841	8031
50°	5258	5731	6690
55°	4464	4919	5525
60°	3814	4264	4410
65°	3037	3587	2849
70°	2692	2800	1740
75°	2495	2271	1066
80°	2295	2088	919
85°	2085	1916	752



TEST NUMBER: P521719

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (3500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	164.3	3.6
10°-20°	427.4	9.4
20°-30°	553.6	12.2
30°-40°	542.1	11.9
40°-50°	415.0	9.1
50°-60°	276.5	6.1
60°-70°	150.9	3.3
70°-80°	62.9	1.4
80°-90°	17.8	0.4
90°-100°	142.1	3.1
100°-110°	404.2	8.9
110°-120°	387.3	8.5
120°-130°	306.6	6.7
130°-140°	246.0	5.4
140°-150°	192.6	4.2
150°-160°	140.9	3.1
160°-170°	87.3	1.9
170°-180°	29.6	0.7
0°-30°	1145.3	25.2
0°-40°	1687.4	37.1
0°-60°	2378.9	52.3
0°-90°	2610.5	57.4
90°-120°	933.6	20.5
90°-150°	1678.9	36.9
90°-180°	1937.0	42.6
0°-180°	4547.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1792	1792	1792	1792	1792	
5°	1762	1745	1756	1760	1766	164
15°	1490	1485	1525	1566	1593	416
25°	1139	1142	1201	1254	1309	524
35°	805	809	863	921	986	500
45°	483	492	524	564	616	376
55°	278	289	306	317	344	252
65°	139	151	164	144	130	145
75°	70	70	64	44	30	75
85°	20	20	18	12	7	21
90°	0	0	0	0	0	2
95°	15	61	275	95	59	18
105°	63	95	412	728	692	66
115°	117	141	312	662	777	115
125°	165	183	298	495	592	147
135°	202	218	295	418	472	156
145°	238	250	297	362	394	148
155°	272	278	304	327	340	126
165°	300	301	308	314	319	84
175°	314	312	311	309	307	30
180°	312	312	312	312	312	

TEST NUMBER: P521719

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (3500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1791.5	1791.5	1791.5	1791.5	1791.5
2.5°	1795.9	1779.9	1783.9	1783.8	1778.9
5°	1762.4	1744.7	1756.1	1760.1	1766.3
7.5°	1697.0	1683.6	1704.4	1719.7	1732.2
10°	1646.0	1634.5	1661.0	1683.3	1699.5
12.5°	1586.9	1577.2	1610.0	1640.1	1661.1
15°	1490.4	1485.0	1525.0	1566.5	1593.4
17.5°	1387.1	1384.5	1430.3	1478.7	1513.2
20°	1316.7	1315.9	1366.2	1416.6	1456.6
22.5°	1245.6	1247.3	1300.2	1352.6	1398.1
25°	1139.0	1142.1	1201.1	1253.5	1308.8
27.5°	1040.4	1041.8	1102.9	1158.1	1217.1
30°	973.2	977.0	1036.8	1094.0	1155.5
32.5°	905.9	910.3	968.9	1028.0	1090.7
35°	804.9	808.8	863.1	921.2	986.5
37.5°	700.9	706.1	754.3	809.2	873.5
40°	633.6	641.3	683.9	735.6	798.6
42.5°	568.8	578.3	617.9	666.9	723.8
45°	482.6	491.9	524.3	564.0	615.5
47.5°	408.4	419.0	444.0	478.1	522.1
50°	366.3	376.3	399.3	424.6	466.1
52.5°	329.2	339.2	359.7	379.2	414.6
55°	277.5	289.0	305.8	317.4	343.5
57.5°	235.0	246.1	259.4	264.6	280.5
60°	206.7	219.0	231.1	230.5	239.0
62.5°	181.0	191.4	203.4	195.1	195.6
65°	139.1	150.7	164.3	143.6	130.5
67.5°	112.4	114.9	128.9	100.1	84.6
70°	99.8	99.8	103.8	77.5	64.5
72.5°	87.9	87.9	84.3	63.0	49.4
75°	70.0	70.0	63.7	43.7	29.9
77.5°	53.9	53.3	48.7	32.6	21.7
80°	43.2	43.2	39.3	25.7	17.3
82.5°	33.8	33.8	30.5	20.1	12.9
85°	19.7	19.7	18.1	11.7	7.1
87.5°	6.9	6.9	6.3	3.8	3.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.7	25.1	58.3	17.0	12.8
95°	15.4	61.2	275.0	95.2	58.7
97.5°	28.3	71.7	423.6	303.1	207.7
100°	37.3	77.9	455.8	461.7	355.7
102.5°	47.3	84.6	448.7	591.0	498.4
105°	62.8	95.3	412.0	727.7	691.7
107.5°	78.6	107.7	369.0	766.2	798.2
110°	89.5	116.7	344.4	751.5	823.3

TEST NUMBER: P521719

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (3500K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	99.9	125.8	327.8	716.6	819.1
115°	116.8	141.1	312.4	661.8	777.1
117.5°	131.6	154.4	303.3	601.8	724.0
120°	143.4	162.6	302.3	567.6	684.6
122.5°	152.9	172.1	299.9	537.5	646.2
125°	164.8	182.8	298.2	494.8	591.6
127.5°	177.7	194.5	297.2	469.3	549.0
130°	184.3	201.2	295.8	451.5	521.0
132.5°	191.5	207.8	295.8	437.6	501.6
135°	201.5	218.3	294.6	417.9	472.4
137.5°	211.0	227.4	294.5	401.3	448.4
140°	218.1	234.9	294.0	387.5	432.7
142.5°	226.2	240.2	295.4	376.5	417.1
145°	237.7	249.9	297.0	361.7	394.2
147.5°	247.5	259.4	299.6	346.8	374.9
150°	256.1	264.2	300.5	341.9	361.6
152.5°	262.7	271.3	301.5	335.2	353.5
155°	271.5	277.9	304.1	326.9	340.2
157.5°	282.4	286.2	304.7	323.1	332.7
160°	288.1	291.0	307.0	320.3	328.4
162.5°	291.4	294.8	307.5	317.9	324.1
165°	299.9	301.1	307.6	314.3	318.9
167.5°	305.7	304.7	310.4	313.4	315.2
170°	307.6	307.1	309.4	310.1	312.4
172.5°	311.9	309.9	310.8	309.1	311.0
175°	314.2	312.4	311.2	309.4	307.0
177.5°	315.1	312.3	310.8	309.0	309.4
180°	311.8	311.8	311.8	311.8	311.8

(END OF REPORT)