

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521723

Luminaire Tested: **SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 5/5/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P521723  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,  
Test Lab: INNOVATION CENTER  
Issue Date: 5/5/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (5700K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4825.0 lumens  
Efficiency: N/A  
Efficacy: 105.3 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 45.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P521723

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (5700K)

### Luminous Intensity Polar Plot





TEST NUMBER: P521723

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (5700K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57
1	101	97	93	90	94	91	88	85	79	76	75	68	66	65	58	57	56	51
2	93	86	81	76	86	81	76	72	71	67	64	61	59	56	52	51	49	45
3	86	77	70	65	80	72	67	62	64	59	55	55	52	49	48	45	43	40
4	79	69	62	56	74	65	59	54	57	52	49	50	47	44	44	41	39	35
5	73	62	55	49	68	59	52	47	52	47	43	46	42	39	40	37	35	32
6	68	57	49	44	63	54	47	42	48	42	38	42	38	35	37	34	31	29
7	63	52	44	39	59	49	42	38	44	38	34	39	35	31	34	31	28	26
8	59	47	40	35	55	45	38	34	40	35	31	36	32	29	32	28	26	24
9	55	44	37	32	52	42	35	31	37	32	28	33	29	26	30	26	24	22
10	52	40	34	29	49	38	32	28	35	30	26	31	27	24	28	24	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17538	17538	17538
5°	17319	17257	17358
10°	16363	16511	16894
15°	15105	15456	16149
20°	13717	14233	15174
25°	12304	12974	14137
30°	11001	11720	13062
35°	9620	10315	11790
40°	8097	8739	10206
45°	6682	7259	8522
50°	5579	6082	7099
55°	4736	5220	5863
60°	4048	4525	4680
65°	3222	3805	3024
70°	2857	2970	1845
75°	2645	2410	1130
80°	2439	2216	972
85°	2212	2032	794



TEST NUMBER: P521723

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (5700K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	174.4	3.6
10°-20°	453.5	9.4
20°-30°	587.4	12.2
30°-40°	575.2	11.9
40°-50°	440.3	9.1
50°-60°	293.4	6.1
60°-70°	160.1	3.3
70°-80°	66.7	1.4
80°-90°	18.9	0.4
90°-100°	150.8	3.1
100°-110°	428.9	8.9
110°-120°	411.0	8.5
120°-130°	325.3	6.7
130°-140°	261.1	5.4
140°-150°	204.4	4.2
150°-160°	149.6	3.1
160°-170°	92.6	1.9
170°-180°	31.4	0.7
0°-30°	1215.3	25.2
0°-40°	1790.5	37.1
0°-60°	2524.2	52.3
0°-90°	2769.9	57.4
90°-120°	990.7	20.5
90°-150°	1781.4	36.9
90°-180°	2055.0	42.6
0°-180°	4825.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1901	1901	1901	1901	1901	
5°	1870	1851	1863	1868	1874	174
15°	1581	1576	1618	1662	1691	442
25°	1209	1212	1274	1330	1389	556
35°	854	858	916	977	1047	531
45°	512	522	556	598	653	399
55°	294	307	324	337	364	267
65°	148	160	174	152	138	153
75°	74	74	68	46	32	79
85°	21	21	19	12	8	23
90°	0	0	0	0	0	2
95°	16	65	292	101	62	19
105°	67	101	437	772	734	71
115°	124	150	332	702	825	122
125°	175	194	316	525	628	157
135°	214	232	313	444	501	165
145°	252	265	315	384	418	158
155°	288	295	323	347	361	133
165°	318	320	326	334	338	90
175°	333	332	330	328	326	32
180°	331	331	331	331	331	



TEST NUMBER: P521723

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (5700K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1900.9	1900.9	1900.9	1900.9	1900.9
2.5°	1905.5	1888.6	1892.8	1892.7	1887.5
5°	1870.0	1851.2	1863.3	1867.6	1874.2
7.5°	1800.6	1786.4	1808.4	1824.8	1838.0
10°	1746.6	1734.3	1762.4	1786.1	1803.3
12.5°	1683.8	1673.6	1708.4	1740.2	1762.6
15°	1581.4	1575.7	1618.1	1662.1	1690.7
17.5°	1471.8	1469.0	1517.7	1569.1	1605.6
20°	1397.1	1396.3	1449.6	1503.1	1545.5
22.5°	1321.7	1323.5	1379.6	1435.2	1483.5
25°	1208.6	1211.8	1274.5	1330.0	1388.7
27.5°	1104.0	1105.4	1170.2	1228.8	1291.5
30°	1032.6	1036.7	1100.1	1160.8	1226.1
32.5°	961.2	965.9	1028.1	1090.8	1157.4
35°	854.1	858.2	915.8	977.4	1046.8
37.5°	743.7	749.2	800.4	858.6	926.8
40°	672.3	680.4	725.6	780.5	847.4
42.5°	603.5	613.6	655.6	707.7	768.0
45°	512.1	521.9	556.3	598.4	653.1
47.5°	433.4	444.6	471.1	507.3	554.0
50°	388.7	399.3	423.7	450.6	494.6
52.5°	349.3	359.9	381.7	402.4	439.9
55°	294.4	306.7	324.5	336.8	364.5
57.5°	249.4	261.1	275.2	280.8	297.6
60°	219.4	232.4	245.2	244.6	253.6
62.5°	192.0	203.1	215.9	207.0	207.5
65°	147.6	159.9	174.3	152.3	138.5
67.5°	119.3	121.9	136.8	106.2	89.7
70°	105.9	105.9	110.1	82.3	68.4
72.5°	93.2	93.2	89.4	66.9	52.4
75°	74.2	74.2	67.6	46.4	31.7
77.5°	57.2	56.6	51.7	34.6	23.0
80°	45.9	45.9	41.7	27.3	18.3
82.5°	35.9	35.9	32.4	21.3	13.7
85°	20.9	20.9	19.2	12.4	7.5
87.5°	7.3	7.3	6.7	4.0	3.3
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.0	26.7	61.9	18.0	13.6
95°	16.4	64.9	291.8	101.0	62.3
97.5°	30.1	76.1	449.5	321.6	220.4
100°	39.6	82.7	483.7	489.9	377.4
102.5°	50.2	89.8	476.1	627.1	528.8
105°	66.7	101.1	437.1	772.1	734.0
107.5°	83.4	114.3	391.6	813.0	847.0
110°	95.0	123.9	365.4	797.4	873.6

TEST NUMBER: P521723

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (5700K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	106.0	133.5	347.8	760.4	869.1
115°	123.9	149.7	331.5	702.2	824.6
117.5°	139.6	163.9	321.8	638.6	768.2
120°	152.2	172.5	320.8	602.2	726.4
122.5°	162.3	182.6	318.3	570.3	685.7
125°	174.8	193.9	316.4	525.0	627.7
127.5°	188.6	206.4	315.4	497.9	582.5
130°	195.6	213.4	313.8	479.1	552.9
132.5°	203.2	220.5	313.8	464.3	532.2
135°	213.8	231.7	312.6	443.5	501.3
137.5°	223.9	241.3	312.5	425.8	475.7
140°	231.5	249.3	312.0	411.2	459.1
142.5°	240.0	254.9	313.5	399.5	442.5
145°	252.2	265.1	315.1	383.8	418.3
147.5°	262.7	275.2	317.9	368.0	397.8
150°	271.7	280.3	318.9	362.8	383.7
152.5°	278.8	287.9	319.9	355.7	375.1
155°	288.1	294.8	322.7	346.9	361.0
157.5°	299.6	303.7	323.3	342.9	353.0
160°	305.7	308.7	325.8	339.8	348.4
162.5°	309.2	312.8	326.3	337.3	343.9
165°	318.3	319.5	326.4	333.5	338.4
167.5°	324.4	323.3	329.3	332.5	334.5
170°	326.4	325.8	328.3	329.0	331.5
172.5°	331.0	328.9	329.8	328.0	329.9
175°	333.3	331.5	330.2	328.3	325.8
177.5°	334.4	331.4	329.8	327.8	328.3
180°	330.8	330.8	330.8	330.8	330.8

(END OF REPORT)