

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521720

Luminaire Tested: **SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521720
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (4000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4630.4 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521720
CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (4000K)

Luminous Intensity Polar Plot





TEST NUMBER: P521720

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (4000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57		
1	101	97	93	90	94	91	88	85	79	76	75	68	66	65	58	57	56	51		
2	93	86	81	76	86	81	76	72	71	67	64	61	59	56	52	51	49	45		
3	86	77	70	65	80	72	67	62	64	59	55	55	52	49	48	45	43	40		
4	79	69	62	56	74	65	59	54	57	52	49	50	47	44	44	41	39	35		
5	73	62	55	49	68	59	52	47	52	47	43	46	42	39	40	37	35	32		
6	68	57	49	44	63	54	47	42	48	42	38	42	38	35	37	34	31	29		
7	63	52	44	39	59	49	42	38	44	38	34	39	35	31	34	31	28	26		
8	59	47	40	35	55	45	38	34	40	35	31	36	32	29	32	28	26	24		
9	55	44	37	32	52	42	35	31	37	32	28	33	29	26	30	26	24	22		
10	52	40	34	29	49	38	32	28	35	30	26	31	27	24	28	24	22	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16830	16830	16830
5°	16621	16561	16658
10°	15703	15845	16213
15°	14497	14833	15498
20°	13164	13659	14563
25°	11808	12451	13567
30°	10558	11248	12536
35°	9232	9899	11315
40°	7771	8387	9795
45°	6413	6966	8178
50°	5354	5836	6814
55°	4546	5009	5627
60°	3884	4342	4489
65°	3093	3652	2901
70°	2743	2851	1770
75°	2538	2310	1084
80°	2338	2125	935
85°	2117	1948	762



TEST NUMBER: P521720

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (4000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.3	3.6
10°-20°	435.2	9.4
20°-30°	563.7	12.2
30°-40°	552.0	11.9
40°-50°	422.6	9.1
50°-60°	281.6	6.1
60°-70°	153.7	3.3
70°-80°	64.0	1.4
80°-90°	18.1	0.4
90°-100°	144.7	3.1
100°-110°	411.6	8.9
110°-120°	394.4	8.5
120°-130°	312.1	6.7
130°-140°	250.5	5.4
140°-150°	196.1	4.2
150°-160°	143.5	3.1
160°-170°	88.9	1.9
170°-180°	30.2	0.7
0°-30°	1166.3	25.2
0°-40°	1718.3	37.1
0°-60°	2422.4	52.3
0°-90°	2658.2	57.4
90°-120°	950.7	20.5
90°-150°	1709.6	36.9
90°-180°	1972.0	42.6
0°-180°	4630.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1824	1824	1824	1824	1824	
5°	1795	1777	1788	1792	1799	167
15°	1518	1512	1553	1595	1622	424
25°	1160	1163	1223	1276	1333	533
35°	820	824	879	938	1005	510
45°	492	501	534	574	627	383
55°	283	294	311	323	350	256
65°	142	153	167	146	133	147
75°	71	71	65	44	30	76
85°	20	20	18	12	7	22
90°	0	0	0	0	0	2
95°	16	62	280	97	60	18
105°	64	97	420	741	704	68
115°	119	144	318	674	791	117
125°	168	186	304	504	602	150
135°	205	222	300	426	481	158
145°	242	254	302	368	401	151
155°	276	283	310	333	346	128
165°	305	307	313	320	325	86
175°	320	318	317	315	313	30
180°	318	318	318	318	318	



TEST NUMBER: P521720

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1824.2	1824.2	1824.2	1824.2	1824.2
2.5°	1828.7	1812.4	1816.5	1816.4	1811.4
5°	1794.6	1776.6	1788.2	1792.3	1798.6
7.5°	1728.0	1714.4	1735.5	1751.2	1763.9
10°	1676.1	1664.4	1691.3	1714.1	1730.6
12.5°	1615.9	1606.1	1639.5	1670.1	1691.5
15°	1517.7	1512.2	1552.9	1595.1	1622.5
17.5°	1412.5	1409.8	1456.5	1505.8	1540.9
20°	1340.8	1340.0	1391.2	1442.5	1483.2
22.5°	1268.4	1270.1	1323.9	1377.3	1423.7
25°	1159.9	1163.0	1223.1	1276.4	1332.7
27.5°	1059.5	1060.9	1123.0	1179.3	1239.4
30°	991.0	994.9	1055.8	1114.0	1176.7
32.5°	922.4	927.0	986.6	1046.8	1110.7
35°	819.7	823.6	878.9	938.0	1004.6
37.5°	713.7	719.0	768.1	824.0	889.5
40°	645.2	653.0	696.4	749.1	813.3
42.5°	579.2	588.9	629.2	679.1	737.1
45°	491.5	500.9	533.9	574.3	626.8
47.5°	415.9	426.7	452.1	486.9	531.7
50°	373.0	383.2	406.6	432.4	474.7
52.5°	335.2	345.4	366.3	386.2	422.2
55°	282.6	294.3	311.4	323.2	349.8
57.5°	239.3	250.6	264.1	269.5	285.6
60°	210.5	223.0	235.3	234.7	243.3
62.5°	184.3	194.9	207.2	198.7	199.2
65°	141.7	153.4	167.3	146.2	132.9
67.5°	114.5	117.0	131.3	101.9	86.1
70°	101.7	101.7	105.7	78.9	65.6
72.5°	89.5	89.5	85.8	64.2	50.3
75°	71.2	71.2	64.8	44.5	30.4
77.5°	54.9	54.3	49.6	33.2	22.1
80°	44.0	44.0	40.0	26.2	17.6
82.5°	34.4	34.4	31.1	20.5	13.1
85°	20.0	20.0	18.4	11.9	7.2
87.5°	7.0	7.0	6.4	3.8	3.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.8	25.6	59.4	17.3	13.0
95°	15.7	62.3	280.1	96.9	59.8
97.5°	28.9	73.0	431.3	308.6	211.5
100°	38.0	79.3	464.2	470.2	362.2
102.5°	48.2	86.2	456.9	601.8	507.5
105°	64.0	97.0	419.5	741.0	704.4
107.5°	80.0	109.7	375.8	780.2	812.8
110°	91.1	118.9	350.7	765.2	838.4

TEST NUMBER: P521720

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	<i>101.8</i>	128.1	333.8	729.7	834.1
115°	<i>118.9</i>	143.7	318.1	673.9	791.3
117.5°	<i>134.0</i>	157.3	308.8	612.8	737.2
120°	<i>146.1</i>	165.5	307.8	577.9	697.2
122.5°	<i>155.7</i>	175.2	305.4	547.3	658.0
125°	<i>167.8</i>	186.1	303.6	503.8	602.4
127.5°	<i>181.0</i>	198.1	302.6	477.8	559.1
130°	<i>187.7</i>	204.8	301.2	459.7	530.6
132.5°	<i>195.0</i>	211.6	301.2	445.6	510.8
135°	<i>205.2</i>	222.3	300.0	425.6	481.1
137.5°	<i>214.9</i>	231.5	299.9	408.6	456.6
140°	<i>222.1</i>	239.2	299.4	394.6	440.6
142.5°	<i>230.3</i>	244.6	300.8	383.4	424.7
145°	<i>242.0</i>	254.4	302.4	368.3	401.4
147.5°	<i>252.1</i>	264.1	305.1	353.2	381.7
150°	<i>260.8</i>	269.0	306.0	348.1	368.2
152.5°	<i>267.5</i>	276.2	307.0	341.3	360.0
155°	<i>276.4</i>	282.9	309.6	332.9	346.5
157.5°	<i>287.6</i>	291.4	310.2	329.1	338.7
160°	<i>293.3</i>	296.3	312.7	326.1	334.4
162.5°	<i>296.7</i>	300.2	313.1	323.7	330.0
165°	<i>305.4</i>	306.6	313.3	320.0	324.7
167.5°	<i>311.3</i>	310.3	316.0	319.1	321.0
170°	<i>313.3</i>	312.7	315.1	315.7	318.1
172.5°	<i>317.6</i>	315.6	316.5	314.8	316.6
175°	<i>319.9</i>	318.1	316.9	315.0	312.7
177.5°	<i>320.9</i>	318.0	316.5	314.6	315.1
180°	<i>317.5</i>	317.5	317.5	317.5	317.5

(END OF REPORT)