

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521724

Luminaire Tested: **SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (6500K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521724
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (6500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 6500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4870.7 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 45.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521724

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (6500K)

Luminous Intensity Polar Plot





TEST NUMBER: P521724

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (6500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57		
1	101	97	93	90	94	91	88	85	79	76	75	68	66	65	58	57	56	51		
2	93	86	81	76	86	81	76	72	71	67	64	61	59	56	52	51	49	45		
3	86	77	70	65	80	72	67	62	64	59	55	55	52	49	48	45	43	40		
4	79	69	62	56	74	65	59	54	57	52	49	50	47	44	44	41	39	35		
5	73	62	55	49	68	59	52	47	52	47	43	46	42	39	40	37	35	32		
6	68	57	49	44	63	54	47	42	48	42	38	42	38	35	37	34	31	29		
7	63	52	44	39	59	49	42	38	44	38	34	39	35	31	34	31	28	26		
8	59	47	40	35	55	45	38	34	40	35	31	36	32	29	32	28	26	24		
9	55	44	37	32	52	42	35	31	37	32	28	33	29	26	30	26	24	22		
10	52	40	34	29	49	38	32	28	35	30	26	31	27	24	28	24	22	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17704	17704	17704
5°	17483	17421	17522
10°	16518	16668	17054
15°	15248	15602	16302
20°	13847	14368	15319
25°	12420	13098	14271
30°	11105	11832	13186
35°	9711	10413	11902
40°	8173	8822	10304
45°	6746	7328	8602
50°	5632	6139	7167
55°	4781	5268	5918
60°	4085	4567	4724
65°	3253	3842	3052
70°	2884	2997	1861
75°	2670	2431	1141
80°	2460	2237	983
85°	2223	2054	805



TEST NUMBER: P521724

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (6500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.0	3.6
10°-20°	457.8	9.4
20°-30°	593.0	12.2
30°-40°	580.7	11.9
40°-50°	444.5	9.1
50°-60°	296.2	6.1
60°-70°	161.6	3.3
70°-80°	67.3	1.4
80°-90°	19.1	0.4
90°-100°	152.2	3.1
100°-110°	433.0	8.9
110°-120°	414.9	8.5
120°-130°	328.4	6.7
130°-140°	263.6	5.4
140°-150°	206.3	4.2
150°-160°	151.0	3.1
160°-170°	93.5	1.9
170°-180°	31.7	0.7
0°-30°	1226.8	25.2
0°-40°	1807.5	37.1
0°-60°	2548.1	52.3
0°-90°	2796.1	57.4
90°-120°	1000.1	20.5
90°-150°	1798.3	36.9
90°-180°	2075.0	42.6
0°-180°	4870.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1919	1919	1919	1919	1919	
5°	1888	1869	1881	1885	1892	176
15°	1596	1591	1633	1678	1707	446
25°	1220	1223	1287	1343	1402	561
35°	862	866	924	987	1057	536
45°	517	527	562	604	659	403
55°	297	310	328	340	368	269
65°	149	161	176	154	140	155
75°	75	75	68	47	32	80
85°	21	21	19	12	8	23
90°	0	0	0	0	0	2
95°	16	66	295	102	63	19
105°	67	102	441	779	741	71
115°	125	151	335	709	832	123
125°	176	196	319	530	634	158
135°	216	234	316	448	506	167
145°	255	268	318	388	422	159
155°	291	298	326	350	364	134
165°	321	322	330	337	342	90
175°	336	335	333	331	329	32
180°	334	334	334	334	334	

TEST NUMBER: P521724

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1918.9	1918.9	1918.9	1918.9	1918.9
2.5°	1923.6	1906.5	1910.8	1910.7	1905.4
5°	1887.7	1868.8	1881.0	1885.4	1891.9
7.5°	1817.7	1803.3	1825.6	1842.1	1855.4
10°	1763.1	1750.8	1779.1	1803.1	1820.4
12.5°	1699.8	1689.4	1724.6	1756.7	1779.3
15°	1596.4	1590.6	1633.4	1677.9	1706.7
17.5°	1485.8	1483.0	1532.1	1583.9	1620.8
20°	1410.3	1409.5	1463.4	1517.4	1560.2
22.5°	1334.2	1336.0	1392.6	1448.8	1497.6
25°	1220.0	1223.3	1286.6	1342.6	1401.9
27.5°	1114.4	1115.9	1181.3	1240.5	1303.7
30°	1042.4	1046.5	1110.6	1171.9	1237.7
32.5°	970.3	975.1	1037.8	1101.2	1168.3
35°	862.2	866.3	924.5	986.7	1056.7
37.5°	750.7	756.3	808.0	866.8	935.6
40°	678.6	686.9	732.5	787.9	855.5
42.5°	609.3	619.5	661.8	714.4	775.3
45°	517.0	526.9	561.6	604.1	659.3
47.5°	437.5	448.9	475.6	512.2	559.2
50°	392.4	403.1	427.7	454.8	499.3
52.5°	352.6	363.3	385.3	406.2	444.1
55°	297.2	309.6	327.5	340.0	367.9
57.5°	251.8	263.6	277.9	283.5	300.4
60°	221.4	234.6	247.5	246.9	256.0
62.5°	193.8	205.0	217.9	209.0	209.5
65°	149.0	161.4	176.0	153.8	139.8
67.5°	120.4	123.0	138.1	107.2	90.6
70°	106.9	106.9	111.1	83.0	69.0
72.5°	94.1	94.1	90.3	67.5	52.9
75°	74.9	74.9	68.2	46.8	32.0
77.5°	57.8	57.1	52.2	34.9	23.2
80°	46.3	46.3	42.1	27.6	18.5
82.5°	36.2	36.2	32.7	21.5	13.8
85°	21.0	21.0	19.4	12.5	7.6
87.5°	7.4	7.4	6.7	4.0	3.4
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.1	26.9	62.5	18.2	13.7
95°	16.5	65.6	294.6	102.0	62.9
97.5°	30.3	76.8	453.7	324.7	222.5
100°	40.0	83.5	488.3	494.6	381.0
102.5°	50.7	90.6	480.6	633.0	533.8
105°	67.3	102.1	441.3	779.4	740.9
107.5°	84.2	115.4	395.3	820.7	855.0
110°	95.9	125.1	368.9	804.9	881.9

TEST NUMBER: P521724

CATALOG NUMBER: SQ4-WB-025U-075D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	107.0	134.7	351.1	767.6	877.3
115°	125.1	151.2	334.6	708.8	832.4
117.5°	141.0	165.4	324.8	644.6	775.5
120°	153.7	174.1	323.8	607.9	733.3
122.5°	163.8	184.3	321.3	575.7	692.2
125°	176.5	195.8	319.4	530.0	633.6
127.5°	190.3	208.4	318.3	502.6	588.1
130°	197.5	215.5	316.8	483.6	558.1
132.5°	205.1	222.6	316.8	468.7	537.3
135°	215.9	233.9	315.6	447.7	506.0
137.5°	226.0	243.5	315.4	429.8	480.3
140°	233.7	251.7	314.9	415.1	463.5
142.5°	242.3	257.3	316.4	403.3	446.7
145°	254.6	267.6	318.1	387.5	422.2
147.5°	265.1	277.8	320.9	371.5	401.5
150°	274.3	283.0	321.9	366.2	387.3
152.5°	281.4	290.6	322.9	359.0	378.7
155°	290.8	297.6	325.7	350.2	364.4
157.5°	302.5	306.6	326.3	346.1	356.3
160°	308.6	311.7	328.9	343.1	351.7
162.5°	312.1	315.7	329.4	340.5	347.2
165°	321.3	322.5	329.5	336.6	341.6
167.5°	327.5	326.4	332.4	335.7	337.6
170°	329.5	328.9	331.4	332.1	334.6
172.5°	334.1	332.0	333.0	331.1	333.1
175°	336.5	334.6	333.3	331.4	328.9
177.5°	337.5	334.5	333.0	330.9	331.4
180°	334.0	334.0	334.0	334.0	334.0

(END OF REPORT)