

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521733

Luminaire Tested: **SQ4-WB-025U-100D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521733
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-025U-100D-92765-1D-UNV-STD-W-4 (4000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5466.5 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 56.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521733

CATALOG NUMBER: SQ4-WB-025U-100D-92765-1D-UNV-STD-W-4 (4000K)

Luminous Intensity Polar Plot





TEST NUMBER: P521733

CATALOG NUMBER: SQ4-WB-025U-100D-92765-1D-UNV-STD-W-4 (4000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	110	110	110	110	104	104	104	104	91	91	91	80	80	80	69	69	69	64		
1	102	98	95	92	96	93	90	87	82	80	78	72	71	69	63	62	61	57		
2	94	88	82	78	89	83	78	74	74	70	67	65	63	60	57	56	54	50		
3	87	79	72	67	82	74	69	64	66	62	58	59	56	53	52	50	48	44		
4	81	71	63	58	76	67	61	56	60	55	51	54	50	47	48	45	42	39		
5	75	64	56	51	70	61	54	49	55	49	45	49	45	42	44	41	38	35		
6	69	58	51	45	65	55	49	44	50	45	40	45	41	37	41	37	34	32		
7	65	53	46	40	61	51	44	39	46	41	36	42	37	34	38	34	31	29		
8	60	49	42	37	57	47	40	35	43	37	33	39	34	31	35	31	29	27		
9	57	45	38	33	54	43	37	32	39	34	30	36	31	28	33	29	26	24		
10	53	42	35	30	50	40	34	29	37	31	28	33	29	26	31	27	24	22		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22125	22125	22125
5°	21849	21771	21898
10°	20643	20830	21313
15°	19057	19499	20373
20°	17305	17956	19144
25°	15521	16367	17835
30°	13878	14786	16479
35°	12136	13013	14874
40°	10214	11026	12876
45°	8430	9157	10750
50°	7037	7672	8957
55°	5974	6584	7396
60°	5106	5709	5903
65°	4065	4801	3814
70°	3604	3747	2328
75°	3337	3037	1426
80°	3076	2795	1227
85°	2784	2562	1006



TEST NUMBER: P521733

CATALOG NUMBER: SQ4-WB-025U-100D-92765-1D-UNV-STD-W-4 (4000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.0	4.0
10°-20°	572.1	10.5
20°-30°	741.1	13.6
30°-40°	725.7	13.3
40°-50°	555.5	10.2
50°-60°	370.1	6.8
60°-70°	202.0	3.7
70°-80°	84.2	1.5
80°-90°	23.8	0.4
90°-100°	144.7	2.6
100°-110°	411.6	7.5
110°-120°	394.4	7.2
120°-130°	312.1	5.7
130°-140°	250.5	4.6
140°-150°	196.1	3.6
150°-160°	143.5	2.6
160°-170°	88.9	1.6
170°-180°	30.2	0.6
0°-30°	1533.2	28.0
0°-40°	2258.8	41.3
0°-60°	3184.4	58.3
0°-90°	3494.4	63.9
90°-120°	950.7	17.4
90°-150°	1709.6	31.3
90°-180°	1972.0	36.1
0°-180°	5466.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2398	2398	2398	2398	2398	
5°	2359	2336	2351	2356	2364	219
15°	1995	1988	2041	2097	2133	557
25°	1525	1529	1608	1678	1752	701
35°	1078	1083	1155	1233	1321	670
45°	646	658	702	755	824	504
55°	371	387	409	425	460	337
65°	186	202	220	192	175	194
75°	94	94	85	58	40	100
85°	26	26	24	16	10	29
90°	0	0	0	0	0	2
95°	16	62	280	97	60	18
105°	64	97	420	741	704	68
115°	119	144	318	674	791	117
125°	168	186	304	504	602	150
135°	205	222	300	426	481	158
145°	242	254	302	368	401	151
155°	276	283	310	333	346	128
165°	305	307	313	320	325	86
175°	320	318	317	315	313	30
180°	318	318	318	318	318	

TEST NUMBER: P521733

CATALOG NUMBER: SQ4-WB-025U-100D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2398.1	2398.1	2398.1	2398.1	2398.1
2.5°	2404.0	2382.6	2388.0	2387.8	2381.2
5°	2359.1	2335.5	2350.7	2356.2	2364.4
7.5°	2271.6	2253.7	2281.5	2302.1	2318.7
10°	2203.4	2188.0	2223.4	2253.4	2275.0
12.5°	2124.3	2111.3	2155.2	2195.4	2223.6
15°	1995.1	1987.9	2041.4	2096.9	2132.9
17.5°	1856.8	1853.3	1914.7	1979.5	2025.6
20°	1762.5	1761.5	1828.8	1896.3	1949.8
22.5°	1667.4	1669.7	1740.4	1810.6	1871.5
25°	1524.7	1528.8	1607.8	1677.9	1752.0
27.5°	1392.8	1394.6	1476.3	1550.3	1629.3
30°	1302.7	1307.8	1387.9	1464.5	1546.8
32.5°	1212.6	1218.6	1297.0	1376.1	1460.1
35°	1077.5	1082.6	1155.4	1233.1	1320.6
37.5°	938.2	945.2	1009.7	1083.2	1169.3
40°	848.1	858.4	915.5	984.7	1069.1
42.5°	761.4	774.2	827.1	892.8	968.9
45°	646.1	658.4	701.8	755.0	823.9
47.5°	546.7	560.9	594.3	640.1	698.9
50°	490.3	503.7	534.5	568.4	624.0
52.5°	440.7	454.1	481.5	507.6	555.0
55°	371.4	386.9	409.3	424.9	459.8
57.5°	314.6	329.4	347.2	354.2	375.4
60°	276.7	293.2	309.4	308.6	319.9
62.5°	242.2	256.2	272.3	261.2	261.8
65°	186.2	201.7	219.9	192.2	174.7
67.5°	150.5	153.8	172.6	134.0	113.2
70°	133.6	133.6	138.9	103.8	86.3
72.5°	117.6	117.6	112.8	84.4	66.1
75°	93.6	93.6	85.2	58.5	40.0
77.5°	72.2	71.4	65.2	43.7	29.0
80°	57.9	57.9	52.6	34.5	23.1
82.5°	45.2	45.2	40.8	26.9	17.3
85°	26.3	26.3	24.2	15.6	9.5
87.5°	9.3	9.3	8.4	5.0	4.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.8	25.6	59.4	17.3	13.0
95°	15.7	62.3	280.1	96.9	59.8
97.5°	28.9	73.0	431.3	308.6	211.5
100°	38.0	79.3	464.2	470.2	362.2
102.5°	48.2	86.2	456.9	601.8	507.5
105°	64.0	97.0	419.5	741.0	704.4
107.5°	80.0	109.7	375.8	780.2	812.8
110°	91.1	118.9	350.7	765.2	838.4

TEST NUMBER: P521733

CATALOG NUMBER: SQ4-WB-025U-100D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	101.8	128.1	333.8	729.7	834.1
115°	118.9	143.7	318.1	673.9	791.3
117.5°	134.0	157.3	308.8	612.8	737.2
120°	146.1	165.5	307.8	577.9	697.2
122.5°	155.7	175.2	305.4	547.3	658.0
125°	167.8	186.1	303.6	503.8	602.4
127.5°	181.0	198.1	302.6	477.8	559.1
130°	187.7	204.8	301.2	459.7	530.6
132.5°	195.0	211.6	301.2	445.6	510.8
135°	205.2	222.3	300.0	425.6	481.1
137.5°	214.9	231.5	299.9	408.6	456.6
140°	222.1	239.2	299.4	394.6	440.6
142.5°	230.3	244.6	300.8	383.4	424.7
145°	242.0	254.4	302.4	368.3	401.4
147.5°	252.1	264.1	305.1	353.2	381.7
150°	260.8	269.0	306.0	348.1	368.2
152.5°	267.5	276.2	307.0	341.3	360.0
155°	276.4	282.9	309.6	332.9	346.5
157.5°	287.6	291.4	310.2	329.1	338.7
160°	293.3	296.3	312.7	326.1	334.4
162.5°	296.7	300.2	313.1	323.7	330.0
165°	305.4	306.6	313.3	320.0	324.7
167.5°	311.3	310.3	316.0	319.1	321.0
170°	313.3	312.7	315.1	315.7	318.1
172.5°	317.6	315.6	316.5	314.8	316.6
175°	319.9	318.1	316.9	315.0	312.7
177.5°	320.9	318.0	316.5	314.6	315.1
180°	317.5	317.5	317.5	317.5	317.5

(END OF REPORT)