

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521736

Luminaire Tested: **SQ4-WB-025U-100D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521736
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-025U-100D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5696.3 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 56.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521736

CATALOG NUMBER: SQ4-WB-025U-100D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P521736

CATALOG NUMBER: SQ4-WB-025U-100D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	104	104	104	104	91	91	91	80	80	80	69	69	69	64				
1	102	98	95	92	96	93	90	87	82	80	78	72	71	69	63	62	61	57				
2	94	88	82	78	89	83	78	74	74	70	67	65	63	60	57	56	54	50				
3	87	79	72	67	82	74	69	64	66	62	58	59	56	53	52	50	48	44				
4	81	71	63	58	76	67	61	56	60	55	51	54	50	47	48	45	42	39				
5	75	64	56	51	70	61	54	49	55	49	45	49	45	42	44	41	38	35				
6	69	58	51	45	65	55	49	44	50	45	40	45	41	37	41	37	34	32				
7	65	53	46	40	61	51	44	39	46	41	36	42	37	34	38	34	31	29				
8	60	49	42	37	57	47	40	35	43	37	33	39	34	31	35	31	29	27				
9	57	45	38	33	54	43	37	32	39	34	30	36	31	28	33	29	26	24				
10	53	42	35	30	50	40	34	29	37	31	28	33	29	26	31	27	24	22				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23054	23054	23054
5°	22766	22686	22817
10°	21510	21705	22208
15°	19857	20317	21229
20°	18032	18710	19948
25°	16174	17056	18585
30°	14461	15407	17171
35°	12646	13560	15498
40°	10643	11489	13417
45°	8784	9542	11202
50°	7333	7995	9333
55°	6225	6860	7707
60°	5322	5949	6150
65°	4237	5004	3973
70°	3755	3903	2425
75°	3479	3165	1486
80°	3204	2912	1280
85°	2901	2668	1048



TEST NUMBER: P521736

CATALOG NUMBER: SQ4-WB-025U-100D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	229.2	4.0
10°-20°	596.2	10.5
20°-30°	772.2	13.6
30°-40°	756.2	13.3
40°-50°	578.8	10.2
50°-60°	385.7	6.8
60°-70°	210.5	3.7
70°-80°	87.7	1.5
80°-90°	24.8	0.4
90°-100°	150.8	2.6
100°-110°	428.9	7.5
110°-120°	411.0	7.2
120°-130°	325.3	5.7
130°-140°	261.1	4.6
140°-150°	204.4	3.6
150°-160°	149.6	2.6
160°-170°	92.6	1.6
170°-180°	31.4	0.6
0°-30°	1597.6	28.0
0°-40°	2353.7	41.3
0°-60°	3318.2	58.3
0°-90°	3641.2	63.9
90°-120°	990.7	17.4
90°-150°	1781.4	31.3
90°-180°	2055.0	36.1
0°-180°	5696.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2499	2499	2499	2499	2499	
5°	2458	2434	2450	2455	2464	229
15°	2079	2071	2127	2185	2222	581
25°	1589	1593	1675	1748	1826	731
35°	1123	1128	1204	1285	1376	698
45°	673	686	731	787	858	525
55°	387	403	426	443	479	351
65°	194	210	229	200	182	202
75°	98	98	89	61	42	104
85°	27	27	25	16	10	30
90°	0	0	0	0	0	2
95°	16	65	292	101	62	19
105°	67	101	437	772	734	71
115°	124	150	332	702	825	122
125°	175	194	316	525	628	157
135°	214	232	313	444	501	165
145°	252	265	315	384	418	158
155°	288	295	323	347	361	133
165°	318	320	326	334	338	90
175°	333	332	330	328	326	32
180°	331	331	331	331	331	

TEST NUMBER: P521736

CATALOG NUMBER: SQ4-WB-025U-100D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2498.8	2498.8	2498.8	2498.8	2498.8
2.5°	2504.9	2482.7	2488.3	2488.1	2481.3
5°	2458.2	2433.6	2449.5	2455.1	2463.7
7.5°	2367.0	2348.4	2377.3	2398.8	2416.1
10°	2296.0	2279.9	2316.8	2348.0	2370.5
12.5°	2213.5	2200.0	2245.7	2287.6	2317.0
15°	2078.9	2071.4	2127.1	2185.0	2222.5
17.5°	1934.8	1931.2	1995.1	2062.6	2110.7
20°	1836.6	1835.5	1905.6	1976.0	2031.7
22.5°	1737.4	1739.8	1813.5	1886.7	1950.1
25°	1588.8	1593.0	1675.4	1748.4	1825.6
27.5°	1451.3	1453.2	1538.3	1615.4	1697.7
30°	1357.4	1362.8	1446.2	1526.0	1611.8
32.5°	1263.5	1269.8	1351.5	1434.0	1521.4
35°	1122.8	1128.1	1203.9	1284.9	1376.0
37.5°	977.6	984.9	1052.2	1128.7	1218.4
40°	883.7	894.5	953.9	1026.1	1114.0
42.5°	793.4	806.7	861.8	930.3	1009.6
45°	673.2	686.1	731.3	786.7	858.5
47.5°	569.7	584.5	619.3	666.9	728.3
50°	510.9	524.9	557.0	592.3	650.2
52.5°	459.2	473.1	501.7	529.0	578.3
55°	387.0	403.1	426.5	442.7	479.1
57.5°	327.8	343.3	361.8	369.1	391.2
60°	288.4	305.5	322.4	321.5	333.3
62.5°	252.4	267.0	283.8	272.2	272.8
65°	194.1	210.2	229.2	200.2	182.0
67.5°	156.8	160.2	179.8	139.6	118.0
70°	139.2	139.2	144.7	108.1	89.9
72.5°	122.6	122.6	117.5	87.9	68.9
75°	97.6	97.6	88.8	61.0	41.7
77.5°	75.2	74.4	68.0	45.5	30.3
80°	60.3	60.3	54.8	35.9	24.1
82.5°	47.1	47.1	42.5	28.1	18.0
85°	27.4	27.4	25.2	16.3	9.9
87.5°	9.6	9.6	8.8	5.2	4.4
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.0	26.7	61.9	18.0	13.6
95°	16.4	64.9	291.8	101.0	62.3
97.5°	30.1	76.1	449.5	321.6	220.4
100°	39.6	82.7	483.7	489.9	377.4
102.5°	50.2	89.8	476.1	627.1	528.8
105°	66.7	101.1	437.1	772.1	734.0
107.5°	83.4	114.3	391.6	813.0	847.0
110°	95.0	123.9	365.4	797.4	873.6

TEST NUMBER: P521736

CATALOG NUMBER: SQ4-WB-025U-100D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	106.0	133.5	347.8	760.4	869.1
115°	123.9	149.7	331.5	702.2	824.6
117.5°	139.6	163.9	321.8	638.6	768.2
120°	152.2	172.5	320.8	602.2	726.4
122.5°	162.3	182.6	318.3	570.3	685.7
125°	174.8	193.9	316.4	525.0	627.7
127.5°	188.6	206.4	315.4	497.9	582.5
130°	195.6	213.4	313.8	479.1	552.9
132.5°	203.2	220.5	313.8	464.3	532.2
135°	213.8	231.7	312.6	443.5	501.3
137.5°	223.9	241.3	312.5	425.8	475.7
140°	231.5	249.3	312.0	411.2	459.1
142.5°	240.0	254.9	313.5	399.5	442.5
145°	252.2	265.1	315.1	383.8	418.3
147.5°	262.7	275.2	317.9	368.0	397.8
150°	271.7	280.3	318.9	362.8	383.7
152.5°	278.8	287.9	319.9	355.7	375.1
155°	288.1	294.8	322.7	346.9	361.0
157.5°	299.6	303.7	323.3	342.9	353.0
160°	305.7	308.7	325.8	339.8	348.4
162.5°	309.2	312.8	326.3	337.3	343.9
165°	318.3	319.5	326.4	333.5	338.4
167.5°	324.4	323.3	329.3	332.5	334.5
170°	326.4	325.8	328.3	329.0	331.5
172.5°	331.0	328.9	329.8	328.0	329.9
175°	333.3	331.5	330.2	328.3	325.8
177.5°	334.4	331.4	329.8	327.8	328.3
180°	330.8	330.8	330.8	330.8	330.8

(END OF REPORT)