

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521744

Luminaire Tested: **SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521744
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (3000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6134.2 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 69.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521744

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (3000K)

Luminous Intensity Polar Plot





TEST NUMBER: P521744

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (3000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74	69				
1	104	100	96	93	98	95	92	89	85	83	81	76	74	73	68	66	65	61				
2	96	89	84	79	90	85	80	76	76	73	69	69	66	63	62	59	58	54				
3	88	80	73	68	84	76	70	65	69	64	60	62	59	56	56	53	51	48				
4	82	72	65	59	77	69	62	57	62	57	53	57	53	49	51	48	45	43				
5	76	65	58	52	72	62	56	50	57	51	47	52	47	44	47	44	41	38				
6	71	59	52	46	67	57	50	45	52	46	42	48	43	40	44	40	37	35				
7	66	54	47	42	63	52	45	40	48	42	38	44	39	36	40	36	34	31				
8	62	50	43	38	59	48	41	37	44	39	35	41	36	33	37	34	31	29				
9	58	46	39	34	55	44	38	33	41	36	32	38	33	30	35	31	28	26				
10	54	43	36	31	52	41	35	31	38	33	29	35	31	28	33	29	26	24				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26864	26864	26864
5°	26528	26434	26588
10°	25065	25291	25878
15°	23138	23675	24737
20°	21011	21802	23244
25°	18846	19873	21656
30°	16851	17953	20008
35°	14736	15800	18059
40°	12403	13387	15634
45°	10236	11119	13053
50°	8546	9315	10874
55°	7255	7994	8980
60°	6200	6931	7167
65°	4936	5829	4630
70°	4378	4548	2827
75°	4053	3689	1729
80°	3735	3395	1493
85°	3377	3112	1217



TEST NUMBER: P521744

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (3000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.1	4.4
10°-20°	694.7	11.3
20°-30°	899.8	14.7
30°-40°	881.1	14.4
40°-50°	674.5	11.0
50°-60°	449.4	7.3
60°-70°	245.2	4.0
70°-80°	102.2	1.7
80°-90°	28.9	0.5
90°-100°	138.8	2.3
100°-110°	394.8	6.4
110°-120°	378.2	6.2
120°-130°	299.4	4.9
130°-140°	240.3	3.9
140°-150°	188.1	3.1
150°-160°	137.6	2.2
160°-170°	85.3	1.4
170°-180°	28.9	0.5
0°-30°	1861.5	30.3
0°-40°	2742.7	44.7
0°-60°	3866.5	63.0
0°-90°	4242.9	69.2
90°-120°	911.8	14.9
90°-150°	1639.5	26.7
90°-180°	1891.0	30.8
0°-180°	6134.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2912	2912	2912	2912	2912	
5°	2864	2836	2854	2861	2871	266
15°	2422	2414	2479	2546	2590	676
25°	1851	1856	1952	2037	2127	851
35°	1308	1314	1403	1497	1603	813
45°	784	800	852	917	1000	612
55°	451	470	497	516	558	409
65°	226	245	267	233	212	235
75°	114	114	104	71	48	121
85°	32	32	29	19	12	35
90°	0	0	0	0	0	2
95°	15	60	269	93	57	17
105°	61	93	402	711	676	65
115°	114	138	305	646	759	112
125°	161	178	291	483	578	144
135°	197	213	288	408	461	152
145°	232	244	290	353	385	145
155°	265	271	297	319	332	123
165°	293	294	300	307	311	82
175°	307	305	304	302	300	29
180°	304	304	304	304	304	



TEST NUMBER: P521744

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2911.7	2911.7	2911.7	2911.7	2911.7
2.5°	2918.9	2892.9	2899.4	2899.3	2891.3
5°	2864.4	2835.7	2854.2	2860.8	2870.8
7.5°	2758.1	2736.4	2770.2	2795.1	2815.4
10°	2675.4	2656.6	2699.6	2736.0	2762.2
12.5°	2579.3	2563.5	2616.8	2665.7	2699.9
15°	2422.4	2413.6	2478.6	2546.0	2589.8
17.5°	2254.5	2250.3	2324.8	2403.5	2459.4
20°	2140.0	2138.8	2220.5	2302.5	2367.4
22.5°	2024.5	2027.3	2113.2	2198.4	2272.4
25°	1851.3	1856.3	1952.2	2037.3	2127.3
27.5°	1691.1	1693.3	1792.5	1882.3	1978.3
30°	1581.7	1587.9	1685.2	1778.2	1878.1
32.5°	1472.3	1479.6	1574.8	1670.9	1772.8
35°	1308.3	1314.5	1402.8	1497.2	1603.4
37.5°	1139.1	1147.6	1226.0	1315.3	1419.7
40°	1029.8	1042.3	1111.5	1195.6	1298.1
42.5°	924.5	940.0	1004.2	1084.0	1176.4
45°	784.5	799.5	852.2	916.7	1000.4
47.5°	663.9	681.1	721.6	777.1	848.6
50°	595.4	611.6	649.0	690.2	757.6
52.5°	535.1	551.3	584.6	616.4	673.8
55°	451.0	469.7	497.0	515.8	558.3
57.5°	382.0	400.0	421.6	430.1	455.9
60°	336.0	356.0	375.6	374.7	388.4
62.5°	294.1	311.1	330.7	317.1	317.9
65°	226.1	244.9	267.0	233.3	212.1
67.5°	182.7	186.7	209.5	162.7	137.5
70°	162.3	162.3	168.6	126.0	104.8
72.5°	142.8	142.8	137.0	102.5	80.2
75°	113.7	113.7	103.5	71.0	48.5
77.5°	87.6	86.6	79.2	53.0	35.3
80°	70.3	70.3	63.9	41.8	28.1
82.5°	54.9	54.9	49.6	32.7	21.0
85°	31.9	31.9	29.4	19.0	11.5
87.5°	11.2	11.2	10.2	6.1	5.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.6	24.6	57.0	16.6	12.5
95°	15.1	59.8	268.6	93.0	57.3
97.5°	27.7	70.0	413.7	296.0	202.8
100°	36.5	76.1	445.1	450.9	347.3
102.5°	46.2	82.6	438.2	577.2	486.7
105°	61.4	93.1	402.3	710.6	675.5
107.5°	76.8	105.2	360.4	748.3	779.5
110°	87.4	114.0	336.3	733.9	804.0

TEST NUMBER: P521744

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	97.6	122.8	320.1	699.8	799.9
115°	114.0	137.8	305.1	646.3	758.9
117.5°	128.5	150.8	296.1	587.7	707.0
120°	140.1	158.8	295.2	554.3	668.6
122.5°	149.3	168.0	292.9	524.9	631.1
125°	160.9	178.5	291.2	483.2	577.7
127.5°	173.5	190.0	290.2	458.3	536.1
130°	180.0	196.4	288.9	440.9	508.8
132.5°	187.0	202.9	288.9	427.3	489.8
135°	196.8	213.2	287.7	408.2	461.4
137.5°	206.1	222.0	287.6	391.9	437.9
140°	213.0	229.4	287.1	378.4	422.6
142.5°	220.9	234.6	288.5	367.7	407.3
145°	232.1	244.0	290.0	353.2	384.9
147.5°	241.7	253.3	292.6	338.7	366.1
150°	250.1	258.0	293.5	333.9	353.1
152.5°	256.6	264.9	294.4	327.3	345.2
155°	265.1	271.3	297.0	319.3	332.3
157.5°	275.8	279.5	297.5	315.6	324.9
160°	281.3	284.2	299.9	312.8	320.7
162.5°	284.6	287.9	300.3	310.4	316.5
165°	292.9	294.0	300.4	306.9	311.4
167.5°	298.6	297.6	303.1	306.0	307.8
170°	300.4	299.9	302.2	302.8	305.1
172.5°	304.6	302.7	303.6	301.9	303.7
175°	306.8	305.1	303.9	302.1	299.9
177.5°	307.7	305.0	303.6	301.7	302.2
180°	304.5	304.5	304.5	304.5	304.5

(END OF REPORT)