

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521746

Luminaire Tested: **SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521746
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (4000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6396.3 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521746
CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (4000K)

Luminous Intensity Polar Plot





TEST NUMBER: P521746

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (4000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74	69				
1	104	100	96	93	98	95	92	89	85	83	81	76	74	73	68	66	65	61				
2	96	89	84	79	90	85	80	76	76	73	69	69	66	63	62	59	58	54				
3	88	80	73	68	84	76	70	65	69	64	60	62	59	56	56	53	51	48				
4	82	72	65	59	77	69	62	57	62	57	53	57	53	49	51	48	45	43				
5	76	65	58	52	72	62	56	50	57	51	47	52	47	44	47	44	41	38				
6	71	59	52	46	67	57	50	45	52	46	42	48	43	40	44	40	37	35				
7	66	54	47	42	63	52	45	40	48	42	38	44	39	36	40	36	34	31				
8	62	50	43	38	59	48	41	37	44	39	35	41	36	33	37	34	31	29				
9	58	46	39	34	55	44	38	33	41	36	32	38	33	30	35	31	28	26				
10	54	43	36	31	52	41	35	31	38	33	29	35	31	28	33	29	26	24				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	28012	28012	28012
5°	27662	27564	27724
10°	26135	26372	26984
15°	24127	24686	25793
20°	21910	22733	24238
25°	19651	20722	22580
30°	17571	18720	20864
35°	15365	16476	18831
40°	12933	13959	16301
45°	10673	11594	13610
50°	8911	9714	11339
55°	7565	8335	9365
60°	6466	7228	7473
65°	5148	6078	4827
70°	4564	4745	2946
75°	4228	3846	1804
80°	3895	3539	1557
85°	3525	3239	1270



TEST NUMBER: P521746

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (4000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	278.5	4.4
10°-20°	724.4	11.3
20°-30°	938.2	14.7
30°-40°	918.8	14.4
40°-50°	703.3	11.0
50°-60°	468.6	7.3
60°-70°	255.7	4.0
70°-80°	106.6	1.7
80°-90°	30.2	0.5
90°-100°	144.7	2.3
100°-110°	411.6	6.4
110°-120°	394.4	6.2
120°-130°	312.1	4.9
130°-140°	250.5	3.9
140°-150°	196.1	3.1
150°-160°	143.5	2.2
160°-170°	88.9	1.4
170°-180°	30.2	0.5
0°-30°	1941.1	30.3
0°-40°	2859.9	44.7
0°-60°	4031.7	63.0
0°-90°	4424.2	69.2
90°-120°	950.7	14.9
90°-150°	1709.6	26.7
90°-180°	1972.0	30.8
0°-180°	6396.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3036	3036	3036	3036	3036	
5°	2987	2957	2976	2983	2994	278
15°	2526	2517	2584	2655	2700	705
25°	1930	1936	2036	2124	2218	888
35°	1364	1371	1463	1561	1672	848
45°	818	834	889	956	1043	638
55°	470	490	518	538	582	426
65°	236	255	278	243	221	245
75°	119	119	108	74	51	127
85°	33	33	31	20	12	36
90°	0	0	0	0	0	2
95°	16	62	280	97	60	18
105°	64	97	420	741	704	68
115°	119	144	318	674	791	117
125°	168	186	304	504	602	150
135°	205	222	300	426	481	158
145°	242	254	302	368	401	151
155°	276	283	310	333	346	128
165°	305	307	313	320	325	86
175°	320	318	317	315	313	30
180°	318	318	318	318	318	

TEST NUMBER: P521746

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3036.1	3036.1	3036.1	3036.1	3036.1
2.5°	3043.6	3016.5	3023.3	3023.2	3014.8
5°	2986.8	2956.9	2976.2	2983.1	2993.5
7.5°	2876.0	2853.3	2888.5	2914.6	2935.7
10°	2789.7	2770.1	2815.0	2852.9	2880.3
12.5°	2689.5	2673.1	2728.7	2779.6	2815.2
15°	2525.9	2516.8	2584.5	2654.8	2700.4
17.5°	2350.8	2346.4	2424.1	2506.2	2564.5
20°	2231.5	2230.2	2315.4	2400.9	2468.6
22.5°	2111.0	2113.9	2203.5	2292.4	2369.5
25°	1930.4	1935.6	2035.6	2124.4	2218.1
27.5°	1763.3	1765.7	1869.1	1962.8	2062.8
30°	1649.3	1655.8	1757.2	1854.2	1958.4
32.5°	1535.3	1542.8	1642.1	1742.3	1848.6
35°	1364.2	1370.7	1462.8	1561.2	1671.9
37.5°	1187.8	1196.7	1278.4	1371.5	1480.4
40°	1073.8	1086.8	1159.0	1246.7	1353.5
42.5°	964.0	980.1	1047.1	1130.3	1226.7
45°	818.0	833.6	888.6	955.9	1043.1
47.5°	692.2	710.2	752.4	810.4	884.9
50°	620.8	637.7	676.8	719.7	790.0
52.5°	557.9	574.9	609.6	642.7	702.6
55°	470.3	489.8	518.2	537.9	582.2
57.5°	398.3	417.1	439.6	448.5	475.3
60°	350.4	371.2	391.7	390.7	405.0
62.5°	306.7	324.4	344.8	330.7	331.5
65°	235.8	255.3	278.4	243.3	221.1
67.5°	190.5	194.7	218.5	169.7	143.3
70°	169.2	169.2	175.9	131.4	109.2
72.5°	148.9	148.9	142.8	106.8	83.7
75°	118.6	118.6	107.9	74.1	50.6
77.5°	91.4	90.3	82.6	55.3	36.8
80°	73.3	73.3	66.6	43.6	29.3
82.5°	57.3	57.3	51.7	34.1	21.8
85°	33.3	33.3	30.6	19.8	12.0
87.5°	11.7	11.7	10.7	6.4	5.3
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.8	25.6	59.4	17.3	13.0
95°	15.7	62.3	280.1	96.9	59.8
97.5°	28.9	73.0	431.3	308.6	211.5
100°	38.0	79.3	464.2	470.2	362.2
102.5°	48.2	86.2	456.9	601.8	507.5
105°	64.0	97.0	419.5	741.0	704.4
107.5°	80.0	109.7	375.8	780.2	812.8
110°	91.1	118.9	350.7	765.2	838.4

TEST NUMBER: P521746

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	101.8	128.1	333.8	729.7	834.1
115°	118.9	143.7	318.1	673.9	791.3
117.5°	134.0	157.3	308.8	612.8	737.2
120°	146.1	165.5	307.8	577.9	697.2
122.5°	155.7	175.2	305.4	547.3	658.0
125°	167.8	186.1	303.6	503.8	602.4
127.5°	181.0	198.1	302.6	477.8	559.1
130°	187.7	204.8	301.2	459.7	530.6
132.5°	195.0	211.6	301.2	445.6	510.8
135°	205.2	222.3	300.0	425.6	481.1
137.5°	214.9	231.5	299.9	408.6	456.6
140°	222.1	239.2	299.4	394.6	440.6
142.5°	230.3	244.6	300.8	383.4	424.7
145°	242.0	254.4	302.4	368.3	401.4
147.5°	252.1	264.1	305.1	353.2	381.7
150°	260.8	269.0	306.0	348.1	368.2
152.5°	267.5	276.2	307.0	341.3	360.0
155°	276.4	282.9	309.6	332.9	346.5
157.5°	287.6	291.4	310.2	329.1	338.7
160°	293.3	296.3	312.7	326.1	334.4
162.5°	296.7	300.2	313.1	323.7	330.0
165°	305.4	306.6	313.3	320.0	324.7
167.5°	311.3	310.3	316.0	319.1	321.0
170°	313.3	312.7	315.1	315.7	318.1
172.5°	317.6	315.6	316.5	314.8	316.6
175°	319.9	318.1	316.9	315.0	312.7
177.5°	320.9	318.0	316.5	314.6	315.1
180°	317.5	317.5	317.5	317.5	317.5

(END OF REPORT)