

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521745

Luminaire Tested: **SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 5/5/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P521745  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,  
Test Lab: INNOVATION CENTER  
Issue Date: 5/5/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (3500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6281.5 lumens  
Efficiency: N/A  
Efficacy: 90.0 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 69.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P521745

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (3500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P521745

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (3500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74	69				
1	104	100	96	93	98	95	92	89	85	83	81	76	74	73	68	66	65	61				
2	96	89	84	79	90	85	80	76	76	73	69	69	66	63	62	59	58	54				
3	88	80	73	68	84	76	70	65	69	64	60	62	59	56	56	53	51	48				
4	82	72	65	59	77	69	62	57	62	57	53	57	53	49	51	48	45	43				
5	76	65	58	52	72	62	56	50	57	51	47	52	47	44	47	44	41	38				
6	71	59	52	46	67	57	50	45	52	46	42	48	43	40	44	40	37	35				
7	66	54	47	42	63	52	45	40	48	42	38	44	39	36	40	36	34	31				
8	62	50	43	38	59	48	41	37	44	39	35	41	36	33	37	34	31	29				
9	58	46	39	34	55	44	38	33	41	36	32	38	33	30	35	31	28	26				
10	54	43	36	31	52	41	35	31	38	33	29	35	31	28	33	29	26	24				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	27509	27509	27509
5°	27166	27068	27226
10°	25666	25898	26499
15°	23693	24243	25330
20°	21516	22325	23803
25°	19298	20351	22175
30°	17255	18384	20489
35°	15089	16179	18493
40°	12700	13708	16009
45°	10481	11386	13366
50°	8751	9539	11135
55°	7428	8186	9196
60°	6349	7097	7339
65°	5056	5969	4742
70°	4483	4659	2894
75°	4149	3779	1772
80°	3825	3475	1530
85°	3462	3186	1249



TEST NUMBER: P521745

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (3500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	273.5	4.4
10°-20°	711.3	11.3
20°-30°	921.4	14.7
30°-40°	902.3	14.4
40°-50°	690.6	11.0
50°-60°	460.2	7.3
60°-70°	251.1	4.0
70°-80°	104.6	1.7
80°-90°	29.6	0.5
90°-100°	142.1	2.3
100°-110°	404.2	6.4
110°-120°	387.3	6.2
120°-130°	306.6	4.9
130°-140°	246.0	3.9
140°-150°	192.6	3.1
150°-160°	140.9	2.2
160°-170°	87.3	1.4
170°-180°	29.6	0.5
0°-30°	1906.2	30.3
0°-40°	2808.5	44.7
0°-60°	3959.3	63.0
0°-90°	4344.7	69.2
90°-120°	933.6	14.9
90°-150°	1678.9	26.7
90°-180°	1937.0	30.8
0°-180°	6281.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2982	2982	2982	2982	2982	
5°	2933	2904	2923	2930	2940	273
15°	2480	2472	2538	2607	2652	693
25°	1896	1901	1999	2086	2178	872
35°	1340	1346	1436	1533	1642	833
45°	803	819	873	939	1024	626
55°	462	481	509	528	572	419
65°	232	251	273	239	217	241
75°	116	116	106	73	50	124
85°	33	33	30	19	12	36
90°	0	0	0	0	0	2
95°	15	61	275	95	59	18
105°	63	95	412	728	692	66
115°	117	141	312	662	777	115
125°	165	183	298	495	592	147
135°	202	218	295	418	472	156
145°	238	250	297	362	394	148
155°	272	278	304	327	340	126
165°	300	301	308	314	319	84
175°	314	312	311	309	307	30
180°	312	312	312	312	312	

TEST NUMBER: P521745

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (3500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2981.6	2981.6	2981.6	2981.6	2981.6
2.5°	2988.9	2962.3	2969.0	2968.8	2960.7
5°	2933.2	2903.8	2922.7	2929.5	2939.7
7.5°	2824.3	2802.1	2836.6	2862.2	2882.9
10°	2739.6	2720.4	2764.4	2801.7	2828.5
12.5°	2641.2	2625.0	2679.6	2729.6	2764.7
15°	2480.5	2471.6	2538.1	2607.1	2651.9
17.5°	2308.6	2304.3	2380.6	2461.1	2518.5
20°	2191.4	2190.1	2273.8	2357.7	2424.3
22.5°	2073.1	2075.9	2163.9	2251.2	2326.9
25°	1895.7	1900.8	1999.1	2086.2	2178.3
27.5°	1731.6	1733.9	1835.5	1927.5	2025.7
30°	1619.7	1626.1	1725.6	1820.8	1923.2
32.5°	1507.7	1515.1	1612.6	1711.0	1815.4
35°	1339.7	1346.1	1436.5	1533.2	1641.9
37.5°	1166.5	1175.2	1255.4	1346.8	1453.8
40°	1054.5	1067.3	1138.2	1224.3	1329.2
42.5°	946.7	962.5	1028.3	1110.0	1204.7
45°	803.3	818.6	872.6	938.7	1024.4
47.5°	679.8	697.4	738.9	795.8	869.0
50°	609.7	626.3	664.6	706.7	775.8
52.5°	547.9	564.5	598.7	631.1	690.0
55°	461.8	481.0	508.9	528.2	571.7
57.5°	391.2	409.6	431.7	440.4	466.8
60°	344.1	364.5	384.6	383.6	397.7
62.5°	301.2	318.6	338.6	324.7	325.5
65°	231.6	250.8	273.4	238.9	217.2
67.5°	187.1	191.2	214.6	166.6	140.8
70°	166.2	166.2	172.7	129.0	107.3
72.5°	146.3	146.3	140.2	104.9	82.2
75°	116.4	116.4	106.0	72.7	49.7
77.5°	89.7	88.7	81.1	54.3	36.1
80°	72.0	72.0	65.4	42.9	28.8
82.5°	56.3	56.3	50.8	33.5	21.5
85°	32.7	32.7	30.1	19.4	11.8
87.5°	11.5	11.5	10.5	6.3	5.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.7	25.1	58.3	17.0	12.8
95°	15.4	61.2	275.0	95.2	58.7
97.5°	28.3	71.7	423.6	303.1	207.7
100°	37.3	77.9	455.8	461.7	355.7
102.5°	47.3	84.6	448.7	591.0	498.4
105°	62.8	95.3	412.0	727.7	691.7
107.5°	78.6	107.7	369.0	766.2	798.2
110°	89.5	116.7	344.4	751.5	823.3

TEST NUMBER: P521745

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (3500K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	99.9	125.8	327.8	716.6	819.1
115°	116.8	141.1	312.4	661.8	777.1
117.5°	131.6	154.4	303.3	601.8	724.0
120°	143.4	162.6	302.3	567.6	684.6
122.5°	152.9	172.1	299.9	537.5	646.2
125°	164.8	182.8	298.2	494.8	591.6
127.5°	177.7	194.5	297.2	469.3	549.0
130°	184.3	201.2	295.8	451.5	521.0
132.5°	191.5	207.8	295.8	437.6	501.6
135°	201.5	218.3	294.6	417.9	472.4
137.5°	211.0	227.4	294.5	401.3	448.4
140°	218.1	234.9	294.0	387.5	432.7
142.5°	226.2	240.2	295.4	376.5	417.1
145°	237.7	249.9	297.0	361.7	394.2
147.5°	247.5	259.4	299.6	346.8	374.9
150°	256.1	264.2	300.5	341.9	361.6
152.5°	262.7	271.3	301.5	335.2	353.5
155°	271.5	277.9	304.1	326.9	340.2
157.5°	282.4	286.2	304.7	323.1	332.7
160°	288.1	291.0	307.0	320.3	328.4
162.5°	291.4	294.8	307.5	317.9	324.1
165°	299.9	301.1	307.6	314.3	318.9
167.5°	305.7	304.7	310.4	313.4	315.2
170°	307.6	307.1	309.4	310.1	312.4
172.5°	311.9	309.9	310.8	309.1	311.0
175°	314.2	312.4	311.2	309.4	307.0
177.5°	315.1	312.3	310.8	309.0	309.4
180°	311.8	311.8	311.8	311.8	311.8

(END OF REPORT)