

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521749

Luminaire Tested: **SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521749
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6665.1 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 69.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521749

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P521749

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74	69				
1	104	100	96	93	98	95	92	89	85	83	81	76	74	73	68	66	65	61				
2	96	89	84	79	90	85	80	76	76	73	69	69	66	63	62	59	58	54				
3	88	80	73	68	84	76	70	65	69	64	60	62	59	56	56	53	51	48				
4	82	72	65	59	77	69	62	57	62	57	53	57	53	49	51	48	45	43				
5	76	65	58	52	72	62	56	50	57	51	47	52	47	44	47	44	41	38				
6	71	59	52	46	67	57	50	45	52	46	42	48	43	40	44	40	37	35				
7	66	54	47	42	62	52	45	40	48	42	38	44	39	36	40	36	34	31				
8	62	50	43	38	59	48	41	37	44	39	35	41	36	33	37	34	31	29				
9	58	46	39	34	55	44	38	33	41	36	32	38	33	30	35	31	28	26				
10	54	43	36	31	52	41	35	31	38	33	29	35	31	28	33	29	26	24				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	29189	29189	29189
5°	28824	28722	28888
10°	27233	27480	28118
15°	25140	25724	26876
20°	22830	23689	25256
25°	20477	21593	23529
30°	18309	19507	21740
35°	16011	17167	19623
40°	13476	14545	16987
45°	11121	12081	14182
50°	9285	10122	11816
55°	7882	8686	9757
60°	6737	7530	7787
65°	5364	6333	5030
70°	4756	4942	3070
75°	4402	4007	1882
80°	4059	3687	1621
85°	3673	3377	1323



TEST NUMBER: P521749

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	290.2	4.4
10°-20°	754.8	11.3
20°-30°	977.7	14.7
30°-40°	957.4	14.4
40°-50°	732.8	11.0
50°-60°	488.3	7.3
60°-70°	266.5	4.0
70°-80°	111.0	1.7
80°-90°	31.4	0.5
90°-100°	150.8	2.3
100°-110°	428.9	6.4
110°-120°	411.0	6.2
120°-130°	325.3	4.9
130°-140°	261.1	3.9
140°-150°	204.4	3.1
150°-160°	149.6	2.2
160°-170°	92.6	1.4
170°-180°	31.4	0.5
0°-30°	2022.6	30.3
0°-40°	2980.0	44.7
0°-60°	4201.1	63.0
0°-90°	4610.0	69.2
90°-120°	990.7	14.9
90°-150°	1781.4	26.7
90°-180°	2055.0	30.8
0°-180°	6665.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3164	3164	3164	3164	3164	
5°	3112	3081	3101	3108	3119	290
15°	2632	2622	2693	2766	2814	735
25°	2012	2017	2121	2214	2311	925
35°	1422	1428	1524	1627	1742	884
45°	852	869	926	996	1087	665
55°	490	510	540	560	607	444
65°	246	266	290	254	230	255
75°	124	124	112	77	53	132
85°	35	35	32	21	12	38
90°	0	0	0	0	0	2
95°	16	65	292	101	62	19
105°	67	101	437	772	734	71
115°	124	150	332	702	825	122
125°	175	194	316	525	628	157
135°	214	232	313	444	501	165
145°	252	265	315	384	418	158
155°	288	295	323	347	361	133
165°	318	320	326	334	338	90
175°	333	332	330	328	326	32
180°	331	331	331	331	331	

TEST NUMBER: P521749

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3163.7	3163.7	3163.7	3163.7	3163.7
2.5°	3171.4	3143.2	3150.3	3150.1	3141.5
5°	3112.3	3081.1	3101.2	3108.4	3119.2
7.5°	2996.8	2973.2	3009.9	3037.0	3059.0
10°	2906.9	2886.5	2933.2	2972.7	3001.3
12.5°	2802.5	2785.4	2843.3	2896.3	2933.5
15°	2632.0	2622.5	2693.1	2766.3	2813.8
17.5°	2449.6	2445.0	2525.9	2611.4	2672.3
20°	2325.2	2323.9	2412.7	2501.7	2572.3
22.5°	2199.7	2202.7	2296.1	2388.7	2469.0
25°	2011.5	2016.9	2121.1	2213.6	2311.3
27.5°	1837.4	1839.8	1947.6	2045.2	2149.5
30°	1718.6	1725.4	1831.0	1932.0	2040.6
32.5°	1599.7	1607.6	1711.1	1815.5	1926.2
35°	1421.5	1428.3	1524.2	1626.8	1742.2
37.5°	1237.7	1246.9	1332.1	1429.1	1542.6
40°	1118.9	1132.4	1207.7	1299.1	1410.4
42.5°	1004.5	1021.3	1091.1	1177.8	1278.2
45°	852.3	868.6	925.9	996.0	1086.9
47.5°	721.3	740.0	784.0	844.4	922.0
50°	646.9	664.5	705.2	749.9	823.2
52.5°	581.4	599.0	635.2	669.7	732.1
55°	490.0	510.4	540.0	560.5	606.6
57.5°	415.1	434.6	458.1	467.3	495.3
60°	365.1	386.8	408.1	407.1	422.0
62.5°	319.6	338.0	359.3	344.6	345.4
65°	245.7	266.1	290.1	253.5	230.4
67.5°	198.5	202.9	227.7	176.8	149.4
70°	176.3	176.3	183.2	136.9	113.8
72.5°	155.2	155.2	148.8	111.3	87.2
75°	123.5	123.5	112.4	77.2	52.8
77.5°	95.2	94.1	86.1	57.6	38.3
80°	76.4	76.4	69.4	45.5	30.5
82.5°	59.7	59.7	53.9	35.5	22.8
85°	34.7	34.7	31.9	20.6	12.5
87.5°	12.2	12.2	11.1	6.6	5.6
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.0	26.7	61.9	18.0	13.6
95°	16.4	64.9	291.8	101.0	62.3
97.5°	30.1	76.1	449.5	321.6	220.4
100°	39.6	82.7	483.7	489.9	377.4
102.5°	50.2	89.8	476.1	627.1	528.8
105°	66.7	101.1	437.1	772.1	734.0
107.5°	83.4	114.3	391.6	813.0	847.0
110°	95.0	123.9	365.4	797.4	873.6

TEST NUMBER: P521749

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	106.0	133.5	347.8	760.4	869.1
115°	123.9	149.7	331.5	702.2	824.6
117.5°	139.6	163.9	321.8	638.6	768.2
120°	152.2	172.5	320.8	602.2	726.4
122.5°	162.3	182.6	318.3	570.3	685.7
125°	174.8	193.9	316.4	525.0	627.7
127.5°	188.6	206.4	315.4	497.9	582.5
130°	195.6	213.4	313.8	479.1	552.9
132.5°	203.2	220.5	313.8	464.3	532.2
135°	213.8	231.7	312.6	443.5	501.3
137.5°	223.9	241.3	312.5	425.8	475.7
140°	231.5	249.3	312.0	411.2	459.1
142.5°	240.0	254.9	313.5	399.5	442.5
145°	252.2	265.1	315.1	383.8	418.3
147.5°	262.7	275.2	317.9	368.0	397.8
150°	271.7	280.3	318.9	362.8	383.7
152.5°	278.8	287.9	319.9	355.7	375.1
155°	288.1	294.8	322.7	346.9	361.0
157.5°	299.6	303.7	323.3	342.9	353.0
160°	305.7	308.7	325.8	339.8	348.4
162.5°	309.2	312.8	326.3	337.3	343.9
165°	318.3	319.5	326.4	333.5	338.4
167.5°	324.4	323.3	329.3	332.5	334.5
170°	326.4	325.8	328.3	329.0	331.5
172.5°	331.0	328.9	329.8	328.0	329.9
175°	333.3	331.5	330.2	328.3	325.8
177.5°	334.4	331.4	329.8	327.8	328.3
180°	330.8	330.8	330.8	330.8	330.8

(END OF REPORT)