

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521748

Luminaire Tested: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4\_5000K

Issue Date: 5-5-2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P521748  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2009-966-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 5-5-2021  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4\_5000K  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6571.4 lumens  
Efficiency: N/A  
Efficacy: 94.3 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 69.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P521748

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4\_5000K

### Luminous Intensity Polar Plot



TEST NUMBER: P521748

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	112	112	112	112	106	106	106	106	94	94	94		83	83	83		74	74	74	69
1	104	100	96	93	98	95	92	89	85	83	81		76	74	73		68	66	65	61
2	96	89	84	79	90	85	80	76	76	73	69		69	66	63		62	59	58	54
3	88	80	73	68	84	76	70	65	69	64	60		62	59	56		56	53	51	48
4	82	72	65	59	77	69	62	57	62	57	53		57	53	49		51	48	45	43
5	76	65	58	52	72	62	56	50	57	51	47		52	47	44		47	44	41	38
6	71	59	52	46	67	57	50	45	52	46	42		48	43	40		44	40	37	35
7	66	54	47	42	63	52	45	40	48	42	38		44	39	36		40	36	34	31
8	62	50	43	38	59	48	41	37	44	39	35		41	36	33		37	34	31	29
9	58	46	39	34	55	44	38	33	41	36	32		38	33	30		35	31	28	26
10	54	43	36	31	52	41	35	31	38	33	29		35	31	28		33	29	26	24

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	28778	28778	28778
5°	28420	28318	28483
10°	26850	27094	27722
15°	24787	25363	26499
20°	22509	23356	24901
25°	20189	21290	23199
30°	18051	19233	21435
35°	15785	16926	19347
40°	13287	14342	16748
45°	10965	11911	13983
50°	9155	9980	11649
55°	7771	8564	9621
60°	6643	7425	7678
65°	5290	6246	4960
70°	4688	4874	3027
75°	4342	3953	1854
80°	4001	3634	1599
85°	3620	3335	1302

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 13983 cd/sqm

TEST NUMBER: P521748

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	286.1	4.4
10°-20°	744.2	11.3
20°-30°	963.9	14.7
30°-40°	943.9	14.4
40°-50°	722.5	11.0
50°-60°	481.4	7.3
60°-70°	262.7	4.0
70°-80°	109.5	1.7
80°-90°	31.0	0.5
90°-100°	148.6	2.3
100°-110°	422.9	6.4
110°-120°	405.2	6.2
120°-130°	320.7	4.9
130°-140°	257.4	3.9
140°-150°	201.5	3.1
150°-160°	147.4	2.2
160°-170°	91.3	1.4
170°-180°	31.0	0.5
0°-30°	1994.2	30.3
0°-40°	2938.1	44.7
0°-60°	4142.1	63.0
0°-90°	4545.3	69.2
90°-120°	976.8	14.9
90°-150°	1756.4	26.7
90°-180°	2026.0	30.8
0°-180°	6571.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3119	3119	3119	3119	3119	
5°	3069	3038	3058	3065	3075	285
15°	2595	2586	2655	2728	2774	725
25°	1983	1989	2091	2182	2279	912
35°	1402	1408	1503	1604	1718	871
45°	840	856	913	982	1072	655
55°	483	503	532	553	598	438
65°	242	262	286	250	227	252
75°	122	122	111	76	52	130
85°	34	34	32	20	12	37
90°	0	0	0	0	0	2
95°	16	64	288	100	61	18
105°	66	100	431	761	724	70
115°	122	148	327	692	813	120
125°	172	191	312	518	619	154
135°	211	228	308	437	494	163
145°	249	261	311	378	412	155
155°	284	291	318	342	356	131
165°	314	315	322	329	334	88
175°	329	327	326	324	321	31
180°	326	326	326	326	326	

TEST NUMBER: P521748

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3119.2	3119.2	3119.2	3119.2	3119.2
2.5°	3126.9	3099.1	3106.1	3105.9	3097.3
5°	3068.6	3037.8	3057.6	3064.7	3075.4
7.5°	2954.7	2931.4	2967.6	2994.4	3016.0
10°	2866.0	2846.0	2892.0	2931.0	2959.1
12.5°	2763.1	2746.2	2803.3	2855.6	2892.3
15°	2595.0	2585.7	2655.3	2727.5	2774.3
17.5°	2415.2	2410.6	2490.5	2574.8	2634.7
20°	2292.6	2291.2	2378.8	2466.6	2536.2
22.5°	2168.8	2171.8	2263.8	2355.1	2434.3
25°	1983.2	1988.6	2091.4	2182.5	2278.9
27.5°	1811.6	1814.0	1920.3	2016.5	2119.3
30°	1694.4	1701.1	1805.3	1904.9	2012.0
32.5°	1577.3	1585.0	1687.0	1790.0	1899.2
35°	1401.5	1408.2	1502.8	1604.0	1717.7
37.5°	1220.3	1229.4	1313.4	1409.0	1520.9
40°	1103.2	1116.5	1190.8	1280.8	1390.6
42.5°	990.4	1007.0	1075.8	1161.3	1260.3
45°	840.4	856.4	912.9	982.0	1071.7
47.5°	711.2	729.6	773.0	832.5	909.1
50°	637.8	655.2	695.3	739.4	811.6
52.5°	573.2	590.6	626.3	660.3	721.8
55°	483.1	503.2	532.4	552.6	598.1
57.5°	409.2	428.5	451.7	460.8	488.3
60°	360.0	381.4	402.4	401.4	416.1
62.5°	315.1	333.3	354.2	339.7	340.5
65°	242.3	262.3	286.1	250.0	227.2
67.5°	195.7	200.0	224.5	174.3	147.3
70°	173.8	173.8	180.7	135.0	112.2
72.5°	153.0	153.0	146.7	109.8	86.0
75°	121.8	121.8	110.9	76.1	52.0
77.5°	93.9	92.8	84.9	56.8	37.8
80°	75.3	75.3	68.4	44.8	30.1
82.5°	58.9	58.9	53.1	35.0	22.4
85°	34.2	34.2	31.5	20.3	12.3
87.5°	12.0	12.0	10.9	6.5	5.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.0	26.3	61.0	17.8	13.4
95°	16.1	64.0	287.7	99.6	61.4
97.5°	29.6	75.0	443.1	317.1	217.3
100°	39.1	81.5	476.9	483.0	372.1
102.5°	49.5	88.5	469.4	618.3	521.4
105°	65.7	99.7	431.0	761.3	723.7
107.5°	82.2	112.7	386.1	801.6	835.1
110°	93.6	122.1	360.3	786.2	861.3

TEST NUMBER: P521748

CATALOG NUMBER: SQ4-WB-025U-125D-92765-1D-UNV-STD-W-4\_5000K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	104.6	131.6	342.9	749.7	856.9
115°	122.2	147.6	326.8	692.3	813.0
117.5°	137.7	161.6	317.3	629.6	757.4
120°	150.1	170.1	316.3	593.8	716.2
122.5°	160.0	180.0	313.8	562.3	676.1
125°	172.4	191.2	311.9	517.6	618.9
127.5°	185.9	203.5	310.9	490.9	574.4
130°	192.9	210.4	309.4	472.3	545.1
132.5°	200.3	217.4	309.4	457.8	524.7
135°	210.8	228.4	308.2	437.2	494.2
137.5°	220.8	237.9	308.1	419.8	469.1
140°	228.2	245.8	307.6	405.4	452.7
142.5°	236.6	251.3	309.1	393.9	436.3
145°	248.7	261.4	310.7	378.4	412.4
147.5°	259.0	271.3	313.4	362.8	392.2
150°	267.9	276.4	314.4	357.7	378.3
152.5°	274.8	283.8	315.4	350.7	369.8
155°	284.0	290.7	318.1	342.0	355.9
157.5°	295.4	299.4	318.7	338.1	348.0
160°	301.4	304.4	321.2	335.1	343.5
162.5°	304.9	308.4	321.7	332.5	339.1
165°	313.8	315.0	321.8	328.8	333.6
167.5°	319.9	318.8	324.7	327.8	329.8
170°	321.8	321.2	323.7	324.4	326.8
172.5°	326.3	324.2	325.2	323.4	325.3
175°	328.7	326.8	325.6	323.6	321.2
177.5°	329.7	326.7	325.2	323.2	323.7
180°	326.2	326.2	326.2	326.2	326.2

(END OF REPORT)