

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521795

Luminaire Tested: **SQ4-WB-050U-125D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 5/5/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P521795  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,  
Test Lab: INNOVATION CENTER  
Issue Date: 5/5/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-WB-050U-125D-92765-1D-UNV-STD-W-4 (2700K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6245.0 lumens  
Efficiency: N/A  
Efficacy: 87.5 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 71.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P521795

CATALOG NUMBER: SQ4-WB-050U-125D-92765-1D-UNV-STD-W-4 (2700K)

### Luminous Intensity Polar Plot





TEST NUMBER: P521795

CATALOG NUMBER: SQ4-WB-050U-125D-92765-1D-UNV-STD-W-4 (2700K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	81	81	81	71	71	71	67				
1	103	99	96	93	97	94	91	88	83	81	79	74	72	71	65	64	63	59				
2	95	88	83	78	90	84	79	75	75	71	68	67	64	62	60	57	56	52				
3	88	79	73	67	83	75	69	65	68	63	59	61	57	54	54	52	49	46				
4	81	71	64	59	77	68	61	56	61	56	52	55	51	48	50	47	44	41				
5	75	65	57	52	71	62	55	50	56	50	46	51	46	43	46	42	39	37				
6	70	59	51	46	66	56	49	44	51	46	41	46	42	38	42	38	36	33				
7	65	54	46	41	62	51	45	40	47	41	37	43	38	35	39	35	32	30				
8	61	49	42	37	58	47	41	36	43	38	34	40	35	32	36	32	30	28				
9	57	46	38	34	54	44	37	33	40	35	31	37	32	29	34	30	27	25				
10	54	42	35	31	51	41	34	30	37	32	28	34	30	27	32	28	25	23				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	26319	26319	26319
5°	25990	25898	26048
10°	24555	24778	25352
15°	22668	23194	24234
20°	20585	21359	22773
25°	18463	19470	21216
30°	16509	17589	19602
35°	14436	15480	17693
40°	12151	13116	15316
45°	10027	10894	12788
50°	8372	9127	10653
55°	7107	7832	8799
60°	6075	6790	7021
65°	4836	5711	4536
70°	4289	4456	2768
75°	3971	3615	1697
80°	3655	3326	1461
85°	3313	3049	1196



TEST NUMBER: P521795

CATALOG NUMBER: SQ4-WB-050U-125D-92765-1D-UNV-STD-W-4 (2700K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	261.7	4.2
10°-20°	680.6	10.9
20°-30°	881.5	14.1
30°-40°	863.2	13.8
40°-50°	660.8	10.6
50°-60°	440.3	7.1
60°-70°	240.3	3.8
70°-80°	100.1	1.6
80°-90°	28.3	0.5
90°-100°	153.2	2.5
100°-110°	435.9	7.0
110°-120°	417.6	6.7
120°-130°	330.5	5.3
130°-140°	265.3	4.2
140°-150°	207.7	3.3
150°-160°	152.0	2.4
160°-170°	94.1	1.5
170°-180°	31.9	0.5
0°-30°	1823.7	29.2
0°-40°	2687.0	43.0
0°-60°	3788.0	60.7
0°-90°	4156.8	66.6
90°-120°	1006.7	16.1
90°-150°	1810.2	29.0
90°-180°	2088.0	33.4
0°-180°	6245.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2853	2853	2853	2853	2853	
5°	2806	2778	2796	2803	2812	261
15°	2373	2365	2428	2494	2537	663
25°	1814	1819	1913	1996	2084	834
35°	1282	1288	1374	1467	1571	797
45°	768	783	835	898	980	599
55°	442	460	487	505	547	401
65°	222	240	262	229	208	230
75°	111	111	101	70	48	119
85°	31	31	29	19	11	34
90°	0	0	0	0	0	2
95°	17	66	297	103	63	19
105°	68	103	444	785	746	72
115°	126	152	337	714	838	124
125°	178	197	322	534	638	159
135°	217	235	318	451	509	168
145°	256	269	320	390	425	160
155°	293	300	328	352	367	135
165°	323	325	332	339	344	91
175°	339	337	336	334	331	32
180°	336	336	336	336	336	

TEST NUMBER: P521795

CATALOG NUMBER: SQ4-WB-050U-125D-92765-1D-UNV-STD-W-4 (2700K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2852.6	2852.6	2852.6	2852.6	2852.6
2.5°	2859.6	2834.1	2840.6	2840.4	2832.6
5°	2806.3	2778.1	2796.3	2802.7	2812.5
7.5°	2702.1	2680.8	2713.9	2738.4	2758.2
10°	2621.0	2602.7	2644.8	2680.4	2706.1
12.5°	2526.9	2511.5	2563.7	2611.5	2645.1
15°	2373.2	2364.6	2428.3	2494.3	2537.2
17.5°	2208.7	2204.6	2277.6	2354.7	2409.5
20°	2096.6	2095.4	2175.4	2255.7	2319.4
22.5°	1983.4	1986.1	2070.3	2153.8	2226.2
25°	1813.7	1818.6	1912.6	1995.9	2084.1
27.5°	1656.7	1658.9	1756.1	1844.1	1938.1
30°	1549.6	1555.7	1651.0	1742.1	1840.0
32.5°	1442.4	1449.5	1542.8	1637.0	1736.8
35°	1281.7	1287.8	1374.4	1466.8	1570.9
37.5°	1116.0	1124.3	1201.1	1288.6	1390.9
40°	1008.9	1021.1	1089.0	1171.4	1271.7
42.5°	905.7	920.9	983.8	1062.0	1152.6
45°	768.5	783.2	834.9	898.1	980.1
47.5°	650.4	667.3	707.0	761.4	831.4
50°	583.3	599.2	635.9	676.2	742.2
52.5°	524.2	540.1	572.8	603.8	660.1
55°	441.8	460.2	486.9	505.4	547.0
57.5°	374.3	391.9	413.1	421.4	446.6
60°	329.2	348.8	368.0	367.1	380.5
62.5°	288.1	304.8	323.9	310.7	311.4
65°	221.5	239.9	261.6	228.6	207.8
67.5°	179.0	182.9	205.3	159.4	134.7
70°	159.0	159.0	165.2	123.4	102.6
72.5°	139.9	139.9	134.2	100.4	78.6
75°	111.4	111.4	101.4	69.6	47.6
77.5°	85.9	84.9	77.6	51.9	34.5
80°	68.8	68.8	62.6	41.0	27.5
82.5°	53.8	53.8	48.6	32.0	20.5
85°	31.3	31.3	28.8	18.6	11.3
87.5°	11.0	11.0	10.0	6.0	5.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.1	27.1	62.9	18.3	13.8
95°	16.6	66.0	296.6	102.6	63.3
97.5°	30.6	77.3	456.7	326.8	224.0
100°	40.3	84.0	491.5	497.8	383.5
102.5°	51.0	91.2	483.8	637.3	537.4
105°	67.7	102.7	444.2	784.6	745.9
107.5°	84.8	116.1	397.9	826.2	860.7
110°	96.5	125.9	371.3	810.3	887.8

TEST NUMBER: P521795

CATALOG NUMBER: SQ4-WB-050U-125D-92765-1D-UNV-STD-W-4 (2700K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	107.8	135.6	353.4	772.7	883.2
115°	125.9	152.2	336.8	713.6	837.9
117.5°	141.9	166.5	327.0	648.9	780.6
120°	154.7	175.3	326.0	612.0	738.2
122.5°	164.9	185.5	323.4	579.6	696.8
125°	177.7	197.1	321.5	533.5	637.9
127.5°	191.6	209.7	320.5	506.0	592.0
130°	198.8	216.9	318.9	486.8	561.8
132.5°	206.4	224.1	318.9	471.8	540.8
135°	217.3	235.4	317.7	450.7	509.4
137.5°	227.5	245.2	317.5	432.7	483.4
140°	235.2	253.3	317.0	417.8	466.6
142.5°	243.9	259.0	318.5	406.0	449.7
145°	256.3	269.4	320.2	390.0	425.0
147.5°	266.9	279.7	323.0	373.9	404.2
150°	276.1	284.9	324.0	368.6	389.9
152.5°	283.3	292.5	325.1	361.4	381.2
155°	292.7	299.6	327.9	352.5	366.9
157.5°	304.5	308.6	328.5	348.4	358.7
160°	310.6	313.7	331.1	345.3	354.1
162.5°	314.2	317.8	331.6	342.7	349.5
165°	323.4	324.7	331.7	338.9	343.9
167.5°	329.7	328.5	334.7	337.9	339.9
170°	331.7	331.1	333.6	334.3	336.8
172.5°	336.3	334.2	335.2	333.3	335.3
175°	338.7	336.9	335.5	333.6	331.1
177.5°	339.8	336.8	335.2	333.1	333.6
180°	336.2	336.2	336.2	336.2	336.2

(END OF REPORT)