

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521800

Luminaire Tested: **SQ4-WB-050U-125D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521800
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-050U-125D-92765-1D-UNV-STD-W-4 (5000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6828.8 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 71.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521800
CATALOG NUMBER: SQ4-WB-050U-125D-92765-1D-UNV-STD-W-4 (5000K)

Luminous Intensity Polar Plot





TEST NUMBER: P521800

CATALOG NUMBER: SQ4-WB-050U-125D-92765-1D-UNV-STD-W-4 (5000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	81	81	81	71	71	71	67				
1	103	99	96	93	97	94	91	88	83	81	79	74	72	71	65	64	63	59				
2	95	88	83	78	90	84	79	75	75	71	68	67	64	62	60	57	56	52				
3	88	79	73	67	83	75	69	65	68	63	59	61	57	54	54	52	49	46				
4	81	71	64	59	77	68	61	56	61	56	52	55	51	48	50	47	44	41				
5	75	65	57	52	71	62	55	50	56	50	46	51	46	43	46	42	39	37				
6	70	59	51	46	66	56	49	44	51	46	41	46	42	38	42	38	36	33				
7	65	54	46	41	62	51	45	40	47	41	37	43	38	35	39	35	32	30				
8	61	49	42	37	58	47	41	36	43	38	34	40	35	32	36	32	30	28				
9	57	46	38	34	54	44	37	33	40	35	31	37	32	29	34	30	27	25				
10	54	42	35	31	51	41	34	30	37	32	28	34	30	27	32	28	25	23				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	28778	28778	28778
5°	28420	28318	28483
10°	26850	27094	27722
15°	24787	25363	26499
20°	22509	23356	24901
25°	20189	21290	23199
30°	18051	19233	21435
35°	15785	16926	19347
40°	13287	14342	16748
45°	10965	11911	13983
50°	9155	9980	11649
55°	7771	8564	9621
60°	6643	7425	7678
65°	5290	6246	4960
70°	4688	4874	3027
75°	4342	3953	1854
80°	4001	3634	1599
85°	3620	3335	1302



TEST NUMBER: P521800

CATALOG NUMBER: SQ4-WB-050U-125D-92765-1D-UNV-STD-W-4 (5000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	286.1	4.2
10°-20°	744.2	10.9
20°-30°	963.9	14.1
30°-40°	943.9	13.8
40°-50°	722.5	10.6
50°-60°	481.4	7.1
60°-70°	262.7	3.8
70°-80°	109.5	1.6
80°-90°	31.0	0.5
90°-100°	167.5	2.5
100°-110°	476.6	7.0
110°-120°	456.7	6.7
120°-130°	361.4	5.3
130°-140°	290.1	4.2
140°-150°	227.1	3.3
150°-160°	166.2	2.4
160°-170°	102.9	1.5
170°-180°	34.9	0.5
0°-30°	1994.2	29.2
0°-40°	2938.1	43.0
0°-60°	4142.1	60.7
0°-90°	4545.3	66.6
90°-120°	1100.8	16.1
90°-150°	1979.5	29.0
90°-180°	2283.0	33.4
0°-180°	6828.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3119	3119	3119	3119	3119	
5°	3069	3038	3058	3065	3075	285
15°	2595	2586	2655	2728	2774	725
25°	1983	1989	2091	2182	2279	912
35°	1402	1408	1503	1604	1718	871
45°	840	856	913	982	1072	655
55°	483	503	532	553	598	438
65°	242	262	286	250	227	252
75°	122	122	111	76	52	130
85°	34	34	32	20	12	37
90°	0	0	0	0	0	2
95°	18	72	324	112	69	21
105°	74	112	486	858	816	78
115°	138	166	368	780	916	136
125°	194	216	352	583	698	174
135°	238	257	347	493	557	183
145°	280	295	350	426	465	175
155°	320	328	358	385	401	148
165°	354	355	363	370	376	99
175°	370	368	367	365	362	35
180°	368	368	368	368	368	

TEST NUMBER: P521800

CATALOG NUMBER: SQ4-WB-050U-125D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3119.2	3119.2	3119.2	3119.2	3119.2
2.5°	3126.9	3099.1	3106.1	3105.9	3097.3
5°	3068.6	3037.8	3057.6	3064.7	3075.4
7.5°	2954.7	2931.4	2967.6	2994.4	3016.0
10°	2866.0	2846.0	2892.0	2931.0	2959.1
12.5°	2763.1	2746.2	2803.3	2855.6	2892.3
15°	2595.0	2585.7	2655.3	2727.5	2774.3
17.5°	2415.2	2410.6	2490.5	2574.8	2634.7
20°	2292.6	2291.2	2378.8	2466.6	2536.2
22.5°	2168.8	2171.8	2263.8	2355.1	2434.3
25°	1983.2	1988.6	2091.4	2182.5	2278.9
27.5°	1811.6	1814.0	1920.3	2016.5	2119.3
30°	1694.4	1701.1	1805.3	1904.9	2012.0
32.5°	1577.3	1585.0	1687.0	1790.0	1899.2
35°	1401.5	1408.2	1502.8	1604.0	1717.7
37.5°	1220.3	1229.4	1313.4	1409.0	1520.9
40°	1103.2	1116.5	1190.8	1280.8	1390.6
42.5°	990.4	1007.0	1075.8	1161.3	1260.3
45°	840.4	856.4	912.9	982.0	1071.7
47.5°	711.2	729.6	773.0	832.5	909.1
50°	637.8	655.2	695.3	739.4	811.6
52.5°	573.2	590.6	626.3	660.3	721.8
55°	483.1	503.2	532.4	552.6	598.1
57.5°	409.2	428.5	451.7	460.8	488.3
60°	360.0	381.4	402.4	401.4	416.1
62.5°	315.1	333.3	354.2	339.7	340.5
65°	242.3	262.3	286.1	250.0	227.2
67.5°	195.7	200.0	224.5	174.3	147.3
70°	173.8	173.8	180.7	135.0	112.2
72.5°	153.0	153.0	146.7	109.8	86.0
75°	121.8	121.8	110.9	76.1	52.0
77.5°	93.9	92.8	84.9	56.8	37.8
80°	75.3	75.3	68.4	44.8	30.1
82.5°	58.9	58.9	53.1	35.0	22.4
85°	34.2	34.2	31.5	20.3	12.3
87.5°	12.0	12.0	10.9	6.5	5.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.6	29.6	68.8	20.0	15.1
95°	18.2	72.2	324.3	112.2	69.2
97.5°	33.4	84.5	499.4	357.4	244.9
100°	44.0	91.9	537.4	544.4	419.3
102.5°	55.8	99.8	529.1	696.8	587.6
105°	74.1	112.3	485.7	858.0	815.6
107.5°	92.7	127.0	435.1	903.4	941.1
110°	105.5	137.6	406.1	886.0	970.8

TEST NUMBER: P521800

CATALOG NUMBER: SQ4-WB-050U-125D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	117.8	148.3	386.5	844.9	965.7
115°	137.7	166.4	368.3	780.3	916.2
117.5°	155.2	182.1	357.6	709.6	853.6
120°	169.1	191.7	356.4	669.2	807.2
122.5°	180.3	202.9	353.6	633.7	761.9
125°	194.3	215.5	351.5	583.4	697.5
127.5°	209.5	229.3	350.4	553.3	647.3
130°	217.4	237.2	348.7	532.3	614.3
132.5°	225.7	245.0	348.7	516.0	591.4
135°	237.6	257.4	347.3	492.8	557.0
137.5°	248.8	268.1	347.2	473.1	528.6
140°	257.2	277.0	346.6	456.9	510.2
142.5°	266.7	283.2	348.3	443.9	491.7
145°	280.3	294.6	350.1	426.5	464.8
147.5°	291.9	305.8	353.2	408.9	442.0
150°	301.9	311.5	354.3	403.1	426.3
152.5°	309.7	319.9	355.5	395.2	416.8
155°	320.1	327.6	358.5	385.4	401.2
157.5°	332.9	337.5	359.2	381.0	392.2
160°	339.7	343.1	362.0	377.6	387.2
162.5°	343.6	347.5	362.6	374.8	382.2
165°	353.6	355.0	362.7	370.5	376.0
167.5°	360.5	359.3	365.9	369.5	371.7
170°	362.7	362.0	364.8	365.6	368.3
172.5°	367.8	365.4	366.5	364.4	366.6
175°	370.4	368.4	366.9	364.8	362.0
177.5°	371.5	368.2	366.5	364.3	364.8
180°	367.6	367.6	367.6	367.6	367.6

(END OF REPORT)