

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521786

Luminaire Tested: **SQ4-WB-050U-100D-92765-1D-UNV-STD-W-4 (4500K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521786
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-050U-100D-92765-1D-UNV-STD-W-4 (4500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5809.3 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 58.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521786

CATALOG NUMBER: SQ4-WB-050U-100D-92765-1D-UNV-STD-W-4 (4500K)

Luminous Intensity Polar Plot





TEST NUMBER: P521786

CATALOG NUMBER: SQ4-WB-050U-100D-92765-1D-UNV-STD-W-4 (4500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	90	90	90	77	77	77	66	66	66	66	66	66	61	
1	102	98	94	91	95	92	89	86	81	78	76	70	69	67	61	60	59	59	59	59	54	
2	94	87	82	77	88	82	77	73	72	69	66	63	61	59	55	53	52	52	52	52	48	
3	87	78	71	66	81	74	68	63	65	61	57	58	54	51	50	48	46	46	46	46	42	
4	80	70	63	57	75	66	60	55	59	54	50	52	48	45	46	43	41	41	41	41	38	
5	74	63	56	50	69	60	53	48	54	48	44	48	44	40	42	39	37	37	37	37	34	
6	69	58	50	45	65	55	48	43	49	44	40	44	40	36	39	36	33	33	33	33	31	
7	64	53	45	40	60	50	43	38	45	40	36	40	36	33	36	33	30	30	30	30	28	
8	60	48	41	36	56	46	39	35	42	36	32	37	33	30	34	30	27	27	27	27	25	
9	56	45	37	33	53	42	36	32	39	33	29	35	30	27	31	28	25	25	25	25	23	
10	53	41	34	30	50	39	33	29	36	31	27	32	28	25	29	26	23	23	23	23	22	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22482	22482	22482
5°	22202	22122	22251
10°	20975	21166	21657
15°	19363	19813	20701
20°	17584	18245	19453
25°	15772	16632	18123
30°	14102	15025	16745
35°	12332	13223	15114
40°	10379	11203	13083
45°	8566	9306	10924
50°	7152	7797	9100
55°	6071	6690	7515
60°	5189	5801	5997
65°	4133	4879	3875
70°	3663	3806	2366
75°	3394	3087	1447
80°	3124	2843	1249
85°	2826	2604	1016



TEST NUMBER: P521786

CATALOG NUMBER: SQ4-WB-050U-100D-92765-1D-UNV-STD-W-4 (4500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	223.5	3.8
10°-20°	581.4	10.0
20°-30°	753.0	13.0
30°-40°	737.4	12.7
40°-50°	564.4	9.7
50°-60°	376.1	6.5
60°-70°	205.2	3.5
70°-80°	85.5	1.5
80°-90°	24.2	0.4
90°-100°	165.7	2.9
100°-110°	471.4	8.1
110°-120°	451.7	7.8
120°-130°	357.5	6.2
130°-140°	286.9	4.9
140°-150°	224.6	3.9
150°-160°	164.4	2.8
160°-170°	101.8	1.8
170°-180°	34.5	0.6
0°-30°	1557.9	26.8
0°-40°	2295.3	39.5
0°-60°	3235.8	55.7
0°-90°	3550.8	61.1
90°-120°	1088.8	18.7
90°-150°	1957.8	33.7
90°-180°	2259.0	38.9
0°-180°	5809.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2437	2437	2437	2437	2437	
5°	2397	2373	2389	2394	2402	223
15°	2027	2020	2074	2131	2167	566
25°	1549	1554	1634	1705	1780	712
35°	1095	1100	1174	1253	1342	681
45°	656	669	713	767	837	512
55°	377	393	416	432	467	342
65°	189	205	224	195	178	197
75°	95	95	87	59	41	102
85°	27	27	25	16	10	29
90°	0	0	0	0	0	2
95°	18	71	321	111	68	21
105°	73	111	480	849	807	78
115°	136	165	364	772	906	134
125°	192	213	348	577	690	172
135°	235	255	344	487	551	181
145°	277	291	346	422	460	173
155°	317	324	355	381	397	146
165°	350	351	359	366	372	98
175°	366	364	363	361	358	35
180°	364	364	364	364	364	

TEST NUMBER: P521786

CATALOG NUMBER: SQ4-WB-050U-100D-92765-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2436.8	2436.8	2436.8	2436.8	2436.8
2.5°	2442.7	2421.0	2426.5	2426.3	2419.6
5°	2397.2	2373.1	2388.6	2394.2	2402.5
7.5°	2308.2	2290.0	2318.3	2339.2	2356.1
10°	2238.9	2223.3	2259.3	2289.7	2311.7
12.5°	2158.5	2145.4	2190.0	2230.8	2259.5
15°	2027.2	2019.9	2074.3	2130.7	2167.3
17.5°	1886.7	1883.2	1945.6	2011.4	2058.3
20°	1790.9	1789.9	1858.3	1926.9	1981.3
22.5°	1694.3	1696.6	1768.5	1839.8	1901.7
25°	1549.3	1553.5	1633.8	1705.0	1780.3
27.5°	1415.2	1417.1	1500.1	1575.3	1655.6
30°	1323.7	1328.9	1410.3	1488.1	1571.8
32.5°	1232.2	1238.2	1317.9	1398.3	1483.7
35°	1094.9	1100.1	1174.0	1253.0	1341.9
37.5°	953.3	960.4	1026.0	1100.7	1188.1
40°	861.8	872.2	930.2	1000.6	1086.3
42.5°	773.7	786.7	840.4	907.2	984.5
45°	656.5	669.0	713.2	767.2	837.2
47.5°	555.6	570.0	603.9	650.4	710.2
50°	498.3	511.8	543.2	577.6	634.0
52.5°	447.8	461.4	489.3	515.8	563.9
55°	377.4	393.1	415.9	431.7	467.2
57.5°	319.7	334.8	352.8	360.0	381.5
60°	281.2	297.9	314.4	313.5	325.0
62.5°	246.1	260.4	276.7	265.4	266.0
65°	189.3	204.9	223.5	195.3	177.5
67.5°	152.9	156.2	175.4	136.2	115.0
70°	135.8	135.8	141.1	105.4	87.7
72.5°	119.5	119.5	114.6	85.8	67.1
75°	95.2	95.2	86.6	59.4	40.6
77.5°	73.3	72.5	66.3	44.4	29.5
80°	58.8	58.8	53.5	35.0	23.5
82.5°	46.0	46.0	41.5	27.4	17.5
85°	26.7	26.7	24.6	15.9	9.6
87.5°	9.4	9.4	8.6	5.1	4.3
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.5	29.3	68.0	19.8	14.9
95°	18.0	71.4	320.7	111.0	68.4
97.5°	33.0	83.6	494.0	353.5	242.2
100°	43.5	90.9	531.6	538.4	414.7
102.5°	55.2	98.7	523.3	689.2	581.2
105°	73.3	111.1	480.4	848.6	806.7
107.5°	91.7	125.6	430.4	893.5	930.8
110°	104.4	136.1	401.6	876.3	960.1

TEST NUMBER: P521786

CATALOG NUMBER: SQ4-WB-050U-100D-92765-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	116.5	146.7	382.3	835.7	955.2
115°	136.2	164.6	364.3	771.7	906.2
117.5°	153.5	180.1	353.6	701.8	844.3
120°	167.3	189.6	352.5	661.9	798.4
122.5°	178.3	200.6	349.8	626.8	753.6
125°	192.2	213.1	347.7	577.0	689.9
127.5°	207.2	226.8	346.6	547.2	640.2
130°	215.0	234.6	344.9	526.5	607.6
132.5°	223.3	242.3	344.9	510.3	584.9
135°	235.0	254.6	343.5	487.4	550.9
137.5°	246.1	265.1	343.4	468.0	522.9
140°	254.4	274.0	342.9	451.9	504.6
142.5°	263.8	280.1	344.5	439.0	486.4
145°	277.2	291.4	346.3	421.8	459.7
147.5°	288.7	302.4	349.4	404.4	437.1
150°	298.6	308.1	350.5	398.7	421.7
152.5°	306.4	316.4	351.6	390.9	412.3
155°	316.6	324.0	354.6	381.2	396.8
157.5°	329.3	333.8	355.3	376.8	387.9
160°	335.9	339.3	358.1	373.5	382.9
162.5°	339.8	343.7	358.6	370.7	378.0
165°	349.8	351.1	358.8	366.5	371.9
167.5°	356.5	355.3	361.9	365.4	367.6
170°	358.8	358.1	360.8	361.6	364.3
172.5°	363.7	361.4	362.5	360.5	362.6
175°	366.4	364.3	362.9	360.8	358.1
177.5°	367.5	364.2	362.5	360.3	360.8
180°	363.6	363.6	363.6	363.6	363.6

(END OF REPORT)