

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521802

Luminaire Tested: **SQ4-WB-050U-125D-92765-1D-UNV-STD-W-4 (6500K)**

Issue Date: 5/5/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P521802  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,  
Test Lab: INNOVATION CENTER  
Issue Date: 5/5/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-WB-050U-125D-92765-1D-UNV-STD-W-4 (6500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 6500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6991.8 lumens  
Efficiency: N/A  
Efficacy: 98.3 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 71.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P521802

CATALOG NUMBER: SQ4-WB-050U-125D-92765-1D-UNV-STD-W-4 (6500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P521802

CATALOG NUMBER: SQ4-WB-050U-125D-92765-1D-UNV-STD-W-4 (6500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	81	81	81	71	71	71	67				
1	103	99	96	93	97	94	91	88	83	81	79	74	72	71	65	64	63	59				
2	95	88	83	78	90	84	79	75	75	71	68	67	64	62	60	57	56	52				
3	88	79	73	67	83	75	69	65	68	63	59	61	57	54	54	52	49	46				
4	81	71	64	59	77	68	61	56	61	56	52	55	51	48	50	47	44	41				
5	75	65	57	52	71	62	55	50	56	50	46	51	46	43	46	42	39	37				
6	70	59	51	46	66	56	49	44	51	46	41	46	42	38	42	38	36	33				
7	65	54	46	41	62	51	45	40	47	41	37	43	38	35	39	35	32	30				
8	61	49	42	37	58	47	41	36	43	38	34	40	35	32	36	32	30	28				
9	57	46	38	34	54	44	37	33	40	35	31	37	32	29	34	30	27	25				
10	54	42	35	31	51	41	34	30	37	32	28	34	30	27	32	28	25	23				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	29466	29466	29466
5°	29098	28994	29162
10°	27491	27740	28384
15°	25379	25967	27132
20°	23047	23913	25495
25°	20671	21798	23752
30°	18483	19692	21946
35°	16163	17331	19808
40°	13604	14684	17148
45°	11226	12196	14317
50°	9373	10218	11928
55°	7957	8768	9851
60°	6802	7602	7861
65°	5414	6394	5078
70°	4802	4990	3099
75°	4445	4046	1900
80°	4096	3725	1636
85°	3705	3409	1334



TEST NUMBER: P521802

CATALOG NUMBER: SQ4-WB-050U-125D-92765-1D-UNV-STD-W-4 (6500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	292.9	4.2
10°-20°	761.9	10.9
20°-30°	986.9	14.1
30°-40°	966.4	13.8
40°-50°	739.8	10.6
50°-60°	492.9	7.1
60°-70°	269.0	3.8
70°-80°	112.1	1.6
80°-90°	31.7	0.5
90°-100°	171.5	2.5
100°-110°	488.0	7.0
110°-120°	467.6	6.7
120°-130°	370.1	5.3
130°-140°	297.0	4.2
140°-150°	232.5	3.3
150°-160°	170.1	2.4
160°-170°	105.4	1.5
170°-180°	35.8	0.5
0°-30°	2041.8	29.2
0°-40°	3008.2	43.0
0°-60°	4240.9	60.7
0°-90°	4653.8	66.6
90°-120°	1127.1	16.1
90°-150°	2026.7	29.0
90°-180°	2338.0	33.4
0°-180°	6991.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3194	3194	3194	3194	3194	
5°	3142	3110	3131	3138	3149	292
15°	2657	2647	2719	2793	2840	742
25°	2031	2036	2141	2235	2333	934
35°	1435	1442	1539	1642	1759	892
45°	860	877	935	1006	1097	671
55°	495	515	545	566	612	449
65°	248	269	293	256	233	258
75°	125	125	114	78	53	133
85°	35	35	32	21	13	38
90°	0	0	0	0	0	2
95°	19	74	332	115	71	21
105°	76	115	497	878	835	80
115°	141	170	377	799	938	139
125°	199	221	360	597	714	178
135°	243	264	356	504	570	188
145°	287	302	358	437	476	179
155°	328	335	367	395	411	151
165°	362	364	371	379	385	102
175°	379	377	376	374	371	36
180°	376	376	376	376	376	

TEST NUMBER: P521802

CATALOG NUMBER: SQ4-WB-050U-125D-92765-1D-UNV-STD-W-4 (6500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3193.7	3193.7	3193.7	3193.7	3193.7
2.5°	3201.5	3173.0	3180.2	3180.0	3171.2
5°	3141.8	3110.3	3130.6	3137.9	3148.8
7.5°	3025.2	3001.4	3038.4	3065.8	3088.0
10°	2934.4	2913.9	2961.0	3000.9	3029.7
12.5°	2829.0	2811.8	2870.2	2923.8	2961.3
15°	2657.0	2647.4	2718.6	2792.6	2840.5
17.5°	2472.8	2468.2	2549.9	2636.2	2697.6
20°	2347.3	2345.9	2435.5	2525.4	2596.7
22.5°	2220.6	2223.6	2317.8	2411.3	2492.4
25°	2030.6	2036.0	2141.3	2234.6	2333.2
27.5°	1854.8	1857.3	1966.1	2064.6	2169.8
30°	1734.9	1741.7	1848.4	1950.4	2060.0
32.5°	1614.9	1622.9	1727.3	1832.7	1944.5
35°	1435.0	1441.8	1538.7	1642.2	1758.7
37.5°	1249.4	1258.8	1344.7	1442.6	1557.2
40°	1129.5	1143.2	1219.2	1311.4	1423.8
42.5°	1014.0	1031.0	1101.5	1189.0	1290.4
45°	860.4	876.9	934.7	1005.5	1097.3
47.5°	728.1	747.0	791.5	852.4	930.8
50°	653.0	670.8	711.9	757.0	831.0
52.5°	586.9	604.7	641.3	676.0	739.1
55°	494.7	515.2	545.1	565.8	612.4
57.5°	419.0	438.7	462.4	471.8	500.0
60°	368.6	390.5	412.0	410.9	426.0
62.5°	322.6	341.2	362.7	347.8	348.7
65°	248.0	268.6	292.9	255.9	232.6
67.5°	200.4	204.8	229.8	178.5	150.8
70°	178.0	178.0	185.0	138.2	114.9
72.5°	156.7	156.7	150.2	112.4	88.0
75°	124.7	124.7	113.5	77.9	53.3
77.5°	96.1	95.0	86.9	58.1	38.7
80°	77.1	77.1	70.1	45.9	30.8
82.5°	60.3	60.3	54.4	35.9	23.0
85°	35.0	35.0	32.2	20.8	12.6
87.5°	12.3	12.3	11.2	6.7	5.6
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.7	30.4	70.4	20.5	15.5
95°	18.6	73.9	332.0	114.9	70.8
97.5°	34.2	86.5	511.3	365.9	250.7
100°	45.1	94.1	550.3	557.4	429.3
102.5°	57.1	102.2	541.7	713.5	601.6
105°	75.8	115.0	497.3	878.4	835.1
107.5°	94.9	130.0	445.5	925.0	963.6
110°	108.1	140.9	415.7	907.2	993.9

TEST NUMBER: P521802

CATALOG NUMBER: SQ4-WB-050U-125D-92765-1D-UNV-STD-W-4 (6500K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	120.6	151.8	395.7	865.1	988.8
115°	141.0	170.4	377.1	798.9	938.1
117.5°	158.9	186.4	366.1	726.5	874.0
120°	173.2	196.3	364.9	685.1	826.5
122.5°	184.6	207.7	362.1	648.9	780.1
125°	198.9	220.6	359.9	597.3	714.1
127.5°	214.5	234.8	358.8	566.5	662.8
130°	222.5	242.8	357.1	545.0	629.0
132.5°	231.1	250.9	357.1	528.3	605.5
135°	243.3	263.6	355.6	504.5	570.3
137.5°	254.7	274.5	355.5	484.4	541.3
140°	263.3	283.6	354.9	467.8	522.4
142.5°	273.1	290.0	356.6	454.5	503.5
145°	286.9	301.6	358.5	436.7	475.8
147.5°	298.8	313.1	361.6	418.7	452.5
150°	309.1	318.9	362.8	412.7	436.5
152.5°	317.1	327.5	363.9	404.7	426.8
155°	327.7	335.4	367.1	394.6	410.7
157.5°	340.9	345.5	367.8	390.1	401.6
160°	347.8	351.3	370.7	386.6	396.4
162.5°	351.8	355.8	371.2	383.7	391.3
165°	362.1	363.5	371.4	379.4	385.0
167.5°	369.1	367.8	374.7	378.3	380.5
170°	371.4	370.7	373.5	374.3	377.1
172.5°	376.5	374.2	375.2	373.1	375.4
175°	379.2	377.1	375.7	373.5	370.7
177.5°	380.4	377.0	375.2	373.0	373.5
180°	376.4	376.4	376.4	376.4	376.4

(END OF REPORT)