

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521834

Luminaire Tested: SQ4-WB-075U-100D-92765-1D-UNV-STD-W-4_2700K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P521834
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-WB-075U-100D-92765-1D-UNV-STD-W-4_2700K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6409.2 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P521834

CATALOG NUMBER: SQ4-WB-075U-100D-92765-1D-UNV-STD-W-4_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P521834

CATALOG NUMBER: SQ4-WB-075U-100D-92765-1D-UNV-STD-W-4_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51				51
1	99	95	92	89	92	88	85	83	75	73	71	63	62	61	52	51	51	45				45
2	91	85	79	75	84	79	74	70	67	64	61	57	55	53	48	46	45	40				40
3	84	76	69	64	78	70	65	60	61	56	53	52	49	46	43	41	39	35				35
4	78	68	60	55	72	63	57	52	55	50	46	47	43	41	40	37	35	32				32
5	72	61	54	48	66	57	51	46	50	45	41	43	39	36	36	34	31	28				28
6	67	55	48	42	62	52	45	40	45	40	36	39	35	32	33	31	28	26				26
7	62	50	43	38	57	47	41	36	42	36	33	36	32	29	31	28	26	23				23
8	58	46	39	34	54	43	37	32	38	33	29	33	29	26	29	26	23	21				21
9	54	42	35	31	50	40	34	29	35	30	27	31	27	24	27	24	22	20				20
10	51	39	32	28	47	37	31	27	33	28	24	29	25	22	25	22	20	18				18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20788	20788	20788
5°	20528	20455	20574
10°	19395	19571	20024
15°	17905	18320	19142
20°	16259	16871	17986
25°	14583	15378	16757
30°	13039	13892	15483
35°	11403	12226	13974
40°	9597	10359	12098
45°	7920	8604	10100
50°	6613	7208	8415
55°	5614	6186	6949
60°	4798	5364	5545
65°	3820	4510	3582
70°	3388	3520	2188
75°	3137	2855	1340
80°	2890	2625	1158
85°	2615	2403	942

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 10100 cd/sqm

TEST NUMBER: P521834

CATALOG NUMBER: SQ4-WB-075U-100D-92765-1D-UNV-STD-W-4_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	206.7	3.2
10°-20°	537.5	8.4
20°-30°	696.3	10.9
30°-40°	681.8	10.6
40°-50°	521.9	8.1
50°-60°	347.8	5.4
60°-70°	189.8	3.0
70°-80°	79.1	1.2
80°-90°	22.4	0.3
90°-100°	229.3	3.6
100°-110°	652.5	10.2
110°-120°	625.2	9.8
120°-130°	494.8	7.7
130°-140°	397.1	6.2
140°-150°	310.9	4.9
150°-160°	227.5	3.5
160°-170°	140.9	2.2
170°-180°	47.8	0.7
0°-30°	1440.5	22.5
0°-40°	2122.3	33.1
0°-60°	2992.0	46.7
0°-90°	3283.2	51.2
90°-120°	1507.0	23.5
90°-150°	2709.8	42.3
90°-180°	3126.0	48.8
0°-180°	6409.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2253	2253	2253	2253	2253	
5°	2216	2194	2209	2214	2222	206
15°	1874	1868	1918	1970	2004	523
25°	1432	1436	1511	1576	1646	659
35°	1012	1017	1086	1159	1241	629
45°	607	619	659	709	774	473
55°	349	364	385	399	432	316
65°	175	190	207	180	164	182
75°	88	88	80	55	38	94
85°	25	25	23	15	9	27
90°	0	0	0	0	0	2
95°	25	99	444	154	95	28
105°	101	154	665	1174	1116	107
115°	188	228	504	1068	1254	186
125°	266	295	481	799	955	238
135°	325	352	476	675	762	251
145°	384	403	479	584	636	240
155°	438	448	491	528	549	203
165°	484	486	496	507	515	136
175°	507	504	502	499	496	48
180°	503	503	503	503	503	

TEST NUMBER: P521834

CATALOG NUMBER: SQ4-WB-075U-100D-92765-1D-UNV-STD-W-4_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2253.1	2253.1	2253.1	2253.1	2253.1
2.5°	2258.6	2238.5	2243.6	2243.5	2237.3
5°	2216.5	2194.3	2208.6	2213.7	2221.5
7.5°	2134.3	2117.5	2143.6	2162.9	2178.6
10°	2070.2	2055.7	2089.0	2117.1	2137.4
12.5°	1995.9	1983.7	2024.9	2062.7	2089.2
15°	1874.5	1867.7	1918.0	1970.1	2004.0
17.5°	1744.6	1741.3	1798.9	1859.8	1903.1
20°	1656.0	1655.0	1718.3	1781.7	1831.9
22.5°	1566.6	1568.7	1635.2	1701.2	1758.4
25°	1432.5	1436.4	1510.6	1576.5	1646.1
27.5°	1308.6	1310.3	1387.1	1456.6	1530.8
30°	1223.9	1228.8	1304.0	1376.0	1453.3
32.5°	1139.3	1144.9	1218.6	1293.0	1371.8
35°	1012.4	1017.2	1085.5	1158.6	1240.7
37.5°	881.5	888.0	948.7	1017.8	1098.6
40°	796.8	806.5	860.1	925.2	1004.5
42.5°	715.4	727.4	777.1	838.8	910.3
45°	607.0	618.6	659.4	709.3	774.1
47.5°	513.7	527.0	558.4	601.4	656.7
50°	460.7	473.3	502.2	534.1	586.3
52.5°	414.0	426.6	452.4	476.9	521.4
55°	349.0	363.5	384.6	399.2	432.0
57.5°	295.6	309.5	326.3	332.8	352.7
60°	260.0	275.5	290.7	289.9	300.5
62.5°	227.6	240.7	255.9	245.4	246.0
65°	175.0	189.5	206.6	180.5	164.1
67.5°	141.4	144.5	162.1	125.9	106.4
70°	125.6	125.6	130.5	97.5	81.1
72.5°	110.5	110.5	106.0	79.3	62.1
75°	88.0	88.0	80.1	55.0	37.6
77.5°	67.8	67.0	61.3	41.0	27.3
80°	54.4	54.4	49.4	32.4	21.8
82.5°	42.5	42.5	38.4	25.3	16.2
85°	24.7	24.7	22.7	14.7	8.9
87.5°	8.7	8.7	7.9	4.7	4.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	7.7	40.6	94.1	27.4	20.7
95°	24.9	98.8	443.9	153.7	94.7
97.5°	45.7	115.7	683.7	489.2	335.2
100°	60.3	125.8	735.7	745.2	574.0
102.5°	76.3	136.6	724.3	953.9	804.4
105°	101.4	153.8	664.9	1174.5	1116.5
107.5°	126.9	173.8	595.7	1236.7	1288.3
110°	144.5	188.4	555.9	1212.9	1328.9

TEST NUMBER: P521834

CATALOG NUMBER: SQ4-WB-075U-100D-92765-1D-UNV-STD-W-4_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	161.3	203.0	529.1	1156.6	1322.0
115°	188.5	227.8	504.2	1068.1	1254.3
117.5°	212.4	249.3	489.5	971.4	1168.6
120°	231.5	262.4	487.9	916.1	1105.0
122.5°	246.8	277.7	484.1	867.5	1043.0
125°	266.0	295.0	481.2	798.6	954.8
127.5°	286.8	314.0	479.7	757.4	886.1
130°	297.5	324.7	477.4	728.7	841.0
132.5°	309.0	335.4	477.4	706.3	809.6
135°	325.3	352.4	475.5	674.6	762.5
137.5°	340.6	367.0	475.3	647.7	723.7
140°	352.1	379.2	474.5	625.5	698.4
142.5°	365.1	387.7	476.8	607.7	673.2
145°	383.7	403.3	479.3	583.8	636.2
147.5°	399.5	418.6	483.5	559.8	605.0
150°	413.3	426.4	485.1	551.8	583.6
152.5°	424.0	437.9	486.6	541.0	570.6
155°	438.2	448.5	490.8	527.7	549.2
157.5°	455.8	462.0	491.8	521.6	536.9
160°	465.0	469.7	495.6	516.9	530.0
162.5°	470.3	475.8	496.4	513.0	523.1
165°	484.1	486.0	496.5	507.2	514.7
167.5°	493.5	491.8	500.9	505.8	508.8
170°	496.5	495.6	499.4	500.5	504.2
172.5°	503.4	500.3	501.7	498.9	501.9
175°	507.1	504.3	502.3	499.3	495.6
177.5°	508.6	504.1	501.7	498.7	499.4
180°	503.2	503.2	503.2	503.2	503.2

(END OF REPORT)