

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521849

Luminaire Tested: **SQ4-WB-075U-125D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 5/5/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P521849  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,  
Test Lab: INNOVATION CENTER  
Issue Date: 5/5/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-WB-075U-125D-92765-1D-UNV-STD-W-4 (3500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7612.1 lumens  
Efficiency: N/A  
Efficacy: 95.7 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 79.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P521849

CATALOG NUMBER: SQ4-WB-075U-125D-92765-1D-UNV-STD-W-4 (3500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P521849

CATALOG NUMBER: SQ4-WB-075U-125D-92765-1D-UNV-STD-W-4 (3500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	101	97	93	90	94	90	87	85	78	76	74	67	66	65	57	56	55	51
2	93	86	81	76	86	81	76	72	70	67	64	61	58	56	52	50	49	45
3	86	77	70	65	80	72	66	62	63	59	55	55	52	49	47	45	43	39
4	79	69	62	56	74	65	59	54	57	52	48	50	46	43	43	41	38	35
5	73	62	55	49	68	59	52	47	52	47	43	46	42	39	40	37	34	32
6	68	57	49	44	63	54	47	42	48	42	38	42	38	35	37	34	31	28
7	63	52	44	39	59	49	42	37	44	38	34	39	34	31	34	31	28	26
8	59	47	40	35	55	45	38	34	40	35	31	36	32	28	32	28	26	24
9	55	44	37	32	52	41	35	31	37	32	28	33	29	26	29	26	24	22
10	52	40	34	29	49	38	32	28	35	29	26	31	27	24	28	24	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	27509	27509	27509
5°	27166	27068	27226
10°	25666	25898	26499
15°	23693	24243	25330
20°	21516	22325	23803
25°	19298	20351	22175
30°	17255	18384	20489
35°	15089	16179	18493
40°	12700	13708	16009
45°	10481	11386	13366
50°	8751	9539	11135
55°	7428	8186	9196
60°	6349	7097	7339
65°	5056	5969	4742
70°	4483	4659	2894
75°	4149	3779	1772
80°	3825	3475	1530
85°	3462	3186	1249



TEST NUMBER: P521849

CATALOG NUMBER: SQ4-WB-075U-125D-92765-1D-UNV-STD-W-4 (3500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	273.5	3.6
10°-20°	711.3	9.3
20°-30°	921.4	12.1
30°-40°	902.3	11.9
40°-50°	690.6	9.1
50°-60°	460.2	6.0
60°-70°	251.1	3.3
70°-80°	104.6	1.4
80°-90°	29.6	0.4
90°-100°	239.7	3.1
100°-110°	682.0	9.0
110°-120°	653.4	8.6
120°-130°	517.2	6.8
130°-140°	415.1	5.5
140°-150°	325.0	4.3
150°-160°	237.8	3.1
160°-170°	147.3	1.9
170°-180°	50.0	0.7
0°-30°	1906.2	25.0
0°-40°	2808.5	36.9
0°-60°	3959.3	52.0
0°-90°	4344.7	57.1
90°-120°	1575.1	20.7
90°-150°	2832.3	37.2
90°-180°	3267.0	42.9
0°-180°	7612.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2982	2982	2982	2982	2982	
5°	2933	2904	2923	2930	2940	273
15°	2480	2472	2538	2607	2652	693
25°	1896	1901	1999	2086	2178	872
35°	1340	1346	1436	1533	1642	833
45°	803	819	873	939	1024	626
55°	462	481	509	528	572	419
65°	232	251	273	239	217	241
75°	116	116	106	73	50	124
85°	33	33	30	19	12	36
90°	0	0	0	0	0	3
95°	26	103	464	161	99	30
105°	106	161	695	1228	1167	112
115°	197	238	527	1116	1311	194
125°	278	308	503	835	998	249
135°	340	368	497	705	797	262
145°	401	422	501	610	665	250
155°	458	469	513	552	574	212
165°	506	508	519	530	538	142
175°	530	527	525	522	518	50
180°	526	526	526	526	526	

TEST NUMBER: P521849

CATALOG NUMBER: SQ4-WB-075U-125D-92765-1D-UNV-STD-W-4 (3500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2981.6	2981.6	2981.6	2981.6	2981.6
2.5°	2988.9	2962.3	2969.0	2968.8	2960.7
5°	2933.2	2903.8	2922.7	2929.5	2939.7
7.5°	2824.3	2802.1	2836.6	2862.2	2882.9
10°	2739.6	2720.4	2764.4	2801.7	2828.5
12.5°	2641.2	2625.0	2679.6	2729.6	2764.7
15°	2480.5	2471.6	2538.1	2607.1	2651.9
17.5°	2308.6	2304.3	2380.6	2461.1	2518.5
20°	2191.4	2190.1	2273.8	2357.7	2424.3
22.5°	2073.1	2075.9	2163.9	2251.2	2326.9
25°	1895.7	1900.8	1999.1	2086.2	2178.3
27.5°	1731.6	1733.9	1835.5	1927.5	2025.7
30°	1619.7	1626.1	1725.6	1820.8	1923.2
32.5°	1507.7	1515.1	1612.6	1711.0	1815.4
35°	1339.7	1346.1	1436.5	1533.2	1641.9
37.5°	1166.5	1175.2	1255.4	1346.8	1453.8
40°	1054.5	1067.3	1138.2	1224.3	1329.2
42.5°	946.7	962.5	1028.3	1110.0	1204.7
45°	803.3	818.6	872.6	938.7	1024.4
47.5°	679.8	697.4	738.9	795.8	869.0
50°	609.7	626.3	664.6	706.7	775.8
52.5°	547.9	564.5	598.7	631.1	690.0
55°	461.8	481.0	508.9	528.2	571.7
57.5°	391.2	409.6	431.7	440.4	466.8
60°	344.1	364.5	384.6	383.6	397.7
62.5°	301.2	318.6	338.6	324.7	325.5
65°	231.6	250.8	273.4	238.9	217.2
67.5°	187.1	191.2	214.6	166.6	140.8
70°	166.2	166.2	172.7	129.0	107.3
72.5°	146.3	146.3	140.2	104.9	82.2
75°	116.4	116.4	106.0	72.7	49.7
77.5°	89.7	88.7	81.1	54.3	36.1
80°	72.0	72.0	65.4	42.9	28.8
82.5°	56.3	56.3	50.8	33.5	21.5
85°	32.7	32.7	30.1	19.4	11.8
87.5°	11.5	11.5	10.5	6.3	5.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.0	42.4	98.4	28.6	21.6
95°	26.0	103.2	464.0	160.6	99.0
97.5°	47.8	120.9	714.6	511.3	350.4
100°	63.0	131.4	769.0	778.9	600.0
102.5°	79.8	142.8	757.0	997.0	840.8
105°	106.0	160.8	695.0	1227.6	1167.0
107.5°	132.6	181.7	622.6	1292.6	1346.6
110°	151.0	197.0	581.0	1267.8	1389.0

TEST NUMBER: P521849

CATALOG NUMBER: SQ4-WB-075U-125D-92765-1D-UNV-STD-W-4 (3500K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	168.6	212.2	553.0	1208.9	1381.8
115°	197.0	238.1	527.0	1116.4	1311.0
117.5°	222.0	260.5	511.6	1015.3	1221.4
120°	242.0	274.3	510.0	957.5	1155.0
122.5°	258.0	290.3	506.0	906.8	1090.2
125°	278.0	308.3	503.0	834.7	998.0
127.5°	299.8	328.2	501.4	791.7	926.2
130°	311.0	339.4	499.0	761.7	879.0
132.5°	323.0	350.6	499.0	738.3	846.2
135°	340.0	368.4	497.0	705.1	797.0
137.5°	356.0	383.6	496.8	677.0	756.4
140°	368.0	396.4	496.0	653.7	730.0
142.5°	381.6	405.3	498.4	635.2	703.6
145°	401.0	421.5	501.0	610.2	665.0
147.5°	417.6	437.5	505.4	585.1	632.4
150°	432.0	445.7	507.0	576.8	610.0
152.5°	443.2	457.7	508.6	565.5	596.4
155°	458.0	468.8	513.0	551.5	574.0
157.5°	476.4	482.9	514.0	545.2	561.2
160°	486.0	490.9	518.0	540.3	554.0
162.5°	491.6	497.3	518.8	536.2	546.8
165°	506.0	508.0	519.0	530.2	538.0
167.5°	515.8	514.0	523.6	528.7	531.8
170°	519.0	518.0	522.0	523.1	527.0
172.5°	526.2	522.9	524.4	521.5	524.6
175°	530.0	527.1	525.0	521.9	518.0
177.5°	531.6	526.9	524.4	521.2	522.0
180°	526.0	526.0	526.0	526.0	526.0

(END OF REPORT)