

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521854

Luminaire Tested: **SQ4-WB-075U-125D-92765-1D-UNV-STD-W-4 (6500K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521854
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-075U-125D-92765-1D-UNV-STD-W-4 (6500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 6500K CCT
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8153.5 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 78.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521854
CATALOG NUMBER: SQ4-WB-075U-125D-92765-1D-UNV-STD-W-4 (6500K)

Luminous Intensity Polar Plot





TEST NUMBER: P521854

CATALOG NUMBER: SQ4-WB-075U-125D-92765-1D-UNV-STD-W-4 (6500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	101	97	93	90	94	90	87	85	78	76	74	67	66	65	57	56	55	51
2	93	86	81	76	86	81	76	72	70	67	64	61	58	56	52	50	49	45
3	86	77	70	65	80	72	66	62	63	59	55	55	52	49	47	45	43	39
4	79	69	62	56	74	65	59	54	57	52	48	50	46	43	43	41	38	35
5	73	62	55	49	68	59	52	47	52	47	43	46	42	39	40	37	34	32
6	68	57	49	44	63	54	47	42	48	42	38	42	38	35	37	34	31	28
7	63	52	44	39	59	49	42	37	44	38	34	39	34	31	34	31	28	26
8	59	47	40	35	55	45	38	34	40	35	31	36	32	28	32	28	26	24
9	55	44	37	32	52	41	35	31	37	32	28	33	29	26	29	26	24	22
10	52	40	34	29	49	38	32	28	35	29	26	31	27	24	28	24	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	29466	29466	29466
5°	29098	28994	29162
10°	27491	27740	28384
15°	25379	25967	27132
20°	23047	23913	25495
25°	20671	21798	23752
30°	18483	19692	21946
35°	16163	17331	19808
40°	13604	14684	17148
45°	11226	12196	14317
50°	9373	10218	11928
55°	7957	8768	9851
60°	6802	7602	7861
65°	5414	6394	5078
70°	4802	4990	3099
75°	4445	4046	1900
80°	4096	3725	1636
85°	3705	3409	1334



TEST NUMBER: P521854

CATALOG NUMBER: SQ4-WB-075U-125D-92765-1D-UNV-STD-W-4 (6500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	292.9	3.6
10°-20°	761.9	9.3
20°-30°	986.9	12.1
30°-40°	966.4	11.9
40°-50°	739.8	9.1
50°-60°	492.9	6.0
60°-70°	269.0	3.3
70°-80°	112.1	1.4
80°-90°	31.7	0.4
90°-100°	256.7	3.1
100°-110°	730.5	9.0
110°-120°	699.9	8.6
120°-130°	553.9	6.8
130°-140°	444.6	5.5
140°-150°	348.1	4.3
150°-160°	254.7	3.1
160°-170°	157.8	1.9
170°-180°	53.5	0.7
0°-30°	2041.8	25.0
0°-40°	3008.2	36.9
0°-60°	4240.9	52.0
0°-90°	4653.8	57.1
90°-120°	1687.1	20.7
90°-150°	3033.8	37.2
90°-180°	3500.0	42.9
0°-180°	8153.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3194	3194	3194	3194	3194	
5°	3142	3110	3131	3138	3149	292
15°	2657	2647	2719	2793	2840	742
25°	2031	2036	2141	2235	2333	934
35°	1435	1442	1539	1642	1759	892
45°	860	877	935	1006	1097	671
55°	495	515	545	566	612	449
65°	248	269	293	256	233	258
75°	125	125	114	78	53	133
85°	35	35	32	21	13	38
90°	0	0	0	0	0	3
95°	28	111	497	172	106	32
105°	114	172	744	1315	1250	120
115°	211	255	564	1196	1404	208
125°	298	330	539	894	1069	267
135°	364	395	532	755	854	281
145°	430	452	537	654	712	268
155°	491	502	550	591	615	227
165°	542	544	556	568	576	152
175°	568	565	562	559	555	54
180°	563	563	563	563	563	

TEST NUMBER: P521854

CATALOG NUMBER: SQ4-WB-075U-125D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3193.7	3193.7	3193.7	3193.7	3193.7
2.5°	3201.5	3173.0	3180.2	3180.0	3171.2
5°	3141.8	3110.3	3130.6	3137.9	3148.8
7.5°	3025.2	3001.4	3038.4	3065.8	3088.0
10°	2934.4	2913.9	2961.0	3000.9	3029.7
12.5°	2829.0	2811.8	2870.2	2923.8	2961.3
15°	2657.0	2647.4	2718.6	2792.6	2840.5
17.5°	2472.8	2468.2	2549.9	2636.2	2697.6
20°	2347.3	2345.9	2435.5	2525.4	2596.7
22.5°	2220.6	2223.6	2317.8	2411.3	2492.4
25°	2030.6	2036.0	2141.3	2234.6	2333.2
27.5°	1854.8	1857.3	1966.1	2064.6	2169.8
30°	1734.9	1741.7	1848.4	1950.4	2060.0
32.5°	1614.9	1622.9	1727.3	1832.7	1944.5
35°	1435.0	1441.8	1538.7	1642.2	1758.7
37.5°	1249.4	1258.8	1344.7	1442.6	1557.2
40°	1129.5	1143.2	1219.2	1311.4	1423.8
42.5°	1014.0	1031.0	1101.5	1189.0	1290.4
45°	860.4	876.9	934.7	1005.5	1097.3
47.5°	728.1	747.0	791.5	852.4	930.8
50°	653.0	670.8	711.9	757.0	831.0
52.5°	586.9	604.7	641.3	676.0	739.1
55°	494.7	515.2	545.1	565.8	612.4
57.5°	419.0	438.7	462.4	471.8	500.0
60°	368.6	390.5	412.0	410.9	426.0
62.5°	322.6	341.2	362.7	347.8	348.7
65°	248.0	268.6	292.9	255.9	232.6
67.5°	200.4	204.8	229.8	178.5	150.8
70°	178.0	178.0	185.0	138.2	114.9
72.5°	156.7	156.7	150.2	112.4	88.0
75°	124.7	124.7	113.5	77.9	53.3
77.5°	96.1	95.0	86.9	58.1	38.7
80°	77.1	77.1	70.1	45.9	30.8
82.5°	60.3	60.3	54.4	35.9	23.0
85°	35.0	35.0	32.2	20.8	12.6
87.5°	12.3	12.3	11.2	6.7	5.6
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.6	45.4	105.4	30.7	23.1
95°	27.8	110.6	497.0	172.0	106.0
97.5°	51.2	129.5	765.4	547.7	375.3
100°	67.5	140.8	823.7	834.3	642.7
102.5°	85.5	152.9	810.8	1068.0	900.6
105°	113.5	172.2	744.4	1314.9	1250.0
107.5°	142.0	194.6	666.9	1384.6	1442.4
110°	161.7	211.0	622.3	1357.9	1487.8

TEST NUMBER: P521854

CATALOG NUMBER: SQ4-WB-075U-125D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	180.6	227.3	592.3	1294.9	1480.1
115°	211.0	255.0	564.5	1195.8	1404.3
117.5°	237.8	279.1	548.0	1087.5	1308.3
120°	259.2	293.8	546.3	1025.6	1237.2
122.5°	276.4	310.9	542.0	971.3	1167.7
125°	297.8	330.2	538.8	894.1	1069.0
127.5°	321.1	351.5	537.1	848.0	992.1
130°	333.1	363.5	534.5	815.8	941.5
132.5°	346.0	375.5	534.5	790.8	906.4
135°	364.2	394.6	532.4	755.2	853.7
137.5°	381.3	410.9	532.1	725.2	810.2
140°	394.2	424.5	531.3	700.2	781.9
142.5°	408.7	434.1	533.9	680.3	753.6
145°	429.5	451.5	536.6	653.7	712.3
147.5°	447.3	468.7	541.4	626.7	677.4
150°	462.7	477.4	543.1	617.8	653.4
152.5°	474.7	490.2	544.8	605.7	638.8
155°	490.6	502.1	549.5	590.7	614.8
157.5°	510.3	517.2	550.6	583.9	601.1
160°	520.6	525.8	554.8	578.7	593.4
162.5°	526.6	532.6	555.7	574.4	585.7
165°	542.0	544.1	555.9	567.9	576.3
167.5°	552.5	550.6	560.8	566.3	569.6
170°	555.9	554.9	559.1	560.3	564.5
172.5°	563.6	560.1	561.7	558.6	561.9
175°	567.7	564.6	562.3	559.0	554.8
177.5°	569.4	564.4	561.7	558.3	559.1
180°	563.4	563.4	563.4	563.4	563.4

(END OF REPORT)