

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521862

Luminaire Tested: **SQ4-WB-0U-050D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521862
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-0U-050D-92765-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 500 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1743.1 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 20.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521862
CATALOG NUMBER: SQ4-WB-OU-050D-92765-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P521862

CATALOG NUMBER: SQ4-WB-OU-050D-92765-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84		88	85	82		85	83	80	78
3	96	87	81	75	94	86	80	75	83	78	73		80	76	72		78	74	71	69
4	89	79	72	66	87	78	71	66	76	70	65		74	68	64		71	67	64	62
5	83	72	65	59	81	71	64	59	69	63	58		67	62	58		66	61	57	55
6	78	66	59	53	76	65	58	53	64	57	53		62	56	52		61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	48		58	52	47		56	51	47	45
8	68	57	49	44	67	56	49	44	55	48	44		53	48	43		52	47	43	41
9	64	53	45	40	63	52	45	40	51	45	40		50	44	40		49	44	40	38
10	61	49	42	37	60	48	42	37	48	41	37		47	41	37		46	41	37	35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11036	11036	11036
5°	10899	10860	10923
10°	10297	10391	10631
15°	9506	9726	10162
20°	8632	8956	9549
25°	7742	8164	8896
30°	6923	7375	8220
35°	6054	6491	7419
40°	5095	5499	6423
45°	4205	4568	5363
50°	3511	3827	4468
55°	2981	3285	3690
60°	2546	2847	2945
65°	2028	2395	1901
70°	1799	1869	1160
75°	1665	1515	709
80°	1536	1392	611
85°	1387	1281	498



TEST NUMBER: P521862

CATALOG NUMBER: SQ4-WB-OU-050D-92765-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.7	6.3
10°-20°	285.4	16.4
20°-30°	369.7	21.2
30°-40°	362.0	20.8
40°-50°	277.1	15.9
50°-60°	184.6	10.6
60°-70°	100.8	5.8
70°-80°	42.0	2.4
80°-90°	11.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	764.8	43.9
0°-40°	1126.7	64.6
0°-60°	1588.4	91.1
0°-90°	1743.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1743.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1177	1165	1173	1175	1179	109
15°	995	992	1018	1046	1064	278
25°	760	763	802	837	874	350
35°	538	540	576	615	659	334
45°	322	328	350	377	411	251
55°	185	193	204	212	229	168
65°	93	101	110	96	87	97
75°	47	47	42	29	20	50
85°	13	13	12	8	5	15
90°	0	0	0	0	0	



TEST NUMBER: P521862

CATALOG NUMBER: SQ4-WB-OU-050D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1196.2	1196.2	1196.2	1196.2	1196.2
2.5°	1199.1	1188.5	1191.2	1191.1	1187.8
5°	1176.8	1165.0	1172.6	1175.3	1179.4
7.5°	1133.1	1124.2	1138.0	1148.3	1156.6
10°	1099.1	1091.4	1109.1	1124.0	1134.8
12.5°	1059.6	1053.2	1075.0	1095.1	1109.2
15°	995.2	991.6	1018.3	1046.0	1063.9
17.5°	926.2	924.4	955.1	987.4	1010.4
20°	879.2	878.7	912.2	945.9	972.6
22.5°	831.7	832.8	868.1	903.2	933.5
25°	760.5	762.6	802.0	837.0	873.9
27.5°	694.7	695.6	736.4	773.3	812.7
30°	649.8	652.4	692.3	730.5	771.6
32.5°	604.9	607.8	647.0	686.4	728.3
35°	537.5	540.0	576.3	615.1	658.7
37.5°	468.0	471.5	503.7	540.3	583.2
40°	423.0	428.2	456.6	491.2	533.3
42.5°	379.8	386.2	412.6	445.3	483.3
45°	322.3	328.4	350.1	376.6	411.0
47.5°	272.7	279.8	296.4	319.3	348.6
50°	244.6	251.3	266.6	283.5	311.3
52.5°	219.8	226.5	240.2	253.2	276.8
55°	185.3	193.0	204.2	211.9	229.4
57.5°	156.9	164.3	173.2	176.7	187.3
60°	138.0	146.3	154.3	153.9	159.6
62.5°	120.8	127.8	135.8	130.3	130.6
65°	92.9	100.6	109.7	95.9	87.1
67.5°	75.1	76.7	86.1	66.8	56.5
70°	66.7	66.7	69.3	51.8	43.0
72.5°	58.7	58.7	56.3	42.1	33.0
75°	46.7	46.7	42.5	29.2	19.9
77.5°	36.0	35.6	32.5	21.8	14.5
80°	28.9	28.9	26.2	17.2	11.5
82.5°	22.6	22.6	20.4	13.4	8.6
85°	13.1	13.1	12.1	7.8	4.7
87.5°	4.6	4.6	4.2	2.5	2.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)