

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521841

Luminaire Tested: SQ4-WB-075U-100D-92765-1D-UNV-STD-W-4\_6500K

Issue Date: 5-5-2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P521841  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2009-966-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 5-5-2021  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-WB-075U-100D-92765-1D-UNV-STD-W-4\_6500K  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 6500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7175.5 lumens  
Efficiency: N/A  
Efficacy: 109.4 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 65.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P521841

CATALOG NUMBER: SQ4-WB-075U-100D-92765-1D-UNV-STD-W-4\_6500K

### Luminous Intensity Polar Plot



TEST NUMBER: P521841

CATALOG NUMBER: SQ4-WB-075U-100D-92765-1D-UNV-STD-W-4\_6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									70									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51						51													
1	99	95	92	89	92	88	85	83	75	73	71	63	62	61	52	51	51	45						45													
2	91	85	79	75	84	79	74	70	67	64	61	57	55	53	48	46	45	40						40													
3	84	76	69	64	78	70	65	60	61	56	53	52	49	46	43	41	39	35						35													
4	78	68	60	55	72	63	57	52	55	50	46	47	43	41	40	37	35	32						32													
5	72	61	54	48	66	57	51	46	50	45	41	43	39	36	36	34	31	28						28													
6	67	55	48	42	62	52	45	40	45	40	36	39	35	32	33	31	28	26						26													
7	62	50	43	38	57	47	41	36	42	36	33	36	32	29	31	28	26	23						23													
8	58	46	39	34	54	43	37	32	38	33	29	33	29	26	29	26	23	21						21													
9	54	42	35	31	50	40	34	29	35	30	27	31	27	24	27	24	22	20						20													
10	51	39	32	28	47	37	31	27	33	28	24	29	25	22	25	22	20	18						18													

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	23273	23273	23273
5°	22982	22901	23034
10°	21713	21911	22419
15°	20045	20510	21430
20°	18203	18888	20137
25°	16327	17217	18761
30°	14598	15553	17334
35°	12766	13688	15646
40°	10744	11598	13545
45°	8867	9633	11309
50°	7403	8071	9422
55°	6285	6926	7781
60°	5371	6004	6209
65°	4277	5050	4010
70°	3793	3941	2449
75°	3511	3198	1501
80°	3236	2938	1296
85°	2932	2699	1059

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 11309 cd/sqm

TEST NUMBER: P521841

CATALOG NUMBER: SQ4-WB-075U-100D-92765-1D-UNV-STD-W-4\_6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	231.4	3.2
10°-20°	601.8	8.4
20°-30°	779.5	10.9
30°-40°	763.3	10.6
40°-50°	584.3	8.1
50°-60°	389.4	5.4
60°-70°	212.5	3.0
70°-80°	88.5	1.2
80°-90°	25.1	0.3
90°-100°	256.7	3.6
100°-110°	730.5	10.2
110°-120°	699.9	9.8
120°-130°	553.9	7.7
130°-140°	444.6	6.2
140°-150°	348.1	4.9
150°-160°	254.7	3.5
160°-170°	157.8	2.2
170°-180°	53.5	0.7
0°-30°	1612.7	22.5
0°-40°	2376.0	33.1
0°-60°	3349.7	46.7
0°-90°	3675.8	51.2
90°-120°	1687.1	23.5
90°-150°	3033.8	42.3
90°-180°	3500.0	48.8
0°-180°	7175.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2522	2522	2522	2522	2522	
5°	2482	2457	2473	2478	2487	231
15°	2099	2091	2147	2206	2244	586
25°	1604	1608	1691	1765	1843	738
35°	1133	1139	1215	1297	1389	705
45°	680	693	738	794	867	530
55°	391	407	431	447	484	354
65°	196	212	231	202	184	204
75°	98	98	90	62	42	105
85°	28	28	26	16	10	30
90°	0	0	0	0	0	3
95°	28	111	497	172	106	32
105°	114	172	744	1315	1250	120
115°	211	255	564	1196	1404	208
125°	298	330	539	894	1069	267
135°	364	395	532	755	854	281
145°	430	452	537	654	712	268
155°	491	502	550	591	615	227
165°	542	544	556	568	576	152
175°	568	565	562	559	555	54
180°	563	563	563	563	563	

TEST NUMBER: P521841

CATALOG NUMBER: SQ4-WB-075U-100D-92765-1D-UNV-STD-W-4\_6500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2522.5	2522.5	2522.5	2522.5	2522.5
2.5°	2528.7	2506.2	2511.9	2511.7	2504.8
5°	2481.5	2456.7	2472.7	2478.4	2487.1
7.5°	2389.5	2370.6	2399.9	2421.5	2439.0
10°	2317.7	2301.5	2338.8	2370.3	2393.0
12.5°	2234.5	2220.9	2267.0	2309.3	2339.0
15°	2098.6	2091.0	2147.3	2205.7	2243.6
17.5°	1953.1	1949.5	2014.0	2082.2	2130.7
20°	1854.0	1852.9	1923.7	1994.7	2051.0
22.5°	1753.9	1756.3	1830.7	1904.6	1968.6
25°	1603.8	1608.1	1691.3	1765.0	1842.9
27.5°	1465.0	1467.0	1552.9	1630.7	1713.8
30°	1370.3	1375.7	1459.9	1540.5	1627.1
32.5°	1275.5	1281.8	1364.3	1447.5	1535.9
35°	1133.4	1138.8	1215.3	1297.1	1389.1
37.5°	986.9	994.2	1062.1	1139.5	1229.9
40°	892.1	902.9	963.0	1035.8	1124.6
42.5°	800.9	814.3	870.0	939.1	1019.2
45°	679.6	692.6	738.3	794.2	866.7
47.5°	575.1	590.1	625.1	673.3	735.2
50°	515.8	529.9	562.3	597.9	656.4
52.5°	463.5	477.6	506.5	534.0	583.8
55°	390.7	407.0	430.6	446.9	483.7
57.5°	330.9	346.5	365.3	372.6	394.9
60°	291.1	308.4	325.4	324.6	336.5
62.5°	254.8	269.5	286.5	274.7	275.4
65°	195.9	212.1	231.3	202.1	183.7
67.5°	158.3	161.7	181.5	141.0	119.1
70°	140.6	140.6	146.1	109.2	90.8
72.5°	123.7	123.7	118.7	88.8	69.5
75°	98.5	98.5	89.7	61.5	42.1
77.5°	75.9	75.1	68.6	45.9	30.5
80°	60.9	60.9	55.3	36.3	24.4
82.5°	47.6	47.6	42.9	28.3	18.2
85°	27.7	27.7	25.5	16.5	10.0
87.5°	9.7	9.7	8.9	5.3	4.4
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.6	45.4	105.4	30.7	23.1
95°	27.8	110.6	497.0	172.0	106.0
97.5°	51.2	129.5	765.4	547.7	375.3
100°	67.5	140.8	823.7	834.3	642.7
102.5°	85.5	152.9	810.8	1068.0	900.6
105°	113.5	172.2	744.4	1314.9	1250.0
107.5°	142.0	194.6	666.9	1384.6	1442.4
110°	161.7	211.0	622.3	1357.9	1487.8

TEST NUMBER: P521841

CATALOG NUMBER: SQ4-WB-075U-100D-92765-1D-UNV-STD-W-4\_6500K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	180.6	227.3	592.3	1294.9	1480.1
115°	211.0	255.0	564.5	1195.8	1404.3
117.5°	237.8	279.1	548.0	1087.5	1308.3
120°	259.2	293.8	546.3	1025.6	1237.2
122.5°	276.4	310.9	542.0	971.3	1167.7
125°	297.8	330.2	538.8	894.1	1069.0
127.5°	321.1	351.5	537.1	848.0	992.1
130°	333.1	363.5	534.5	815.8	941.5
132.5°	346.0	375.5	534.5	790.8	906.4
135°	364.2	394.6	532.4	755.2	853.7
137.5°	381.3	410.9	532.1	725.2	810.2
140°	394.2	424.5	531.3	700.2	781.9
142.5°	408.7	434.1	533.9	680.3	753.6
145°	429.5	451.5	536.6	653.7	712.3
147.5°	447.3	468.7	541.4	626.7	677.4
150°	462.7	477.4	543.1	617.8	653.4
152.5°	474.7	490.2	544.8	605.7	638.8
155°	490.6	502.1	549.5	590.7	614.8
157.5°	510.3	517.2	550.6	583.9	601.1
160°	520.6	525.8	554.8	578.7	593.4
162.5°	526.6	532.6	555.7	574.4	585.7
165°	542.0	544.1	555.9	567.9	576.3
167.5°	552.5	550.6	560.8	566.3	569.6
170°	555.9	554.9	559.1	560.3	564.5
172.5°	563.6	560.1	561.7	558.6	561.9
175°	567.7	564.6	562.3	559.0	554.8
177.5°	569.4	564.4	561.7	558.3	559.1
180°	563.4	563.4	563.4	563.4	563.4

(END OF REPORT)