

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521865

Luminaire Tested: **SQ4-WB-0U-050D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 5/5/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P521865  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2009-966-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/5/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-WB-0U-050D-92765-1D-UNV-STD-W-4 (5000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 500 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1823.5 lumens  
Efficiency: N/A  
Efficacy: 88.1 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 20.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P521865

CATALOG NUMBER: SQ4-WB-OU-050D-92765-1D-UNV-STD-W-4 (5000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P521865

CATALOG NUMBER: SQ4-WB-OU-050D-92765-1D-UNV-STD-W-4 (5000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89				89
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78				78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69				69
4	89	79	72	66	87	78	71	66	76	70	65	74	68	64	71	67	64	62				62
5	83	72	65	59	81	71	64	59	69	63	58	67	62	58	66	61	57	55				55
6	78	66	59	53	76	65	58	53	64	57	53	62	56	52	61	56	52	50				50
7	73	61	53	48	71	60	53	48	59	52	48	58	52	47	56	51	47	45				45
8	68	57	49	44	67	56	49	44	55	48	44	53	48	43	52	47	43	41				41
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38				38
10	61	49	42	37	60	48	42	37	48	41	37	47	41	37	46	41	37	35				35

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11546	11546	11546
5°	11402	11361	11427
10°	10772	10870	11122
15°	9944	10175	10631
20°	9031	9370	9990
25°	8100	8541	9308
30°	7242	7716	8600
35°	6333	6791	7761
40°	5331	5753	6719
45°	4400	4779	5611
50°	3673	4003	4673
55°	3117	3436	3860
60°	2665	2978	3080
65°	2122	2506	1991
70°	1880	1956	1214
75°	1743	1586	745
80°	1605	1461	643
85°	1450	1334	519



TEST NUMBER: P521865

CATALOG NUMBER: SQ4-WB-OU-050D-92765-1D-UNV-STD-W-4 (5000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	114.8	6.3
10°-20°	298.6	16.4
20°-30°	386.7	21.2
30°-40°	378.7	20.8
40°-50°	289.9	15.9
50°-60°	193.2	10.6
60°-70°	105.4	5.8
70°-80°	43.9	2.4
80°-90°	12.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	800.1	43.9
0°-40°	1178.8	64.6
0°-60°	1661.8	91.1
0°-90°	1823.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1823.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1251	1251	1251	1251	1251	
5°	1231	1219	1227	1230	1234	115
15°	1041	1037	1065	1094	1113	291
25°	796	798	839	876	914	366
35°	562	565	603	644	689	350
45°	337	344	366	394	430	263
55°	194	202	214	222	240	176
65°	97	105	115	100	91	101
75°	49	49	44	30	21	52
85°	14	14	13	8	5	16
90°	0	0	0	0	0	



TEST NUMBER: P521865

CATALOG NUMBER: SQ4-WB-OU-050D-92765-1D-UNV-STD-W-4 (5000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1251.4	1251.4	1251.4	1251.4	1251.4
2.5°	1254.5	1243.3	1246.1	1246.1	1242.6
5°	1231.1	1218.8	1226.7	1229.5	1233.8
7.5°	1185.4	1176.1	1190.6	1201.3	1210.0
10°	1149.8	1141.8	1160.3	1175.9	1187.2
12.5°	1108.5	1101.8	1124.7	1145.7	1160.4
15°	1041.1	1037.3	1065.3	1094.2	1113.0
17.5°	969.0	967.1	999.2	1033.0	1057.0
20°	919.8	919.2	954.3	989.6	1017.5
22.5°	870.1	871.3	908.2	944.9	976.6
25°	795.7	797.8	839.0	875.6	914.3
27.5°	726.8	727.8	770.4	809.0	850.2
30°	679.8	682.5	724.3	764.2	807.2
32.5°	632.8	635.9	676.8	718.1	761.9
35°	562.3	565.0	602.9	643.5	689.1
37.5°	489.6	493.2	526.9	565.3	610.2
40°	442.6	447.9	477.7	513.9	557.9
42.5°	397.3	404.0	431.6	465.9	505.6
45°	337.2	343.6	366.3	394.0	430.0
47.5°	285.3	292.7	310.1	334.0	364.7
50°	255.9	262.9	278.9	296.6	325.6
52.5°	230.0	236.9	251.3	264.9	289.6
55°	193.8	201.9	213.6	221.7	240.0
57.5°	164.2	171.9	181.2	184.9	195.9
60°	144.4	153.0	161.4	161.0	166.9
62.5°	126.4	133.7	142.1	136.3	136.6
65°	97.2	105.2	114.8	100.3	91.2
67.5°	78.5	80.2	90.1	69.9	59.1
70°	69.7	69.7	72.5	54.2	45.0
72.5°	61.4	61.4	58.9	44.0	34.5
75°	48.9	48.9	44.5	30.5	20.9
77.5°	37.7	37.2	34.0	22.8	15.2
80°	30.2	30.2	27.5	18.0	12.1
82.5°	23.6	23.6	21.3	14.1	9.0
85°	13.7	13.7	12.6	8.2	4.9
87.5°	4.8	4.8	4.4	2.6	2.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)