

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521866

Luminaire Tested: **SQ4-WB-0U-050D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521866
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-0U-050D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 500 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1849.5 lumens
Efficiency: N/A
Efficacy: 89.8 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 20.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521866

CATALOG NUMBER: SQ4-WB-OU-050D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P521866

CATALOG NUMBER: SQ4-WB-OU-050D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89				89
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78				78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69				69
4	89	79	72	66	87	78	71	66	76	70	65	74	68	64	71	67	64	62				62
5	83	72	65	59	81	71	64	59	69	63	58	67	62	58	66	61	57	55				55
6	78	66	59	53	76	65	58	53	64	57	53	62	56	52	61	56	52	50				50
7	73	61	53	48	71	60	53	48	59	52	48	58	52	47	56	51	47	45				45
8	68	57	49	44	67	56	49	44	55	48	44	53	48	43	52	47	43	41				41
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38				38
10	61	49	42	37	60	48	42	37	48	41	37	47	41	37	46	41	37	35				35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11710	11710	11710
5°	11564	11523	11590
10°	10926	11025	11281
15°	10086	10320	10783
20°	9160	9503	10133
25°	8215	8663	9440
30°	7346	7826	8722
35°	6423	6887	7872
40°	5407	5835	6814
45°	4462	4847	5690
50°	3725	4061	4741
55°	3162	3484	3915
60°	2703	3021	3124
65°	2153	2541	2019
70°	1907	1983	1233
75°	1768	1608	756
80°	1626	1477	654
85°	1471	1355	529



TEST NUMBER: P521866

CATALOG NUMBER: SQ4-WB-OU-050D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.4	6.3
10°-20°	302.8	16.4
20°-30°	392.2	21.2
30°-40°	384.1	20.8
40°-50°	294.0	15.9
50°-60°	195.9	10.6
60°-70°	106.9	5.8
70°-80°	44.6	2.4
80°-90°	12.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	811.5	43.9
0°-40°	1195.6	64.6
0°-60°	1685.5	91.1
0°-90°	1849.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1849.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1269	1269	1269	1269	1269	
5°	1249	1236	1244	1247	1251	116
15°	1056	1052	1080	1110	1129	295
25°	807	809	851	888	927	371
35°	570	573	612	653	699	355
45°	342	348	372	400	436	267
55°	197	205	217	225	243	178
65°	99	107	116	102	92	102
75°	50	50	45	31	21	53
85°	14	14	13	8	5	16
90°	0	0	0	0	0	



TEST NUMBER: P521866

CATALOG NUMBER: SQ4-WB-OU-050D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1269.2	1269.2	1269.2	1269.2	1269.2
2.5°	1272.4	1261.0	1263.9	1263.8	1260.3
5°	1248.6	1236.1	1244.2	1247.1	1251.4
7.5°	1202.3	1192.8	1207.5	1218.4	1227.2
10°	1166.2	1158.0	1176.8	1192.6	1204.1
12.5°	1124.3	1117.5	1140.7	1162.0	1176.9
15°	1055.9	1052.1	1080.4	1109.8	1128.9
17.5°	982.8	980.9	1013.4	1047.7	1072.1
20°	932.9	932.3	967.9	1003.7	1032.0
22.5°	882.5	883.7	921.2	958.3	990.6
25°	807.0	809.2	851.0	888.1	927.3
27.5°	737.2	738.1	781.4	820.5	862.3
30°	689.5	692.2	734.6	775.1	818.7
32.5°	641.8	645.0	686.5	728.4	772.8
35°	570.3	573.0	611.5	652.7	698.9
37.5°	496.6	500.3	534.4	573.3	618.9
40°	448.9	454.3	484.5	521.2	565.8
42.5°	403.0	409.7	437.7	472.5	512.8
45°	342.0	348.5	371.5	399.6	436.1
47.5°	289.4	296.9	314.6	338.8	369.9
50°	259.5	266.6	282.9	300.9	330.3
52.5°	233.2	240.3	254.9	268.7	293.7
55°	196.6	204.8	216.6	224.9	243.4
57.5°	166.5	174.4	183.8	187.5	198.7
60°	146.5	155.2	163.7	163.3	169.3
62.5°	128.2	135.6	144.1	138.2	138.6
65°	98.6	106.7	116.4	101.7	92.5
67.5°	79.6	81.4	91.3	70.9	59.9
70°	70.7	70.7	73.5	54.9	45.7
72.5°	62.3	62.3	59.7	44.7	35.0
75°	49.6	49.6	45.1	31.0	21.2
77.5°	38.2	37.8	34.5	23.1	15.4
80°	30.6	30.6	27.8	18.2	12.3
82.5°	23.9	23.9	21.6	14.3	9.1
85°	13.9	13.9	12.8	8.3	5.0
87.5°	4.9	4.9	4.5	2.7	2.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)