

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521888

Luminaire Tested: **SQ4-WB-0U-100D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521888
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-0U-100D-92765-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3431.6 lumens
Efficiency: N/A
Efficacy: 80.9 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 42.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521888

CATALOG NUMBER: SQ4-WB-OU-100D-92765-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P521888

CATALOG NUMBER: SQ4-WB-OU-100D-92765-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89				
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78				
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69				
4	89	79	72	66	87	78	71	66	76	70	65	74	68	64	71	67	64	62				
5	83	72	65	59	81	71	64	59	69	63	58	67	62	58	66	61	57	55				
6	78	66	59	53	76	65	58	53	64	57	53	62	56	52	61	56	52	50				
7	73	61	53	48	71	60	53	48	59	52	48	58	52	47	56	51	47	45				
8	68	57	49	44	67	56	49	44	55	48	44	53	48	43	52	47	43	41				
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38				
10	61	49	42	37	60	48	42	37	48	41	37	47	41	37	46	41	37	35				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21728	21728	21728
5°	21457	21380	21504
10°	20272	20456	20930
15°	18714	19148	20007
20°	16994	17633	18800
25°	15242	16073	17515
30°	13629	14521	16183
35°	11918	12779	14606
40°	10031	10828	12645
45°	8279	8993	10557
50°	6911	7534	8796
55°	5868	6466	7264
60°	5015	5606	5796
65°	3993	4716	3744
70°	3539	3679	2285
75°	3280	2984	1401
80°	3018	2747	1206
85°	2731	2519	984



TEST NUMBER: P521888

CATALOG NUMBER: SQ4-WB-OU-100D-92765-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	216.0	6.3
10°-20°	561.8	16.4
20°-30°	727.8	21.2
30°-40°	712.7	20.8
40°-50°	545.5	15.9
50°-60°	363.5	10.6
60°-70°	198.4	5.8
70°-80°	82.7	2.4
80°-90°	23.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1505.6	43.9
0°-40°	2218.3	64.6
0°-60°	3127.2	91.1
0°-90°	3431.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3431.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2355	2355	2355	2355	2355	
5°	2317	2294	2308	2314	2322	216
15°	1959	1952	2005	2059	2095	547
25°	1497	1501	1579	1648	1720	689
35°	1058	1063	1135	1211	1297	658
45°	634	647	689	741	809	495
55°	365	380	402	417	452	331
65°	183	198	216	189	172	190
75°	92	92	84	58	39	98
85°	26	26	24	15	9	29
90°	0	0	0	0	0	



TEST NUMBER: P521888

CATALOG NUMBER: SQ4-WB-OU-100D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2355.0	2355.0	2355.0	2355.0	2355.0
2.5°	2360.8	2339.8	2345.1	2344.9	2338.5
5°	2316.8	2293.5	2308.5	2313.8	2321.9
7.5°	2230.8	2213.2	2240.5	2260.7	2277.1
10°	2163.8	2148.7	2183.5	2212.9	2234.1
12.5°	2086.1	2073.4	2116.5	2156.0	2183.7
15°	1959.2	1952.1	2004.7	2059.2	2094.6
17.5°	1823.4	1820.0	1880.3	1943.9	1989.2
20°	1730.8	1729.8	1795.9	1862.2	1914.8
22.5°	1637.4	1639.7	1709.1	1778.1	1837.9
25°	1497.3	1501.4	1578.9	1647.8	1720.5
27.5°	1367.7	1369.6	1449.8	1522.4	1600.0
30°	1279.3	1284.3	1363.0	1438.2	1519.0
32.5°	1190.8	1196.7	1273.7	1351.4	1433.9
35°	1058.1	1063.2	1134.6	1211.0	1296.8
37.5°	921.3	928.2	991.6	1063.8	1148.3
40°	832.9	843.0	899.0	967.0	1049.9
42.5°	747.7	760.3	812.2	876.7	951.5
45°	634.5	646.6	689.2	741.4	809.1
47.5°	536.9	550.9	583.6	628.6	686.3
50°	481.5	494.7	524.9	558.2	612.8
52.5°	432.8	445.9	472.9	498.5	545.0
55°	364.8	379.9	402.0	417.2	451.6
57.5°	309.0	323.5	341.0	347.9	368.7
60°	271.8	287.9	303.8	303.0	314.1
62.5°	237.9	251.6	267.4	256.5	257.1
65°	182.9	198.1	216.0	188.7	171.5
67.5°	147.8	151.0	169.5	131.6	111.2
70°	131.2	131.2	136.4	101.9	84.7
72.5°	115.5	115.5	110.8	82.9	64.9
75°	92.0	92.0	83.7	57.5	39.3
77.5°	70.9	70.1	64.1	42.9	28.5
80°	56.8	56.8	51.7	33.8	22.7
82.5°	44.4	44.4	40.1	26.4	16.9
85°	25.8	25.8	23.8	15.4	9.3
87.5°	9.1	9.1	8.3	4.9	4.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)