

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521867

Luminaire Tested: SQ4-WB-0U-050D-92765-1D-UNV-STD-W-4_6500K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P521867
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-WB-0U-050D-92765-1D-UNV-STD-W-4_6500K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 500 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 6500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1867.1 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 20.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P521867

CATALOG NUMBER: SQ4-WB-0U-050D-92765-1D-UNV-STD-W-4_6500K

Luminous Intensity Polar Plot



TEST NUMBER: P521867

CATALOG NUMBER: SQ4-WB-OU-050D-92765-1D-UNV-STD-W-4_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69
4	89	79	72	66	87	78	71	66	76	70	65	74	68	64	71	67	64	62
5	83	72	65	59	81	71	64	59	69	63	58	67	62	58	66	61	57	55
6	78	66	59	53	76	65	58	53	64	57	53	62	56	52	61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	48	58	52	47	56	51	47	45
8	68	57	49	44	67	56	49	44	55	48	44	53	48	43	52	47	43	41
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38
10	61	49	42	37	60	48	42	37	48	41	37	47	41	37	46	41	37	35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11822	11822	11822
5°	11674	11632	11700
10°	11030	11130	11387
15°	10182	10418	10885
20°	9246	9593	10229
25°	8293	8746	9529
30°	7415	7901	8804
35°	6484	6953	7947
40°	5457	5891	6880
45°	4504	4893	5744
50°	3761	4099	4785
55°	3193	3518	3952
60°	2729	3050	3154
65°	2172	2565	2037
70°	1926	2002	1244
75°	1782	1622	763
80°	1642	1493	659
85°	1493	1366	540

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 5744 cd/sqm

TEST NUMBER: P521867

CATALOG NUMBER: SQ4-WB-OU-050D-92765-1D-UNV-STD-W-4_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.5	6.3
10°-20°	305.7	16.4
20°-30°	395.9	21.2
30°-40°	387.7	20.8
40°-50°	296.8	15.9
50°-60°	197.8	10.6
60°-70°	107.9	5.8
70°-80°	45.0	2.4
80°-90°	12.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	819.2	43.9
0°-40°	1206.9	64.6
0°-60°	1701.4	91.1
0°-90°	1867.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1867.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1281	1281	1281	1281	1281	
5°	1260	1248	1256	1259	1263	117
15°	1066	1062	1091	1120	1140	298
25°	815	817	859	896	936	375
35°	576	578	617	659	706	358
45°	345	352	375	403	440	269
55°	198	207	219	227	246	180
65°	100	108	118	103	93	103
75°	50	50	46	31	21	53
85°	14	14	13	8	5	16
90°	0	0	0	0	0	

TEST NUMBER: P521867

CATALOG NUMBER: SQ4-WB-OU-050D-92765-1D-UNV-STD-W-4_6500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1281.3	1281.3	1281.3	1281.3	1281.3
2.5°	1284.4	1273.0	1275.9	1275.8	1272.3
5°	1260.5	1247.8	1256.0	1258.9	1263.3
7.5°	1213.7	1204.1	1219.0	1230.0	1238.9
10°	1177.3	1169.0	1188.0	1204.0	1215.5
12.5°	1135.0	1128.1	1151.5	1173.0	1188.1
15°	1066.0	1062.1	1090.7	1120.4	1139.6
17.5°	992.1	990.2	1023.0	1057.6	1082.3
20°	941.7	941.2	977.1	1013.2	1041.8
22.5°	890.9	892.1	929.9	967.4	999.9
25°	814.6	816.8	859.1	896.5	936.1
27.5°	744.1	745.1	788.8	828.3	870.5
30°	696.0	698.8	741.6	782.5	826.4
32.5°	647.9	651.1	693.0	735.3	780.1
35°	575.7	578.5	617.3	658.8	705.6
37.5°	501.3	505.0	539.5	578.8	624.7
40°	453.1	458.6	489.1	526.1	571.2
42.5°	406.8	413.6	441.9	477.0	517.7
45°	345.2	351.8	375.0	403.4	440.2
47.5°	292.1	299.7	317.5	342.0	373.4
50°	262.0	269.1	285.6	303.7	333.4
52.5°	235.5	242.6	257.3	271.2	296.5
55°	198.5	206.7	218.7	227.0	245.7
57.5°	168.1	176.0	185.5	189.3	200.6
60°	147.9	156.7	165.3	164.9	170.9
62.5°	129.4	136.9	145.5	139.5	139.9
65°	99.5	107.8	117.5	102.7	93.3
67.5°	80.4	82.2	92.2	71.6	60.5
70°	71.4	71.4	74.2	55.4	46.1
72.5°	62.9	62.9	60.3	45.1	35.3
75°	50.0	50.0	45.5	31.3	21.4
77.5°	38.6	38.1	34.9	23.3	15.5
80°	30.9	30.9	28.1	18.4	12.4
82.5°	24.2	24.2	21.8	14.4	9.2
85°	14.1	14.1	12.9	8.4	5.1
87.5°	4.9	4.9	4.5	2.7	2.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)