

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521903

Luminaire Tested: **SQ4-WB-0U-125D-92765-1D-UNV-STD-W-4 (4500K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521903
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-0U-125D-92765-1D-UNV-STD-W-4 (4500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4495.6 lumens
Efficiency: N/A
Efficacy: 80.7 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 55.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521903

CATALOG NUMBER: SQ4-WB-0U-125D-92765-1D-UNV-STD-W-4 (4500K)

Luminous Intensity Polar Plot





TEST NUMBER: P521903

CATALOG NUMBER: SQ4-WB-OU-125D-92765-1D-UNV-STD-W-4 (4500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89				
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78				
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69				
4	89	79	72	66	87	78	71	66	76	70	65	74	68	64	71	67	64	62				
5	83	72	65	59	81	71	64	59	69	63	58	67	62	58	66	61	57	55				
6	78	66	59	53	76	65	58	53	64	57	53	62	56	52	61	56	52	50				
7	73	61	53	48	71	60	53	48	59	52	48	58	52	47	56	51	47	45				
8	68	57	49	44	67	56	49	44	55	48	44	53	48	43	52	47	43	41				
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38				
10	61	49	42	37	60	48	42	37	48	41	37	47	41	37	46	41	37	35				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	28464	28464	28464
5°	28108	28008	28171
10°	26557	26798	27419
15°	24515	25085	26210
20°	22263	23100	24628
25°	19968	21057	22945
30°	17854	19022	21200
35°	15613	16741	19135
40°	13141	14184	16565
45°	10845	11781	13831
50°	9054	9871	11523
55°	7687	8471	9516
60°	6569	7344	7593
65°	5231	6176	4905
70°	4637	4821	2994
75°	4296	3911	1832
80°	3958	3597	1583
85°	3578	3292	1291



TEST NUMBER: P521903

CATALOG NUMBER: SQ4-WB-OU-125D-92765-1D-UNV-STD-W-4 (4500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	283.0	6.3
10°-20°	736.0	16.4
20°-30°	953.4	21.2
30°-40°	933.6	20.8
40°-50°	714.6	15.9
50°-60°	476.2	10.6
60°-70°	259.8	5.8
70°-80°	108.3	2.4
80°-90°	30.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1972.4	43.9
0°-40°	2906.0	64.6
0°-60°	4096.8	91.1
0°-90°	4495.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4495.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3085	3085	3085	3085	3085	
5°	3035	3005	3024	3031	3042	282
15°	2567	2557	2626	2698	2744	717
25°	1962	1967	2068	2159	2254	902
35°	1386	1393	1486	1586	1699	862
45°	831	847	903	971	1060	648
55°	478	498	527	547	592	433
65°	240	260	283	247	225	249
75°	120	120	110	75	51	129
85°	34	34	31	20	12	38
90°	0	0	0	0	0	



TEST NUMBER: P521903

CATALOG NUMBER: SQ4-WB-OU-125D-92765-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3085.1	3085.1	3085.1	3085.1	3085.1
2.5°	3092.7	3065.2	3072.1	3071.9	3063.4
5°	3035.0	3004.6	3024.2	3031.2	3041.8
7.5°	2922.4	2899.4	2935.1	2961.6	2983.0
10°	2834.7	2814.8	2860.4	2898.9	2926.7
12.5°	2732.9	2716.2	2772.7	2824.4	2860.7
15°	2566.6	2557.4	2626.2	2697.6	2744.0
17.5°	2388.8	2384.3	2463.2	2546.6	2605.9
20°	2267.5	2266.1	2352.7	2439.6	2508.4
22.5°	2145.1	2148.0	2239.0	2329.4	2407.7
25°	1961.5	1966.8	2068.5	2158.6	2253.9
27.5°	1791.8	1794.2	1899.3	1994.4	2096.1
30°	1675.9	1682.5	1785.5	1884.1	1990.0
32.5°	1560.0	1567.7	1668.6	1770.4	1878.4
35°	1386.2	1392.8	1486.4	1586.4	1698.9
37.5°	1207.0	1216.0	1299.0	1393.6	1504.2
40°	1091.1	1104.3	1177.7	1266.8	1375.4
42.5°	979.5	996.0	1064.0	1148.5	1246.5
45°	831.2	847.1	902.9	971.3	1060.0
47.5°	703.4	721.7	764.6	823.4	899.1
50°	630.8	648.0	687.7	731.3	802.8
52.5°	566.9	584.1	619.5	653.1	713.9
55°	477.9	497.7	526.6	546.6	591.6
57.5°	404.8	423.8	446.7	455.7	483.0
60°	356.0	377.2	398.0	397.0	411.5
62.5°	311.6	329.6	350.3	336.0	336.8
65°	239.6	259.5	282.9	247.2	224.7
67.5°	193.6	197.8	222.0	172.4	145.7
70°	171.9	171.9	178.7	133.5	111.0
72.5°	151.3	151.3	145.1	108.6	85.0
75°	120.5	120.5	109.7	75.3	51.4
77.5°	92.9	91.8	83.9	56.2	37.4
80°	74.5	74.5	67.7	44.3	29.8
82.5°	58.2	58.2	52.5	34.6	22.2
85°	33.8	33.8	31.1	20.1	12.2
87.5°	11.9	11.9	10.8	6.5	5.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)