

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521893

Luminaire Tested: SQ4-WB-0U-100D-92765-1D-UNV-STD-W-4_6500K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P521893
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-WB-0U-100D-92765-1D-UNV-STD-W-4_6500K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 6500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3675.8 lumens
Efficiency: N/A
Efficacy: 87.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 42.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P521893

CATALOG NUMBER: SQ4-WB-0U-100D-92765-1D-UNV-STD-W-4_6500K

Luminous Intensity Polar Plot



TEST NUMBER: P521893

CATALOG NUMBER: SQ4-WB-OU-100D-92765-1D-UNV-STD-W-4_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69
4	89	79	72	66	87	78	71	66	76	70	65	74	68	64	71	67	64	62
5	83	72	65	59	81	71	64	59	69	63	58	67	62	58	66	61	57	55
6	78	66	59	53	76	65	58	53	64	57	53	62	56	52	61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	48	58	52	47	56	51	47	45
8	68	57	49	44	67	56	49	44	55	48	44	53	48	43	52	47	43	41
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38
10	61	49	42	37	60	48	42	37	48	41	37	47	41	37	46	41	37	35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23273	23273	23273
5°	22982	22901	23034
10°	21713	21911	22419
15°	20045	20510	21430
20°	18203	18888	20137
25°	16327	17217	18761
30°	14598	15553	17334
35°	12766	13688	15646
40°	10744	11598	13545
45°	8867	9633	11309
50°	7403	8071	9422
55°	6285	6926	7781
60°	5371	6004	6209
65°	4277	5050	4010
70°	3793	3941	2449
75°	3511	3198	1501
80°	3236	2938	1296
85°	2932	2699	1059

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 11309 cd/sqm

TEST NUMBER: P521893

CATALOG NUMBER: SQ4-WB-OU-100D-92765-1D-UNV-STD-W-4_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	231.4	6.3
10°-20°	601.8	16.4
20°-30°	779.5	21.2
30°-40°	763.3	20.8
40°-50°	584.3	15.9
50°-60°	389.4	10.6
60°-70°	212.5	5.8
70°-80°	88.5	2.4
80°-90°	25.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1612.7	43.9
0°-40°	2376.0	64.6
0°-60°	3349.7	91.1
0°-90°	3675.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3675.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2522	2522	2522	2522	2522	
5°	2482	2457	2473	2478	2487	231
15°	2099	2091	2147	2206	2244	586
25°	1604	1608	1691	1765	1843	738
35°	1133	1139	1215	1297	1389	705
45°	680	693	738	794	867	530
55°	391	407	431	447	484	354
65°	196	212	231	202	184	204
75°	98	98	90	62	42	105
85°	28	28	26	16	10	31
90°	0	0	0	0	0	

TEST NUMBER: P521893

CATALOG NUMBER: SQ4-WB-OU-100D-92765-1D-UNV-STD-W-4_6500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2522.5	2522.5	2522.5	2522.5	2522.5
2.5°	2528.7	2506.2	2511.9	2511.7	2504.8
5°	2481.5	2456.7	2472.7	2478.4	2487.1
7.5°	2389.5	2370.6	2399.9	2421.5	2439.0
10°	2317.7	2301.5	2338.8	2370.3	2393.0
12.5°	2234.5	2220.9	2267.0	2309.3	2339.0
15°	2098.6	2091.0	2147.3	2205.7	2243.6
17.5°	1953.1	1949.5	2014.0	2082.2	2130.7
20°	1854.0	1852.9	1923.7	1994.7	2051.0
22.5°	1753.9	1756.3	1830.7	1904.6	1968.6
25°	1603.8	1608.1	1691.3	1765.0	1842.9
27.5°	1465.0	1467.0	1552.9	1630.7	1713.8
30°	1370.3	1375.7	1459.9	1540.5	1627.1
32.5°	1275.5	1281.8	1364.3	1447.5	1535.9
35°	1133.4	1138.8	1215.3	1297.1	1389.1
37.5°	986.9	994.2	1062.1	1139.5	1229.9
40°	892.1	902.9	963.0	1035.8	1124.6
42.5°	800.9	814.3	870.0	939.1	1019.2
45°	679.6	692.6	738.3	794.2	866.7
47.5°	575.1	590.1	625.1	673.3	735.2
50°	515.8	529.9	562.3	597.9	656.4
52.5°	463.5	477.6	506.5	534.0	583.8
55°	390.7	407.0	430.6	446.9	483.7
57.5°	330.9	346.5	365.3	372.6	394.9
60°	291.1	308.4	325.4	324.6	336.5
62.5°	254.8	269.5	286.5	274.7	275.4
65°	195.9	212.1	231.3	202.1	183.7
67.5°	158.3	161.7	181.5	141.0	119.1
70°	140.6	140.6	146.1	109.2	90.8
72.5°	123.7	123.7	118.7	88.8	69.5
75°	98.5	98.5	89.7	61.5	42.1
77.5°	75.9	75.1	68.6	45.9	30.5
80°	60.9	60.9	55.3	36.3	24.4
82.5°	47.6	47.6	42.9	28.3	18.2
85°	27.7	27.7	25.5	16.5	10.0
87.5°	9.7	9.7	8.9	5.3	4.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)