

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521901

Luminaire Tested: **SQ4-WB-0U-125D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521901
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-0U-125D-92765-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4344.7 lumens
Efficiency: N/A
Efficacy: 77.9 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 55.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521901

CATALOG NUMBER: SQ4-WB-0U-125D-92765-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P521901

CATALOG NUMBER: SQ4-WB-OU-125D-92765-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84		88	85	82		85	83	80	78
3	96	87	81	75	94	86	80	75	83	78	73		80	76	72		78	74	71	69
4	89	79	72	66	87	78	71	66	76	70	65		74	68	64		71	67	64	62
5	83	72	65	59	81	71	64	59	69	63	58		67	62	58		66	61	57	55
6	78	66	59	53	76	65	58	53	64	57	53		62	56	52		61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	48		58	52	47		56	51	47	45
8	68	57	49	44	67	56	49	44	55	48	44		53	48	43		52	47	43	41
9	64	53	45	40	63	52	45	40	51	45	40		50	44	40		49	44	40	38
10	61	49	42	37	60	48	42	37	48	41	37		47	41	37		46	41	37	35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27509	27509	27509
5°	27166	27068	27226
10°	25666	25898	26499
15°	23693	24243	25330
20°	21516	22325	23803
25°	19298	20351	22175
30°	17255	18384	20489
35°	15089	16179	18493
40°	12700	13708	16009
45°	10481	11386	13366
50°	8751	9539	11135
55°	7428	8186	9196
60°	6349	7097	7339
65°	5056	5969	4742
70°	4483	4659	2894
75°	4149	3779	1772
80°	3825	3475	1530
85°	3462	3186	1249



TEST NUMBER: P521901

CATALOG NUMBER: SQ4-WB-OU-125D-92765-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	273.5	6.3
10°-20°	711.3	16.4
20°-30°	921.4	21.2
30°-40°	902.3	20.8
40°-50°	690.6	15.9
50°-60°	460.2	10.6
60°-70°	251.1	5.8
70°-80°	104.6	2.4
80°-90°	29.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1906.2	43.9
0°-40°	2808.5	64.6
0°-60°	3959.3	91.1
0°-90°	4344.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4344.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2982	2982	2982	2982	2982	
5°	2933	2904	2923	2930	2940	273
15°	2480	2472	2538	2607	2652	693
25°	1896	1901	1999	2086	2178	872
35°	1340	1346	1436	1533	1642	833
45°	803	819	873	939	1024	626
55°	462	481	509	528	572	419
65°	232	251	273	239	217	241
75°	116	116	106	73	50	124
85°	33	33	30	19	12	37
90°	0	0	0	0	0	



TEST NUMBER: P521901

CATALOG NUMBER: SQ4-WB-OU-125D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2981.6	2981.6	2981.6	2981.6	2981.6
2.5°	2988.9	2962.3	2969.0	2968.8	2960.7
5°	2933.2	2903.8	2922.7	2929.5	2939.7
7.5°	2824.3	2802.1	2836.6	2862.2	2882.9
10°	2739.6	2720.4	2764.4	2801.7	2828.5
12.5°	2641.2	2625.0	2679.6	2729.6	2764.7
15°	2480.5	2471.6	2538.1	2607.1	2651.9
17.5°	2308.6	2304.3	2380.6	2461.1	2518.5
20°	2191.4	2190.1	2273.8	2357.7	2424.3
22.5°	2073.1	2075.9	2163.9	2251.2	2326.9
25°	1895.7	1900.8	1999.1	2086.2	2178.3
27.5°	1731.6	1733.9	1835.5	1927.5	2025.7
30°	1619.7	1626.1	1725.6	1820.8	1923.2
32.5°	1507.7	1515.1	1612.6	1711.0	1815.4
35°	1339.7	1346.1	1436.5	1533.2	1641.9
37.5°	1166.5	1175.2	1255.4	1346.8	1453.8
40°	1054.5	1067.3	1138.2	1224.3	1329.2
42.5°	946.7	962.5	1028.3	1110.0	1204.7
45°	803.3	818.6	872.6	938.7	1024.4
47.5°	679.8	697.4	738.9	795.8	869.0
50°	609.7	626.3	664.6	706.7	775.8
52.5°	547.9	564.5	598.7	631.1	690.0
55°	461.8	481.0	508.9	528.2	571.7
57.5°	391.2	409.6	431.7	440.4	466.8
60°	344.1	364.5	384.6	383.6	397.7
62.5°	301.2	318.6	338.6	324.7	325.5
65°	231.6	250.8	273.4	238.9	217.2
67.5°	187.1	191.2	214.6	166.6	140.8
70°	166.2	166.2	172.7	129.0	107.3
72.5°	146.3	146.3	140.2	104.9	82.2
75°	116.4	116.4	106.0	72.7	49.7
77.5°	89.7	88.7	81.1	54.3	36.1
80°	72.0	72.0	65.4	42.9	28.8
82.5°	56.3	56.3	50.8	33.5	21.5
85°	32.7	32.7	30.1	19.4	11.8
87.5°	11.5	11.5	10.5	6.3	5.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)