

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521926

Luminaire Tested: SQ4-WB-100U-075D-92765-1D-UNV-STD-W-4_3000K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P521926
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-WB-100U-075D-92765-1D-UNV-STD-W-4_3000K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6819.3 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 64.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P521926

CATALOG NUMBER: SQ4-WB-100U-075D-92765-1D-UNV-STD-W-4_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P521926

CATALOG NUMBER: SQ4-WB-100U-075D-92765-1D-UNV-STD-W-4_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	37				
1	96	92	88	85	87	84	81	78	68	66	64	54	53	51	41	40	39	33				
2	88	81	76	71	80	74	69	65	61	57	55	48	46	44	37	36	34	29				
3	81	72	66	60	73	66	60	56	54	50	47	44	41	39	33	32	30	26				
4	74	64	57	52	67	59	53	48	49	44	41	39	36	34	31	29	27	23				
5	69	58	50	45	62	53	47	42	44	39	36	36	32	30	28	26	24	21				
6	63	52	45	39	58	48	42	37	40	35	32	33	29	27	26	23	22	19				
7	59	47	40	35	53	44	37	33	37	32	28	30	27	24	24	21	20	17				
8	55	43	36	31	50	40	34	29	34	29	25	28	24	22	22	20	18	16				
9	51	40	33	28	47	37	30	26	31	26	23	26	22	20	21	18	16	14				
10	48	36	30	25	44	34	28	24	29	24	21	24	20	18	19	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16141	16141	16141
5°	15940	15882	15975
10°	15060	15196	15549
15°	13902	14224	14862
20°	12624	13100	13967
25°	11323	11941	13011
30°	10124	10787	12021
35°	8854	9494	10851
40°	7452	8044	9393
45°	6149	6680	7843
50°	5134	5598	6534
55°	4359	4803	5397
60°	3726	4165	4307
65°	2967	3502	2781
70°	2630	2733	1697
75°	2435	2217	1041
80°	2242	2040	898
85°	2032	1874	730

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7843 cd/sqm

TEST NUMBER: P521926

CATALOG NUMBER: SQ4-WB-100U-075D-92765-1D-UNV-STD-W-4_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.5	2.4
10°-20°	417.4	6.1
20°-30°	540.6	7.9
30°-40°	529.4	7.8
40°-50°	405.2	5.9
50°-60°	270.0	4.0
60°-70°	147.4	2.2
70°-80°	61.4	0.9
80°-90°	17.4	0.3
90°-100°	313.2	4.6
100°-110°	891.3	13.1
110°-120°	853.9	12.5
120°-130°	675.9	9.9
130°-140°	542.5	8.0
140°-150°	424.7	6.2
150°-160°	310.7	4.6
160°-170°	192.5	2.8
170°-180°	65.3	1.0
0°-30°	1118.5	16.4
0°-40°	1647.9	24.2
0°-60°	2323.1	34.1
0°-90°	2549.3	37.4
90°-120°	2058.5	30.2
90°-150°	3701.5	54.3
90°-180°	4270.0	62.6
0°-180°	6819.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1750	1750	1750	1750	1750	
5°	1721	1704	1715	1719	1725	160
15°	1456	1450	1489	1530	1556	406
25°	1112	1115	1173	1224	1278	512
35°	786	790	843	900	963	489
45°	471	480	512	551	601	368
55°	271	282	299	310	336	246
65°	136	147	160	140	127	141
75°	68	68	62	43	29	73
85°	19	19	18	11	7	21
90°	0	0	0	0	0	2
95°	34	135	606	210	129	39
105°	138	210	908	1604	1525	147
115°	258	311	689	1459	1713	253
125°	363	403	657	1091	1304	325
135°	444	481	650	922	1042	343
145°	524	551	655	798	869	327
155°	599	613	670	721	750	277
165°	661	664	678	693	703	186
175°	693	689	686	682	677	66
180°	687	687	687	687	687	

TEST NUMBER: P521926

CATALOG NUMBER: SQ4-WB-100U-075D-92765-1D-UNV-STD-W-4_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1749.5	1749.5	1749.5	1749.5	1749.5
2.5°	1753.8	1738.2	1742.1	1742.0	1737.2
5°	1721.1	1703.8	1714.9	1718.9	1724.9
7.5°	1657.2	1644.1	1664.4	1679.4	1691.6
10°	1607.5	1596.2	1622.0	1643.9	1659.7
12.5°	1549.7	1540.3	1572.3	1601.6	1622.2
15°	1455.5	1450.2	1489.2	1529.8	1556.0
17.5°	1354.6	1352.0	1396.8	1444.1	1477.7
20°	1285.8	1285.1	1334.2	1383.4	1422.5
22.5°	1216.4	1218.1	1269.7	1320.9	1365.3
25°	1112.3	1115.3	1173.0	1224.1	1278.1
27.5°	1016.1	1017.4	1077.0	1131.0	1188.6
30°	950.3	954.1	1012.5	1068.4	1128.4
32.5°	884.6	889.0	946.2	1003.9	1065.2
35°	786.1	789.8	842.9	899.6	963.4
37.5°	684.4	689.5	736.6	790.3	853.0
40°	618.7	626.2	667.9	718.4	779.9
42.5°	555.5	564.8	603.4	651.3	706.9
45°	471.3	480.3	512.0	550.8	601.1
47.5°	398.9	409.2	433.6	466.9	509.9
50°	357.7	367.5	390.0	414.7	455.2
52.5°	321.5	331.2	351.3	370.3	404.9
55°	271.0	282.2	298.6	309.9	335.5
57.5°	229.5	240.3	253.3	258.4	273.9
60°	201.9	213.9	225.7	225.1	233.4
62.5°	176.7	186.9	198.7	190.5	191.0
65°	135.9	147.1	160.4	140.2	127.4
67.5°	109.8	112.2	125.9	97.8	82.6
70°	97.5	97.5	101.3	75.7	62.9
72.5°	85.8	85.8	82.3	61.6	48.2
75°	68.3	68.3	62.2	42.7	29.2
77.5°	52.7	52.1	47.6	31.8	21.2
80°	42.2	42.2	38.4	25.1	16.9
82.5°	33.0	33.0	29.8	19.6	12.6
85°	19.2	19.2	17.7	11.4	6.9
87.5°	6.8	6.8	6.1	3.7	3.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	10.5	55.4	128.6	37.4	28.2
95°	34.0	134.9	606.4	209.9	129.4
97.5°	62.5	158.1	933.9	668.3	457.9
100°	82.3	171.8	1005.0	1018.0	784.1
102.5°	104.3	186.6	989.3	1303.0	1098.8
105°	138.5	210.1	908.3	1604.4	1525.1
107.5°	173.3	237.4	813.7	1689.3	1759.9
110°	197.3	257.4	759.3	1656.8	1815.3

TEST NUMBER: P521926

CATALOG NUMBER: SQ4-WB-100U-075D-92765-1D-UNV-STD-W-4_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	220.3	277.3	722.7	1579.9	1805.9
115°	257.5	311.1	688.7	1459.0	1713.3
117.5°	290.1	340.5	668.6	1326.9	1596.2
120°	316.3	358.4	666.5	1251.3	1509.5
122.5°	337.2	379.3	661.3	1185.0	1424.8
125°	363.3	402.9	657.4	1090.9	1304.3
127.5°	391.8	428.9	655.3	1034.6	1210.4
130°	406.4	443.5	652.1	995.4	1148.8
132.5°	422.1	458.2	652.1	964.8	1105.9
135°	444.3	481.4	649.5	921.5	1041.6
137.5°	465.3	501.3	649.3	884.8	988.5
140°	480.9	518.0	648.2	854.4	954.0
142.5°	498.7	529.6	651.4	830.1	919.5
145°	524.1	550.9	654.8	797.5	869.1
147.5°	545.8	571.8	660.5	764.6	826.5
150°	564.6	582.5	662.6	753.8	797.2
152.5°	579.2	598.1	664.7	739.0	779.4
155°	598.6	612.6	670.4	720.8	750.2
157.5°	622.6	631.0	671.7	712.5	733.4
160°	635.1	641.5	677.0	706.1	724.0
162.5°	642.5	649.9	678.0	700.8	714.6
165°	661.3	663.8	678.3	692.9	703.1
167.5°	674.1	671.8	684.3	690.9	695.0
170°	678.3	677.0	682.2	683.6	688.7
172.5°	687.7	683.3	685.3	681.5	685.6
175°	692.7	688.8	686.1	682.1	677.0
177.5°	694.7	688.6	685.3	681.2	682.2
180°	687.4	687.4	687.4	687.4	687.4

(END OF REPORT)