

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521977

Luminaire Tested: **SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521977
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (2700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7751.8 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 73.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521977
CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (2700K)

Luminous Intensity Polar Plot





TEST NUMBER: P521977

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (2700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20									
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0				
RCR																									
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32							
1	95	91	87	84	85	82	79	76	65	63	62	50	49	48	36	36	35	29							
2	87	80	74	70	78	72	68	64	58	55	52	45	43	41	33	32	31	25							
3	80	71	64	59	72	64	59	54	52	48	45	40	38	36	30	28	27	22							
4	73	63	56	51	66	57	51	47	47	42	39	37	34	31	27	25	24	20							
5	67	57	49	44	61	52	45	40	42	37	34	33	30	28	25	23	21	18							
6	62	51	44	38	56	47	40	35	38	33	30	30	27	25	23	21	19	16							
7	58	46	39	34	52	42	36	31	35	30	27	28	24	22	21	19	17	15							
8	54	42	35	30	48	39	32	28	32	27	24	26	22	20	20	17	16	13							
9	50	39	32	27	45	35	29	25	29	25	21	24	20	18	18	16	14	12							
10	47	35	29	24	42	33	27	23	27	23	19	22	19	16	17	15	13	11							

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15813	15813	15813
5°	15616	15560	15651
10°	14754	14888	15233
15°	13620	13936	14561
20°	12368	12834	13683
25°	11093	11699	12747
30°	9919	10568	11777
35°	8674	9301	10630
40°	7301	7880	9203
45°	6025	6545	7684
50°	5031	5483	6402
55°	4271	4707	5287
60°	3650	4080	4218
65°	2906	3432	2725
70°	2576	2679	1664
75°	2385	2171	1020
80°	2200	1998	877
85°	1990	1831	720



TEST NUMBER: P521977

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (2700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.2	2.0
10°-20°	408.9	5.3
20°-30°	529.7	6.8
30°-40°	518.7	6.7
40°-50°	397.0	5.1
50°-60°	264.5	3.4
60°-70°	144.4	1.9
70°-80°	60.1	0.8
80°-90°	17.0	0.2
90°-100°	385.4	5.0
100°-110°	1096.7	14.1
110°-120°	1050.8	13.6
120°-130°	831.6	10.7
130°-140°	667.5	8.6
140°-150°	522.6	6.7
150°-160°	382.4	4.9
160°-170°	236.8	3.1
170°-180°	80.4	1.0
0°-30°	1095.8	14.1
0°-40°	1614.4	20.8
0°-60°	2276.0	29.4
0°-90°	2497.5	32.2
90°-120°	2532.9	32.7
90°-150°	4554.7	58.8
90°-180°	5254.0	67.8
0°-180°	7751.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1714	1714	1714	1714	1714	
5°	1686	1669	1680	1684	1690	157
15°	1426	1421	1459	1499	1524	398
25°	1090	1093	1149	1199	1252	501
35°	770	774	826	881	944	479
45°	462	471	502	540	589	360
55°	266	276	293	304	329	241
65°	133	144	157	137	125	138
75°	67	67	61	42	29	71
85°	19	19	17	11	7	20
90°	0	0	0	0	0	3
95°	42	166	746	258	159	48
105°	170	258	1118	1974	1877	180
115°	317	383	848	1795	2108	312
125°	447	496	809	1342	1605	400
135°	547	592	799	1134	1282	422
145°	645	678	806	981	1069	403
155°	736	754	825	887	923	340
165°	814	817	835	853	865	229
175°	852	848	844	839	833	81
180°	846	846	846	846	846	

TEST NUMBER: P521977

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1713.9	1713.9	1713.9	1713.9	1713.9
2.5°	1718.2	1702.9	1706.7	1706.6	1701.9
5°	1686.1	1669.2	1680.1	1684.0	1689.9
7.5°	1623.6	1610.8	1630.6	1645.3	1657.2
10°	1574.8	1563.8	1589.1	1610.5	1626.0
12.5°	1518.3	1509.0	1540.4	1569.1	1589.3
15°	1425.9	1420.8	1459.0	1498.7	1524.4
17.5°	1327.1	1324.6	1368.5	1414.8	1447.7
20°	1259.7	1259.0	1307.1	1355.3	1393.6
22.5°	1191.7	1193.3	1243.9	1294.1	1337.6
25°	1089.7	1092.7	1149.2	1199.2	1252.2
27.5°	995.4	996.8	1055.1	1108.0	1164.5
30°	931.1	934.7	992.0	1046.7	1105.5
32.5°	866.7	870.9	927.0	983.6	1043.6
35°	770.1	773.8	825.8	881.3	943.8
37.5°	670.5	675.5	721.7	774.2	835.7
40°	606.2	613.5	654.3	703.8	764.1
42.5°	544.2	553.3	591.1	638.1	692.5
45°	461.8	470.6	501.6	539.6	588.9
47.5°	390.8	400.9	424.8	457.5	499.5
50°	350.5	360.0	382.0	406.3	446.0
52.5°	315.0	324.5	344.1	362.8	396.6
55°	265.5	276.5	292.6	303.6	328.7
57.5°	224.9	235.5	248.2	253.2	268.3
60°	197.8	209.6	221.1	220.5	228.6
62.5°	173.1	183.1	194.6	186.7	187.1
65°	133.1	144.1	157.2	137.3	124.8
67.5°	107.5	109.9	123.3	95.8	80.9
70°	95.5	95.5	99.3	74.2	61.7
72.5°	84.1	84.1	80.6	60.3	47.2
75°	66.9	66.9	60.9	41.8	28.6
77.5°	51.6	51.0	46.6	31.2	20.8
80°	41.4	41.4	37.6	24.6	16.5
82.5°	32.3	32.3	29.2	19.2	12.3
85°	18.8	18.8	17.3	11.2	6.8
87.5°	6.6	6.6	6.0	3.6	3.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	12.9	68.2	158.2	46.1	34.7
95°	41.8	166.0	746.2	258.3	159.2
97.5°	76.9	194.5	1149.2	822.3	563.5
100°	101.3	211.4	1236.6	1252.6	964.9
102.5°	128.3	229.6	1217.3	1603.4	1352.1
105°	170.5	258.5	1117.6	1974.1	1876.7
107.5°	213.2	292.2	1001.2	2078.7	2165.5
110°	242.8	316.7	934.3	2038.7	2233.7



TEST NUMBER: P521977

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	271.1	341.3	889.3	1944.1	2222.1
115°	316.8	382.8	847.5	1795.3	2108.2
117.5°	357.0	419.0	822.7	1632.7	1964.1
120°	389.2	441.0	820.1	1539.7	1857.4
122.5°	414.9	466.8	813.7	1458.2	1753.2
125°	447.1	495.8	808.9	1342.3	1604.9
127.5°	482.1	527.7	806.3	1273.1	1489.4
130°	500.1	545.7	802.4	1224.8	1413.5
132.5°	519.4	563.8	802.4	1187.2	1360.8
135°	546.8	592.4	799.2	1133.9	1281.7
137.5°	572.5	616.8	798.9	1088.7	1216.4
140°	591.8	637.4	797.6	1051.3	1173.9
142.5°	613.7	651.7	801.5	1021.4	1131.5
145°	644.8	677.9	805.7	981.3	1069.4
147.5°	671.5	703.6	812.7	940.9	1017.0
150°	694.7	716.7	815.3	927.5	980.9
152.5°	712.7	736.0	817.9	909.4	959.1
155°	736.5	753.8	825.0	886.9	923.1
157.5°	766.1	776.5	826.6	876.7	902.5
160°	781.5	789.4	833.0	868.9	890.9
162.5°	790.5	799.7	834.3	862.3	879.3
165°	813.7	816.8	834.6	852.6	865.2
167.5°	829.5	826.6	842.0	850.2	855.2
170°	834.6	833.0	839.4	841.2	847.5
172.5°	846.2	840.8	843.3	838.6	843.6
175°	852.3	847.6	844.3	839.3	833.0
177.5°	854.9	847.3	843.3	838.2	839.4
180°	845.9	845.9	845.9	845.9	845.9

(END OF REPORT)