

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521964

Luminaire Tested: **SQ4-WB-125U-050D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 5/5/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P521964  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,  
Test Lab: INNOVATION CENTER  
Issue Date: 5/5/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-WB-125U-050D-92765-1D-UNV-STD-W-4 (2700K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6921.9 lumens  
Efficiency: N/A  
Efficacy: 111.6 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 62  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P521964  
CATALOG NUMBER: SQ4-WB-125U-050D-92765-1D-UNV-STD-W-4 (2700K)

### Luminous Intensity Polar Plot





TEST NUMBER: P521964

CATALOG NUMBER: SQ4-WB-125U-050D-92765-1D-UNV-STD-W-4 (2700K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	93	89	85	82	82	79	76	73	61	59	57	45	43	42	29	29	28	21
2	85	78	72	68	75	70	65	61	54	51	48	40	38	36	27	26	25	19
3	78	69	62	57	69	62	56	52	48	44	41	36	33	31	24	23	22	17
4	71	61	54	49	63	55	49	44	43	39	36	32	29	27	22	20	19	15
5	65	55	47	42	58	49	43	38	39	34	31	29	26	24	20	18	17	13
6	60	49	42	36	54	44	38	33	35	31	27	26	23	21	18	17	15	12
7	56	44	37	32	50	40	34	29	32	27	24	24	21	19	17	15	14	11
8	52	40	33	28	46	37	30	26	29	25	21	22	19	17	16	14	13	10
9	48	37	30	25	43	33	27	23	27	22	19	20	17	15	15	13	11	9
10	45	34	27	23	40	31	25	21	25	20	17	19	16	14	14	12	11	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10558	10558	10558
5°	10427	10389	10451
10°	9851	9941	10171
15°	9094	9305	9723
20°	8258	8569	9136
25°	7407	7811	8511
30°	6623	7057	7864
35°	5791	6210	7098
40°	4874	5262	6145
45°	4023	4370	5130
50°	3359	3662	4274
55°	2852	3141	3529
60°	2438	2724	2818
65°	1941	2292	1821
70°	1721	1788	1111
75°	1593	1451	681
80°	1466	1334	584
85°	1334	1217	476



TEST NUMBER: P521964

CATALOG NUMBER: SQ4-WB-125U-050D-92765-1D-UNV-STD-W-4 (2700K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	105.0	1.5
10°-20°	273.0	3.9
20°-30°	353.7	5.1
30°-40°	346.3	5.0
40°-50°	265.1	3.8
50°-60°	176.6	2.6
60°-70°	96.4	1.4
70°-80°	40.2	0.6
80°-90°	11.4	0.2
90°-100°	385.4	5.6
100°-110°	1096.7	15.8
110°-120°	1050.8	15.2
120°-130°	831.6	12.0
130°-140°	667.5	9.6
140°-150°	522.6	7.5
150°-160°	382.4	5.5
160°-170°	236.8	3.4
170°-180°	80.4	1.2
0°-30°	731.7	10.6
0°-40°	1078.0	15.6
0°-60°	1519.7	22.0
0°-90°	1667.7	24.1
90°-120°	2532.9	36.6
90°-150°	4554.7	65.8
90°-180°	5254.0	75.9
0°-180°	6921.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1144	1144	1144	1144	1144	
5°	1126	1115	1122	1124	1128	105
15°	952	949	974	1001	1018	266
25°	728	730	767	801	836	335
35°	514	517	551	588	630	320
45°	308	314	335	360	393	240
55°	177	185	195	203	219	161
65°	89	96	105	92	83	92
75°	45	45	41	28	19	48
85°	13	13	12	8	4	14
90°	0	0	0	0	0	2
95°	42	166	746	258	159	48
105°	170	258	1118	1974	1877	180
115°	317	383	848	1795	2108	312
125°	447	496	809	1342	1605	400
135°	547	592	799	1134	1282	422
145°	645	678	806	981	1069	403
155°	736	754	825	887	923	340
165°	814	817	835	853	865	229
175°	852	848	844	839	833	81
180°	846	846	846	846	846	



TEST NUMBER: P521964

CATALOG NUMBER: SQ4-WB-125U-050D-92765-1D-UNV-STD-W-4 (2700K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1144.4	1144.4	1144.4	1144.4	1144.4
2.5°	1147.3	1137.0	1139.6	1139.5	1136.4
5°	1125.9	1114.6	1121.8	1124.4	1128.4
7.5°	1084.1	1075.5	1088.8	1098.6	1106.6
10°	1051.5	1044.2	1061.1	1075.4	1085.7
12.5°	1013.8	1007.6	1028.5	1047.7	1061.2
15°	952.1	948.7	974.2	1000.7	1017.9
17.5°	886.1	884.5	913.7	944.7	966.7
20°	841.1	840.6	872.8	905.0	930.5
22.5°	795.7	796.8	830.6	864.1	893.2
25°	727.6	729.6	767.3	800.8	836.1
27.5°	664.7	665.6	704.5	739.8	777.6
30°	621.7	624.1	662.4	698.9	738.2
32.5°	578.7	581.5	619.0	656.7	696.8
35°	514.2	516.7	551.4	588.5	630.2
37.5°	447.7	451.1	481.9	517.0	558.0
40°	404.7	409.7	436.9	469.9	510.2
42.5°	363.4	369.5	394.7	426.1	462.4
45°	308.3	314.2	334.9	360.3	393.2
47.5°	260.9	267.7	283.6	305.5	333.5
50°	234.0	240.4	255.1	271.3	297.8
52.5°	210.3	216.7	229.8	242.3	264.8
55°	177.3	184.6	195.3	202.8	219.4
57.5°	150.1	157.2	165.7	169.1	179.2
60°	132.1	139.9	147.6	147.3	152.7
62.5°	115.6	122.3	130.0	124.6	124.9
65°	88.9	96.2	105.0	91.7	83.4
67.5°	71.8	73.4	82.4	64.0	54.0
70°	63.8	63.8	66.3	49.5	41.2
72.5°	56.1	56.1	53.8	40.3	31.5
75°	44.7	44.7	40.7	27.9	19.1
77.5°	34.4	34.1	31.1	20.8	13.9
80°	27.6	27.6	25.1	16.4	11.0
82.5°	21.6	21.6	19.5	12.9	8.2
85°	12.6	12.6	11.5	7.5	4.5
87.5°	4.4	4.4	4.0	2.4	2.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	12.9	68.2	158.2	46.1	34.7
95°	41.8	166.0	746.2	258.3	159.2
97.5°	76.9	194.5	1149.2	822.3	563.5
100°	101.3	211.4	1236.6	1252.6	964.9
102.5°	128.3	229.6	1217.3	1603.4	1352.1
105°	170.5	258.5	1117.6	1974.1	1876.7
107.5°	213.2	292.2	1001.2	2078.7	2165.5
110°	242.8	316.7	934.3	2038.7	2233.7

TEST NUMBER: P521964

CATALOG NUMBER: SQ4-WB-125U-050D-92765-1D-UNV-STD-W-4 (2700K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	271.1	341.3	889.3	1944.1	2222.1
115°	316.8	382.8	847.5	1795.3	2108.2
117.5°	357.0	419.0	822.7	1632.7	1964.1
120°	389.2	441.0	820.1	1539.7	1857.4
122.5°	414.9	466.8	813.7	1458.2	1753.2
125°	447.1	495.8	808.9	1342.3	1604.9
127.5°	482.1	527.7	806.3	1273.1	1489.4
130°	500.1	545.7	802.4	1224.8	1413.5
132.5°	519.4	563.8	802.4	1187.2	1360.8
135°	546.8	592.4	799.2	1133.9	1281.7
137.5°	572.5	616.8	798.9	1088.7	1216.4
140°	591.8	637.4	797.6	1051.3	1173.9
142.5°	613.7	651.7	801.5	1021.4	1131.5
145°	644.8	677.9	805.7	981.3	1069.4
147.5°	671.5	703.6	812.7	940.9	1017.0
150°	694.7	716.7	815.3	927.5	980.9
152.5°	712.7	736.0	817.9	909.4	959.1
155°	736.5	753.8	825.0	886.9	923.1
157.5°	766.1	776.5	826.6	876.7	902.5
160°	781.5	789.4	833.0	868.9	890.9
162.5°	790.5	799.7	834.3	862.3	879.3
165°	813.7	816.8	834.6	852.6	865.2
167.5°	829.5	826.6	842.0	850.2	855.2
170°	834.6	833.0	839.4	841.2	847.5
172.5°	846.2	840.8	843.3	838.6	843.6
175°	852.3	847.6	844.3	839.3	833.0
177.5°	854.9	847.3	843.3	838.2	839.4
180°	845.9	845.9	845.9	845.9	845.9

(END OF REPORT)