

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521980

Luminaire Tested: **SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 5/5/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P521980  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,  
Test Lab: INNOVATION CENTER  
Issue Date: 5/5/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (4000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8250.5 lumens  
Efficiency: N/A  
Efficacy: 112.4 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 73.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P521980  
CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (4000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P521980

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (4000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32				
1	95	91	87	84	85	82	79	76	65	63	62	50	49	48	36	36	35	29				
2	87	80	74	70	78	72	68	64	58	55	52	45	43	41	33	32	31	25				
3	80	71	64	59	72	64	59	54	52	48	45	40	38	36	30	28	27	22				
4	73	63	56	51	66	57	51	47	47	42	39	37	34	31	27	25	24	20				
5	67	57	49	44	61	52	45	40	42	37	34	33	30	28	25	23	21	18				
6	62	51	44	38	56	47	40	35	38	33	30	30	27	25	23	21	19	16				
7	58	46	39	34	52	42	36	31	35	30	27	28	24	22	21	19	17	15				
8	54	42	35	30	48	39	32	28	32	27	24	26	22	20	20	17	16	13				
9	50	39	32	27	45	35	29	25	29	25	21	24	20	18	18	16	14	12				
10	47	35	29	24	42	33	27	23	27	23	19	22	19	16	17	15	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16830	16830	16830
5°	16621	16561	16658
10°	15703	15845	16213
15°	14497	14833	15498
20°	13164	13659	14563
25°	11808	12451	13567
30°	10558	11248	12536
35°	9232	9899	11315
40°	7771	8387	9795
45°	6413	6966	8178
50°	5354	5836	6814
55°	4546	5009	5627
60°	3884	4342	4489
65°	3093	3652	2901
70°	2743	2851	1770
75°	2538	2310	1084
80°	2338	2125	935
85°	2117	1948	762



TEST NUMBER: P521980

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (4000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	167.3	2.0
10°-20°	435.2	5.3
20°-30°	563.7	6.8
30°-40°	552.0	6.7
40°-50°	422.6	5.1
50°-60°	281.6	3.4
60°-70°	153.7	1.9
70°-80°	64.0	0.8
80°-90°	18.1	0.2
90°-100°	410.2	5.0
100°-110°	1167.3	14.1
110°-120°	1118.4	13.6
120°-130°	885.2	10.7
130°-140°	710.5	8.6
140°-150°	556.2	6.7
150°-160°	407.0	4.9
160°-170°	252.1	3.1
170°-180°	85.5	1.0
0°-30°	1166.3	14.1
0°-40°	1718.3	20.8
0°-60°	2422.4	29.4
0°-90°	2658.2	32.2
90°-120°	2695.9	32.7
90°-150°	4847.7	58.8
90°-180°	5592.0	67.8
0°-180°	8250.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1824	1824	1824	1824	1824	
5°	1795	1777	1788	1792	1799	167
15°	1518	1512	1553	1595	1622	424
25°	1160	1163	1223	1276	1333	533
35°	820	824	879	938	1005	510
45°	492	501	534	574	627	383
55°	283	294	311	323	350	256
65°	142	153	167	146	133	147
75°	71	71	65	44	30	76
85°	20	20	18	12	7	22
90°	0	0	0	0	0	3
95°	44	177	794	275	169	51
105°	181	275	1190	2101	1997	192
115°	337	408	902	1911	2244	332
125°	476	528	861	1429	1708	426
135°	582	630	851	1207	1364	449
145°	686	722	858	1044	1138	429
155°	784	802	878	944	982	362
165°	866	869	888	907	921	244
175°	907	902	899	893	887	86
180°	900	900	900	900	900	

TEST NUMBER: P521980

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (4000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1824.2	1824.2	1824.2	1824.2	1824.2
2.5°	1828.7	1812.4	1816.5	1816.4	1811.4
5°	1794.6	1776.6	1788.2	1792.3	1798.6
7.5°	1728.0	1714.4	1735.5	1751.2	1763.9
10°	1676.1	1664.4	1691.3	1714.1	1730.6
12.5°	1615.9	1606.1	1639.5	1670.1	1691.5
15°	1517.7	1512.2	1552.9	1595.1	1622.5
17.5°	1412.5	1409.8	1456.5	1505.8	1540.9
20°	1340.8	1340.0	1391.2	1442.5	1483.2
22.5°	1268.4	1270.1	1323.9	1377.3	1423.7
25°	1159.9	1163.0	1223.1	1276.4	1332.7
27.5°	1059.5	1060.9	1123.0	1179.3	1239.4
30°	991.0	994.9	1055.8	1114.0	1176.7
32.5°	922.4	927.0	986.6	1046.8	1110.7
35°	819.7	823.6	878.9	938.0	1004.6
37.5°	713.7	719.0	768.1	824.0	889.5
40°	645.2	653.0	696.4	749.1	813.3
42.5°	579.2	588.9	629.2	679.1	737.1
45°	491.5	500.9	533.9	574.3	626.8
47.5°	415.9	426.7	452.1	486.9	531.7
50°	373.0	383.2	406.6	432.4	474.7
52.5°	335.2	345.4	366.3	386.2	422.2
55°	282.6	294.3	311.4	323.2	349.8
57.5°	239.3	250.6	264.1	269.5	285.6
60°	210.5	223.0	235.3	234.7	243.3
62.5°	184.3	194.9	207.2	198.7	199.2
65°	141.7	153.4	167.3	146.2	132.9
67.5°	114.5	117.0	131.3	101.9	86.1
70°	101.7	101.7	105.7	78.9	65.6
72.5°	89.5	89.5	85.8	64.2	50.3
75°	71.2	71.2	64.8	44.5	30.4
77.5°	54.9	54.3	49.6	33.2	22.1
80°	44.0	44.0	40.0	26.2	17.6
82.5°	34.4	34.4	31.1	20.5	13.1
85°	20.0	20.0	18.4	11.9	7.2
87.5°	7.0	7.0	6.4	3.8	3.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.7	72.6	168.4	49.0	37.0
95°	44.5	176.7	794.2	274.9	169.4
97.5°	81.8	207.0	1223.1	875.2	599.7
100°	107.8	225.0	1316.2	1333.2	1026.9
102.5°	136.6	244.4	1295.7	1706.5	1439.1
105°	181.4	275.1	1189.5	2101.2	1997.4
107.5°	227.0	311.0	1065.6	2212.4	2304.8
110°	258.4	337.1	994.4	2169.9	2377.4



TEST NUMBER: P521980

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (4000K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	288.6	363.2	946.5	2069.2	2365.0
115°	337.2	407.5	902.0	1910.8	2243.9
117.5°	380.0	445.9	875.6	1737.7	2090.5
120°	414.2	469.4	872.9	1638.8	1976.9
122.5°	441.6	496.8	866.1	1552.0	1866.0
125°	475.8	527.7	860.9	1428.7	1708.1
127.5°	513.1	561.7	858.2	1355.0	1585.3
130°	532.3	580.8	854.1	1303.6	1504.5
132.5°	552.8	600.0	854.1	1263.6	1448.3
135°	581.9	630.5	850.7	1206.8	1364.1
137.5°	609.3	656.5	850.3	1158.7	1294.6
140°	629.9	678.4	848.9	1118.9	1249.4
142.5°	653.1	693.6	853.0	1087.1	1204.3
145°	686.3	721.5	857.5	1044.5	1138.2
147.5°	714.8	748.9	865.0	1001.4	1082.4
150°	739.4	762.8	867.8	987.2	1044.1
152.5°	758.6	783.3	870.5	967.9	1020.8
155°	783.9	802.3	878.0	943.9	982.4
157.5°	815.4	826.4	879.7	933.1	960.5
160°	831.8	840.2	886.6	924.8	948.2
162.5°	841.4	851.1	888.0	917.8	935.9
165°	866.1	869.4	888.3	907.4	920.8
167.5°	882.8	879.8	896.2	904.9	910.2
170°	888.3	886.6	893.4	895.3	902.0
172.5°	900.6	894.9	897.5	892.5	897.9
175°	907.1	902.1	898.6	893.3	886.6
177.5°	909.9	901.8	897.5	892.1	893.4
180°	900.3	900.3	900.3	900.3	900.3

(END OF REPORT)