

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521984

Luminaire Tested: **SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (6500K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521984
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (6500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 6500K CCT
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8678.6 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 72.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521984
CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (6500K)

Luminous Intensity Polar Plot





TEST NUMBER: P521984

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (6500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32				
1	95	91	87	84	85	82	79	76	65	63	62	50	49	48	36	36	35	29				
2	87	80	74	70	78	72	68	64	58	55	52	45	43	41	33	32	31	25				
3	80	71	64	59	72	64	59	54	52	48	45	40	38	36	30	28	27	22				
4	73	63	56	51	66	57	51	47	47	42	39	37	34	31	27	25	24	20				
5	67	57	49	44	61	52	45	40	42	37	34	33	30	28	25	23	21	18				
6	62	51	44	38	56	47	40	35	38	33	30	30	27	25	23	21	19	16				
7	58	46	39	34	52	42	36	31	35	30	27	28	24	22	21	19	17	15				
8	54	42	35	30	48	39	32	28	32	27	24	26	22	20	20	17	16	13				
9	50	39	32	27	45	35	29	25	29	25	21	24	20	18	18	16	14	12				
10	47	35	29	24	42	33	27	23	27	23	19	22	19	16	17	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17704	17704	17704
5°	17483	17421	17522
10°	16518	16668	17054
15°	15248	15602	16302
20°	13847	14368	15319
25°	12420	13098	14271
30°	11105	11832	13186
35°	9711	10413	11902
40°	8173	8822	10304
45°	6746	7328	8602
50°	5632	6139	7167
55°	4781	5268	5918
60°	4085	4567	4724
65°	3253	3842	3052
70°	2884	2997	1861
75°	2670	2431	1141
80°	2460	2237	983
85°	2223	2054	805



TEST NUMBER: P521984

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (6500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.0	2.0
10°-20°	457.8	5.3
20°-30°	593.0	6.8
30°-40°	580.7	6.7
40°-50°	444.5	5.1
50°-60°	296.2	3.4
60°-70°	161.6	1.9
70°-80°	67.3	0.8
80°-90°	19.1	0.2
90°-100°	431.5	5.0
100°-110°	1227.8	14.1
110°-120°	1176.4	13.6
120°-130°	931.1	10.7
130°-140°	747.3	8.6
140°-150°	585.1	6.7
150°-160°	428.1	4.9
160°-170°	265.2	3.1
170°-180°	90.0	1.0
0°-30°	1226.8	14.1
0°-40°	1807.5	20.8
0°-60°	2548.1	29.4
0°-90°	2796.1	32.2
90°-120°	2835.8	32.7
90°-150°	5099.2	58.8
90°-180°	5882.0	67.8
0°-180°	8678.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1919	1919	1919	1919	1919	
5°	1888	1869	1881	1885	1892	176
15°	1596	1591	1633	1678	1707	446
25°	1220	1223	1287	1343	1402	561
35°	862	866	924	987	1057	536
45°	517	527	562	604	659	403
55°	297	310	328	340	368	269
65°	149	161	176	154	140	155
75°	75	75	68	47	32	80
85°	21	21	19	12	8	23
90°	0	0	0	0	0	3
95°	47	186	835	289	178	54
105°	191	289	1251	2210	2101	202
115°	355	429	949	2010	2360	349
125°	500	555	906	1503	1797	448
135°	612	663	895	1269	1435	472
145°	722	759	902	1099	1197	451
155°	825	844	924	993	1033	381
165°	911	914	934	954	969	256
175°	954	949	945	940	933	90
180°	947	947	947	947	947	



TEST NUMBER: P521984

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1918.9	1918.9	1918.9	1918.9	1918.9
2.5°	1923.6	1906.5	1910.8	1910.7	1905.4
5°	1887.7	1868.8	1881.0	1885.4	1891.9
7.5°	1817.7	1803.3	1825.6	1842.1	1855.4
10°	1763.1	1750.8	1779.1	1803.1	1820.4
12.5°	1699.8	1689.4	1724.6	1756.7	1779.3
15°	1596.4	1590.6	1633.4	1677.9	1706.7
17.5°	1485.8	1483.0	1532.1	1583.9	1620.8
20°	1410.3	1409.5	1463.4	1517.4	1560.2
22.5°	1334.2	1336.0	1392.6	1448.8	1497.6
25°	1220.0	1223.3	1286.6	1342.6	1401.9
27.5°	1114.4	1115.9	1181.3	1240.5	1303.7
30°	1042.4	1046.5	1110.6	1171.9	1237.7
32.5°	970.3	975.1	1037.8	1101.2	1168.3
35°	862.2	866.3	924.5	986.7	1056.7
37.5°	750.7	756.3	808.0	866.8	935.6
40°	678.6	686.9	732.5	787.9	855.5
42.5°	609.3	619.5	661.8	714.4	775.3
45°	517.0	526.9	561.6	604.1	659.3
47.5°	437.5	448.9	475.6	512.2	559.2
50°	392.4	403.1	427.7	454.8	499.3
52.5°	352.6	363.3	385.3	406.2	444.1
55°	297.2	309.6	327.5	340.0	367.9
57.5°	251.8	263.6	277.9	283.5	300.4
60°	221.4	234.6	247.5	246.9	256.0
62.5°	193.8	205.0	217.9	209.0	209.5
65°	149.0	161.4	176.0	153.8	139.8
67.5°	120.4	123.0	138.1	107.2	90.6
70°	106.9	106.9	111.1	83.0	69.0
72.5°	94.1	94.1	90.3	67.5	52.9
75°	74.9	74.9	68.2	46.8	32.0
77.5°	57.8	57.1	52.2	34.9	23.2
80°	46.3	46.3	42.1	27.6	18.5
82.5°	36.2	36.2	32.7	21.5	13.8
85°	21.0	21.0	19.4	12.5	7.6
87.5°	7.4	7.4	6.7	4.0	3.4
90°	0.0	0.0	0.0	0.0	0.0
92.5°	14.4	76.4	177.2	51.6	38.9
95°	46.8	185.9	835.4	289.1	178.2
97.5°	86.1	217.7	1286.6	920.6	630.9
100°	113.4	236.6	1384.5	1402.4	1080.2
102.5°	143.7	257.0	1362.9	1795.1	1513.8
105°	190.8	289.4	1251.3	2210.2	2101.0
107.5°	238.7	327.1	1120.9	2327.2	2424.4
110°	271.9	354.6	1046.0	2282.4	2500.7



TEST NUMBER: P521984

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	303.5	382.1	995.6	2176.5	2487.8
115°	354.7	428.6	948.8	2010.0	2360.3
117.5°	399.7	469.0	921.1	1827.9	2199.0
120°	435.7	493.8	918.2	1723.8	2079.4
122.5°	464.5	522.6	911.0	1632.5	1962.8
125°	500.5	555.1	905.6	1502.8	1796.8
127.5°	539.8	590.8	902.7	1425.3	1667.5
130°	559.9	611.0	898.4	1371.3	1582.5
132.5°	581.5	631.2	898.4	1329.1	1523.5
135°	612.1	663.2	894.8	1269.4	1434.9
137.5°	640.9	690.6	894.4	1218.9	1361.8
140°	662.5	713.6	893.0	1177.0	1314.3
142.5°	687.0	729.6	897.3	1143.5	1266.7
145°	722.0	758.9	902.0	1098.7	1197.3
147.5°	751.8	787.8	909.9	1053.4	1138.6
150°	777.8	802.4	912.8	1038.4	1098.2
152.5°	797.9	824.0	915.7	1018.1	1073.7
155°	824.6	843.9	923.6	992.9	1033.4
157.5°	857.7	869.3	925.4	981.5	1010.4
160°	875.0	883.8	932.6	972.8	997.4
162.5°	885.1	895.3	934.0	965.4	984.4
165°	911.0	914.5	934.4	954.5	968.6
167.5°	928.6	925.5	942.7	951.8	957.4
170°	934.4	932.6	939.8	941.8	948.8
172.5°	947.4	941.4	944.1	938.8	944.5
175°	954.2	948.9	945.2	939.6	932.6
177.5°	957.1	948.6	944.1	938.4	939.8
180°	947.0	947.0	947.0	947.0	947.0

(END OF REPORT)