

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521995

Luminaire Tested: **SQ4-WB-125U-100D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521995
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-125U-100D-92765-1D-UNV-STD-W-4 (5000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9335.5 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 83.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521995

CATALOG NUMBER: SQ4-WB-125U-100D-92765-1D-UNV-STD-W-4 (5000K)

Luminous Intensity Polar Plot





TEST NUMBER: P521995

CATALOG NUMBER: SQ4-WB-125U-100D-92765-1D-UNV-STD-W-4 (5000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	38
1	96	92	89	86	87	84	81	78	69	67	65	55	53	52	42	41	40	34
2	88	82	76	71	80	74	70	66	61	58	55	49	47	45	38	36	35	30
3	81	72	66	61	74	66	61	56	55	51	47	44	41	39	34	33	31	27
4	75	65	57	52	68	59	53	48	49	45	41	40	37	34	31	29	28	24
5	69	58	51	45	63	53	47	42	45	40	36	36	33	30	29	26	25	21
6	64	52	45	40	58	48	42	37	41	36	32	33	30	27	26	24	22	19
7	59	48	40	35	54	44	37	33	37	32	29	30	27	24	24	22	20	17
8	55	43	36	31	50	40	34	29	34	29	26	28	25	22	23	20	18	16
9	51	40	33	28	47	37	31	26	31	27	23	26	23	20	21	19	17	15
10	48	37	30	25	44	34	28	24	29	24	21	24	21	18	20	17	15	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22731	22731	22731
5°	22447	22367	22497
10°	21208	21401	21896
15°	19578	20032	20931
20°	17779	18448	19668
25°	15946	16815	18324
30°	14258	15191	16929
35°	12468	13369	15281
40°	10494	11327	13228
45°	8661	9409	11045
50°	7231	7883	9202
55°	6138	6764	7599
60°	5246	5864	6063
65°	4176	4932	3919
70°	3704	3849	2390
75°	3429	3123	1465
80°	3161	2874	1265
85°	2858	2636	1027



TEST NUMBER: P521995

CATALOG NUMBER: SQ4-WB-125U-100D-92765-1D-UNV-STD-W-4 (5000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	226.0	2.4
10°-20°	587.8	6.3
20°-30°	761.4	8.2
30°-40°	745.6	8.0
40°-50°	570.7	6.1
50°-60°	380.3	4.1
60°-70°	207.5	2.2
70°-80°	86.5	0.9
80°-90°	24.5	0.3
90°-100°	421.5	4.5
100°-110°	1199.2	12.8
110°-120°	1149.0	12.3
120°-130°	909.4	9.7
130°-140°	729.9	7.8
140°-150°	571.4	6.1
150°-160°	418.1	4.5
160°-170°	259.0	2.8
170°-180°	87.9	0.9
0°-30°	1575.1	16.9
0°-40°	2320.7	24.9
0°-60°	3271.6	35.0
0°-90°	3590.1	38.5
90°-120°	2769.7	29.7
90°-150°	4980.4	53.3
90°-180°	5745.0	61.5
0°-180°	9335.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2464	2464	2464	2464	2464	
5°	2424	2399	2415	2421	2429	225
15°	2050	2042	2097	2154	2191	572
25°	1566	1571	1652	1724	1800	720
35°	1107	1112	1187	1267	1357	688
45°	664	676	721	776	846	518
55°	382	398	420	436	472	346
65°	191	207	226	197	180	199
75°	96	96	88	60	41	103
85°	27	27	25	16	10	29
90°	0	0	0	0	0	3
95°	46	182	816	282	174	52
105°	186	283	1222	2159	2052	197
115°	346	419	927	1963	2305	341
125°	489	542	884	1468	1755	438
135°	598	648	874	1240	1402	461
145°	705	741	881	1073	1169	440
155°	805	824	902	970	1009	372
165°	890	893	913	932	946	250
175°	932	927	923	918	911	88
180°	925	925	925	925	925	

TEST NUMBER: P521995

CATALOG NUMBER: SQ4-WB-125U-100D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2463.7	2463.7	2463.7	2463.7	2463.7
2.5°	2469.8	2447.8	2453.3	2453.2	2446.4
5°	2423.7	2399.4	2415.1	2420.7	2429.1
7.5°	2333.8	2315.4	2343.9	2365.1	2382.2
10°	2263.7	2247.9	2284.3	2315.0	2337.2
12.5°	2182.4	2169.1	2214.2	2255.5	2284.5
15°	2049.7	2042.3	2097.2	2154.3	2191.3
17.5°	1907.6	1904.0	1967.1	2033.7	2081.0
20°	1810.8	1809.7	1878.9	1948.2	2003.2
22.5°	1713.0	1715.4	1788.1	1860.2	1922.8
25°	1566.4	1570.7	1651.8	1723.8	1800.0
27.5°	1430.9	1432.8	1516.7	1592.7	1673.9
30°	1338.3	1343.6	1425.9	1504.6	1589.1
32.5°	1245.8	1251.9	1332.5	1413.8	1500.1
35°	1107.0	1112.3	1187.0	1266.9	1356.7
37.5°	963.9	971.1	1037.4	1112.9	1201.3
40°	871.3	881.9	940.5	1011.7	1098.3
42.5°	782.2	795.4	849.7	917.2	995.4
45°	663.8	676.4	721.1	775.6	846.5
47.5°	561.7	576.3	610.6	657.6	718.0
50°	503.8	517.5	549.2	584.0	641.1
52.5°	452.7	466.5	494.7	521.5	570.1
55°	381.6	397.5	420.5	436.5	472.4
57.5°	323.2	338.5	356.7	363.9	385.7
60°	284.3	301.2	317.8	317.0	328.6
62.5°	248.9	263.2	279.8	268.3	269.0
65°	191.3	207.2	225.9	197.4	179.5
67.5°	154.6	158.0	177.3	137.7	116.3
70°	137.3	137.3	142.7	106.6	88.6
72.5°	120.9	120.9	115.9	86.7	67.9
75°	96.2	96.2	87.6	60.1	41.1
77.5°	74.2	73.3	67.0	44.8	29.8
80°	59.5	59.5	54.1	35.4	23.8
82.5°	46.5	46.5	41.9	27.7	17.7
85°	27.0	27.0	24.9	16.1	9.7
87.5°	9.5	9.5	8.6	5.2	4.3
90°	0.0	0.0	0.0	0.0	0.0
92.5°	14.1	74.6	173.0	50.4	38.0
95°	45.7	181.5	815.9	282.4	174.1
97.5°	84.1	212.7	1256.6	899.2	616.2
100°	110.8	231.1	1352.2	1369.7	1055.1
102.5°	140.3	251.0	1331.1	1753.2	1478.5
105°	186.4	282.7	1222.1	2158.7	2052.1
107.5°	233.2	319.5	1094.8	2273.0	2367.9
110°	265.5	346.3	1021.6	2229.2	2442.4

TEST NUMBER: P521995

CATALOG NUMBER: SQ4-WB-125U-100D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	296.5	373.2	972.4	2125.8	2429.8
115°	346.4	418.6	926.7	1963.1	2305.3
117.5°	390.4	458.1	899.6	1785.3	2147.7
120°	425.5	482.3	896.8	1683.7	2031.0
122.5°	453.7	510.4	889.8	1594.5	1917.0
125°	488.8	542.1	884.5	1467.8	1754.9
127.5°	527.2	577.0	881.7	1392.1	1628.7
130°	546.9	596.7	877.5	1339.3	1545.7
132.5°	568.0	616.5	877.5	1298.2	1488.0
135°	597.9	647.7	873.9	1239.8	1401.5
137.5°	626.0	674.5	873.6	1190.5	1330.1
140°	647.1	697.0	872.2	1149.5	1283.6
142.5°	671.0	712.6	876.4	1116.9	1237.2
145°	705.1	741.2	881.0	1073.1	1169.4
147.5°	734.3	769.4	888.7	1028.8	1112.0
150°	759.6	783.7	891.5	1014.2	1072.6
152.5°	779.3	804.8	894.3	994.4	1048.7
155°	805.4	824.3	902.1	969.8	1009.3
157.5°	837.7	849.1	903.8	958.6	986.8
160°	854.6	863.2	910.9	950.1	974.2
162.5°	864.4	874.4	912.3	942.9	961.5
165°	889.8	893.2	912.6	932.3	946.0
167.5°	907.0	903.9	920.7	929.6	935.1
170°	912.6	910.9	917.9	919.8	926.7
172.5°	925.3	919.4	922.1	917.0	922.5
175°	932.0	926.8	923.2	917.7	910.9
177.5°	934.8	926.5	922.1	916.5	917.9
180°	924.9	924.9	924.9	924.9	924.9

(END OF REPORT)