

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521979

Luminaire Tested: **SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521979
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8102.3 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 73.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521979

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P521979

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32
1	95	91	87	84	85	82	79	76	65	63	62	50	49	48	36	36	35	29
2	87	80	74	70	78	72	68	64	58	55	52	45	43	41	33	32	31	25
3	80	71	64	59	72	64	59	54	52	48	45	40	38	36	30	28	27	22
4	73	63	56	51	66	57	51	47	47	42	39	37	34	31	27	25	24	20
5	67	57	49	44	61	52	45	40	42	37	34	33	30	28	25	23	21	18
6	62	51	44	38	56	47	40	35	38	33	30	30	27	25	23	21	19	16
7	58	46	39	34	52	42	36	31	35	30	27	28	24	22	21	19	17	15
8	54	42	35	30	48	39	32	28	32	27	24	26	22	20	20	17	16	13
9	50	39	32	27	45	35	29	25	29	25	21	24	20	18	18	16	14	12
10	47	35	29	24	42	33	27	23	27	23	19	22	19	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16529	16529	16529
5°	16322	16264	16358
10°	15421	15561	15922
15°	14236	14566	15220
20°	12928	13414	14301
25°	11595	12227	13324
30°	10368	11046	12310
35°	9066	9721	11111
40°	7631	8237	9618
45°	6297	6841	8031
50°	5258	5731	6690
55°	4464	4919	5525
60°	3814	4264	4410
65°	3037	3587	2849
70°	2692	2800	1740
75°	2495	2271	1066
80°	2295	2088	919
85°	2085	1916	752



TEST NUMBER: P521979

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.3	2.0
10°-20°	427.4	5.3
20°-30°	553.6	6.8
30°-40°	542.1	6.7
40°-50°	415.0	5.1
50°-60°	276.5	3.4
60°-70°	150.9	1.9
70°-80°	62.9	0.8
80°-90°	17.8	0.2
90°-100°	402.9	5.0
100°-110°	1146.3	14.1
110°-120°	1098.3	13.6
120°-130°	869.3	10.7
130°-140°	697.7	8.6
140°-150°	546.2	6.7
150°-160°	399.7	4.9
160°-170°	247.6	3.1
170°-180°	84.0	1.0
0°-30°	1145.3	14.1
0°-40°	1687.4	20.8
0°-60°	2378.9	29.4
0°-90°	2610.5	32.2
90°-120°	2647.5	32.7
90°-150°	4760.6	58.8
90°-180°	5492.0	67.8
0°-180°	8102.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1792	1792	1792	1792	1792	
5°	1762	1745	1756	1760	1766	164
15°	1490	1485	1525	1566	1593	416
25°	1139	1142	1201	1254	1309	524
35°	805	809	863	921	986	500
45°	483	492	524	564	616	376
55°	278	289	306	317	344	252
65°	139	151	164	144	130	145
75°	70	70	64	44	30	75
85°	20	20	18	12	7	21
90°	0	0	0	0	0	3
95°	44	174	780	270	166	50
105°	178	270	1168	2063	1962	188
115°	331	400	886	1876	2204	326
125°	467	518	846	1403	1678	418
135°	572	619	835	1185	1340	441
145°	674	708	842	1026	1118	421
155°	770	788	862	927	965	356
165°	850	854	872	891	904	239
175°	891	886	882	877	871	84
180°	884	884	884	884	884	

TEST NUMBER: P521979

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1791.5	1791.5	1791.5	1791.5	1791.5
2.5°	1795.9	1779.9	1783.9	1783.8	1778.9
5°	1762.4	1744.7	1756.1	1760.1	1766.3
7.5°	1697.0	1683.6	1704.4	1719.7	1732.2
10°	1646.0	1634.5	1661.0	1683.3	1699.5
12.5°	1586.9	1577.2	1610.0	1640.1	1661.1
15°	1490.4	1485.0	1525.0	1566.5	1593.4
17.5°	1387.1	1384.5	1430.3	1478.7	1513.2
20°	1316.7	1315.9	1366.2	1416.6	1456.6
22.5°	1245.6	1247.3	1300.2	1352.6	1398.1
25°	1139.0	1142.1	1201.1	1253.5	1308.8
27.5°	1040.4	1041.8	1102.9	1158.1	1217.1
30°	973.2	977.0	1036.8	1094.0	1155.5
32.5°	905.9	910.3	968.9	1028.0	1090.7
35°	804.9	808.8	863.1	921.2	986.5
37.5°	700.9	706.1	754.3	809.2	873.5
40°	633.6	641.3	683.9	735.6	798.6
42.5°	568.8	578.3	617.9	666.9	723.8
45°	482.6	491.9	524.3	564.0	615.5
47.5°	408.4	419.0	444.0	478.1	522.1
50°	366.3	376.3	399.3	424.6	466.1
52.5°	329.2	339.2	359.7	379.2	414.6
55°	277.5	289.0	305.8	317.4	343.5
57.5°	235.0	246.1	259.4	264.6	280.5
60°	206.7	219.0	231.1	230.5	239.0
62.5°	181.0	191.4	203.4	195.1	195.6
65°	139.1	150.7	164.3	143.6	130.5
67.5°	112.4	114.9	128.9	100.1	84.6
70°	99.8	99.8	103.8	77.5	64.5
72.5°	87.9	87.9	84.3	63.0	49.4
75°	70.0	70.0	63.7	43.7	29.9
77.5°	53.9	53.3	48.7	32.6	21.7
80°	43.2	43.2	39.3	25.7	17.3
82.5°	33.8	33.8	30.5	20.1	12.9
85°	19.7	19.7	18.1	11.7	7.1
87.5°	6.9	6.9	6.3	3.8	3.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.4	71.3	165.4	48.1	36.3
95°	43.7	173.5	779.9	269.9	166.4
97.5°	80.3	203.3	1201.1	859.5	589.0
100°	105.9	220.9	1292.6	1309.2	1008.5
102.5°	134.1	240.0	1272.4	1675.9	1413.2
105°	178.2	270.2	1168.2	2063.4	1961.5
107.5°	222.9	305.4	1046.5	2172.7	2263.4
110°	253.8	331.0	976.6	2130.9	2334.7



TEST NUMBER: P521979

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	283.4	356.7	929.5	2032.0	2322.6
115°	331.1	400.1	885.8	1876.5	2203.6
117.5°	373.1	437.9	859.9	1706.5	2053.0
120°	406.8	461.0	857.2	1609.4	1941.3
122.5°	433.7	487.9	850.5	1524.1	1832.4
125°	467.3	518.2	845.5	1403.0	1677.5
127.5°	503.9	551.6	842.8	1330.6	1556.8
130°	522.7	570.4	838.7	1280.2	1477.4
132.5°	542.9	589.3	838.7	1240.9	1422.3
135°	571.5	619.1	835.4	1185.1	1339.6
137.5°	598.4	644.7	835.0	1137.9	1271.4
140°	618.5	666.2	833.7	1098.8	1227.0
142.5°	641.4	681.2	837.7	1067.6	1182.6
145°	674.0	708.5	842.1	1025.7	1117.7
147.5°	701.9	735.4	849.5	983.4	1063.0
150°	726.1	749.1	852.2	969.4	1025.3
152.5°	744.9	769.3	854.9	950.5	1002.4
155°	769.8	787.9	862.3	927.0	964.8
157.5°	800.7	811.6	863.9	916.3	943.3
160°	816.9	825.1	870.7	908.2	931.2
162.5°	826.3	835.8	872.0	901.3	919.1
165°	850.5	853.8	872.3	891.1	904.3
167.5°	867.0	864.0	880.1	888.6	893.9
170°	872.3	870.7	877.4	879.2	885.8
172.5°	884.4	878.9	881.4	876.5	881.8
175°	890.8	885.9	882.4	877.2	870.7
177.5°	893.5	885.6	881.4	876.1	877.4
180°	884.1	884.1	884.1	884.1	884.1

(END OF REPORT)