

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521982

Luminaire Tested: **SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521982
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (5000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8476.4 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 73.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521982

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (5000K)

Luminous Intensity Polar Plot





TEST NUMBER: P521982

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (5000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32				
1	95	91	87	84	85	82	79	76	65	63	62	50	49	48	36	36	35	29				
2	87	80	74	70	78	72	68	64	58	55	52	45	43	41	33	32	31	25				
3	80	71	64	59	72	64	59	54	52	48	45	40	38	36	30	28	27	22				
4	73	63	56	51	66	57	51	47	47	42	39	37	34	31	27	25	24	20				
5	67	57	49	44	61	52	45	40	42	37	34	33	30	28	25	23	21	18				
6	62	51	44	38	56	47	40	35	38	33	30	30	27	25	23	21	19	16				
7	58	46	39	34	52	42	36	31	35	30	27	28	24	22	21	19	17	15				
8	54	42	35	30	48	39	32	28	32	27	24	26	22	20	20	17	16	13				
9	50	39	32	27	45	35	29	25	29	25	21	24	20	18	18	16	14	12				
10	47	35	29	24	42	33	27	23	27	23	19	22	19	16	17	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17292	17292	17292
5°	17075	17015	17113
10°	16133	16279	16656
15°	14893	15239	15922
20°	13525	14033	14961
25°	12130	12792	13938
30°	10846	11556	12879
35°	9485	10171	11625
40°	7983	8617	10063
45°	6588	7157	8401
50°	5500	5997	7000
55°	4670	5146	5781
60°	3991	4462	4613
65°	3179	3753	2980
70°	2816	2930	1818
75°	2609	2374	1112
80°	2402	2184	962
85°	2181	2001	783



TEST NUMBER: P521982

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (5000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.9	2.0
10°-20°	447.1	5.3
20°-30°	579.2	6.8
30°-40°	567.1	6.7
40°-50°	434.1	5.1
50°-60°	289.3	3.4
60°-70°	157.9	1.9
70°-80°	65.8	0.8
80°-90°	18.6	0.2
90°-100°	421.5	5.0
100°-110°	1199.2	14.1
110°-120°	1149.0	13.6
120°-130°	909.4	10.7
130°-140°	729.9	8.6
140°-150°	571.4	6.7
150°-160°	418.1	4.9
160°-170°	259.0	3.1
170°-180°	87.9	1.0
0°-30°	1198.2	14.1
0°-40°	1765.3	20.8
0°-60°	2488.8	29.4
0°-90°	2731.0	32.2
90°-120°	2769.7	32.7
90°-150°	4980.4	58.8
90°-180°	5745.0	67.8
0°-180°	8476.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1874	1874	1874	1874	1874	
5°	1844	1825	1837	1841	1848	172
15°	1559	1554	1595	1639	1667	435
25°	1192	1195	1257	1311	1369	548
35°	842	846	903	964	1032	524
45°	505	515	548	590	644	394
55°	290	302	320	332	359	263
65°	146	158	172	150	136	151
75°	73	73	67	46	31	78
85°	21	21	19	12	7	22
90°	0	0	0	0	0	3
95°	46	182	816	282	174	52
105°	186	283	1222	2159	2052	197
115°	346	419	927	1963	2305	341
125°	489	542	884	1468	1755	438
135°	598	648	874	1240	1402	461
145°	705	741	881	1073	1169	440
155°	805	824	902	970	1009	372
165°	890	893	913	932	946	250
175°	932	927	923	918	911	88
180°	925	925	925	925	925	

TEST NUMBER: P521982

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1874.2	1874.2	1874.2	1874.2	1874.2
2.5°	1878.8	1862.0	1866.3	1866.1	1861.0
5°	1843.7	1825.2	1837.2	1841.4	1847.8
7.5°	1775.3	1761.3	1783.0	1799.1	1812.2
10°	1722.0	1710.0	1737.6	1761.1	1777.9
12.5°	1660.2	1650.1	1684.4	1715.8	1737.8
15°	1559.2	1553.6	1595.4	1638.8	1666.9
17.5°	1451.1	1448.4	1496.4	1547.0	1583.0
20°	1377.5	1376.7	1429.3	1482.0	1523.8
22.5°	1303.1	1304.9	1360.2	1415.0	1462.7
25°	1191.6	1194.8	1256.6	1311.3	1369.2
27.5°	1088.5	1089.9	1153.8	1211.6	1273.3
30°	1018.1	1022.1	1084.7	1144.5	1208.9
32.5°	947.7	952.4	1013.6	1075.5	1141.1
35°	842.1	846.1	903.0	963.7	1032.1
37.5°	733.2	738.7	789.1	846.6	913.8
40°	662.8	670.9	715.5	769.6	835.5
42.5°	595.1	605.0	646.4	697.7	757.2
45°	504.9	514.6	548.5	590.0	643.9
47.5°	427.3	438.4	464.5	500.2	546.2
50°	383.2	393.7	417.8	444.2	487.7
52.5°	344.4	354.9	376.3	396.7	433.7
55°	290.3	302.4	319.9	332.0	359.4
57.5°	245.9	257.5	271.4	276.9	293.4
60°	216.3	229.1	241.8	241.2	250.0
62.5°	189.3	200.2	212.8	204.1	204.6
65°	145.6	157.6	171.9	150.2	136.5
67.5°	117.6	120.2	134.9	104.7	88.5
70°	104.4	104.4	108.6	81.1	67.4
72.5°	91.9	91.9	88.2	66.0	51.6
75°	73.2	73.2	66.6	45.7	31.2
77.5°	56.4	55.8	51.0	34.1	22.7
80°	45.2	45.2	41.1	26.9	18.1
82.5°	35.4	35.4	31.9	21.0	13.5
85°	20.6	20.6	18.9	12.2	7.4
87.5°	7.2	7.2	6.6	3.9	3.3
90°	0.0	0.0	0.0	0.0	0.0
92.5°	14.1	74.6	173.0	50.4	38.0
95°	45.7	181.5	815.9	282.4	174.1
97.5°	84.1	212.7	1256.6	899.2	616.2
100°	110.8	231.1	1352.2	1369.7	1055.1
102.5°	140.3	251.0	1331.1	1753.2	1478.5
105°	186.4	282.7	1222.1	2158.7	2052.1
107.5°	233.2	319.5	1094.8	2273.0	2367.9
110°	265.5	346.3	1021.6	2229.2	2442.4

TEST NUMBER: P521982

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	296.5	373.2	972.4	2125.8	2429.8
115°	346.4	418.6	926.7	1963.1	2305.3
117.5°	390.4	458.1	899.6	1785.3	2147.7
120°	425.5	482.3	896.8	1683.7	2031.0
122.5°	453.7	510.4	889.8	1594.5	1917.0
125°	488.8	542.1	884.5	1467.8	1754.9
127.5°	527.2	577.0	881.7	1392.1	1628.7
130°	546.9	596.7	877.5	1339.3	1545.7
132.5°	568.0	616.5	877.5	1298.2	1488.0
135°	597.9	647.7	873.9	1239.8	1401.5
137.5°	626.0	674.5	873.6	1190.5	1330.1
140°	647.1	697.0	872.2	1149.5	1283.6
142.5°	671.0	712.6	876.4	1116.9	1237.2
145°	705.1	741.2	881.0	1073.1	1169.4
147.5°	734.3	769.4	888.7	1028.8	1112.0
150°	759.6	783.7	891.5	1014.2	1072.6
152.5°	779.3	804.8	894.3	994.4	1048.7
155°	805.4	824.3	902.1	969.8	1009.3
157.5°	837.7	849.1	903.8	958.6	986.8
160°	854.6	863.2	910.9	950.1	974.2
162.5°	864.4	874.4	912.3	942.9	961.5
165°	889.8	893.2	912.6	932.3	946.0
167.5°	907.0	903.9	920.7	929.6	935.1
170°	912.6	910.9	917.9	919.8	926.7
172.5°	925.3	919.4	922.1	917.0	922.5
175°	932.0	926.8	923.2	917.7	910.9
177.5°	934.8	926.5	922.1	916.5	917.9
180°	924.9	924.9	924.9	924.9	924.9

(END OF REPORT)