

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521983

Luminaire Tested: **SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521983
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8597.1 lumens
Efficiency: N/A
Efficacy: 117.4 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 73.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521983
CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P521983

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32
1	95	91	87	84	85	82	79	76	65	63	62	50	49	48	36	36	35	29
2	87	80	74	70	78	72	68	64	58	55	52	45	43	41	33	32	31	25
3	80	71	64	59	72	64	59	54	52	48	45	40	38	36	30	28	27	22
4	73	63	56	51	66	57	51	47	47	42	39	37	34	31	27	25	24	20
5	67	57	49	44	61	52	45	40	42	37	34	33	30	28	25	23	21	18
6	62	51	44	38	56	47	40	35	38	33	30	30	27	25	23	21	19	16
7	58	46	39	34	52	42	36	31	35	30	27	28	24	22	21	19	17	15
8	54	42	35	30	48	39	32	28	32	27	24	26	22	20	20	17	16	13
9	50	39	32	27	45	35	29	25	29	25	21	24	20	18	18	16	14	12
10	47	35	29	24	42	33	27	23	27	23	19	22	19	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17538	17538	17538
5°	17319	17257	17358
10°	16363	16511	16894
15°	15105	15456	16149
20°	13717	14233	15174
25°	12304	12974	14137
30°	11001	11720	13062
35°	9620	10315	11790
40°	8097	8739	10206
45°	6682	7259	8522
50°	5579	6082	7099
55°	4736	5220	5863
60°	4048	4525	4680
65°	3222	3805	3024
70°	2857	2970	1845
75°	2645	2410	1130
80°	2439	2216	972
85°	2212	2032	794



TEST NUMBER: P521983

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.4	2.0
10°-20°	453.5	5.3
20°-30°	587.4	6.8
30°-40°	575.2	6.7
40°-50°	440.3	5.1
50°-60°	293.4	3.4
60°-70°	160.1	1.9
70°-80°	66.7	0.8
80°-90°	18.9	0.2
90°-100°	427.5	5.0
100°-110°	1216.3	14.1
110°-120°	1165.4	13.6
120°-130°	922.3	10.7
130°-140°	740.3	8.6
140°-150°	579.6	6.7
150°-160°	424.1	4.9
160°-170°	262.7	3.1
170°-180°	89.1	1.0
0°-30°	1215.3	14.1
0°-40°	1790.5	20.8
0°-60°	2524.2	29.4
0°-90°	2769.9	32.2
90°-120°	2809.1	32.7
90°-150°	5051.4	58.8
90°-180°	5827.0	67.8
0°-180°	8597.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1901	1901	1901	1901	1901	
5°	1870	1851	1863	1868	1874	174
15°	1581	1576	1618	1662	1691	442
25°	1209	1212	1274	1330	1389	556
35°	854	858	916	977	1047	531
45°	512	522	556	598	653	399
55°	294	307	324	337	364	267
65°	148	160	174	152	138	153
75°	74	74	68	46	32	79
85°	21	21	19	12	8	23
90°	0	0	0	0	0	3
95°	46	184	828	286	177	53
105°	189	287	1240	2189	2081	200
115°	351	425	940	1991	2338	346
125°	496	550	897	1489	1780	444
135°	606	657	886	1258	1421	468
145°	715	752	894	1088	1186	447
155°	817	836	915	984	1024	378
165°	902	906	926	946	960	254
175°	945	940	936	931	924	90
180°	938	938	938	938	938	



TEST NUMBER: P521983

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1900.9	1900.9	1900.9	1900.9	1900.9
2.5°	1905.5	1888.6	1892.8	1892.7	1887.5
5°	1870.0	1851.2	1863.3	1867.6	1874.2
7.5°	1800.6	1786.4	1808.4	1824.8	1838.0
10°	1746.6	1734.3	1762.4	1786.1	1803.3
12.5°	1683.8	1673.6	1708.4	1740.2	1762.6
15°	1581.4	1575.7	1618.1	1662.1	1690.7
17.5°	1471.8	1469.0	1517.7	1569.1	1605.6
20°	1397.1	1396.3	1449.6	1503.1	1545.5
22.5°	1321.7	1323.5	1379.6	1435.2	1483.5
25°	1208.6	1211.8	1274.5	1330.0	1388.7
27.5°	1104.0	1105.4	1170.2	1228.8	1291.5
30°	1032.6	1036.7	1100.1	1160.8	1226.1
32.5°	961.2	965.9	1028.1	1090.8	1157.4
35°	854.1	858.2	915.8	977.4	1046.8
37.5°	743.7	749.2	800.4	858.6	926.8
40°	672.3	680.4	725.6	780.5	847.4
42.5°	603.5	613.6	655.6	707.7	768.0
45°	512.1	521.9	556.3	598.4	653.1
47.5°	433.4	444.6	471.1	507.3	554.0
50°	388.7	399.3	423.7	450.6	494.6
52.5°	349.3	359.9	381.7	402.4	439.9
55°	294.4	306.7	324.5	336.8	364.5
57.5°	249.4	261.1	275.2	280.8	297.6
60°	219.4	232.4	245.2	244.6	253.6
62.5°	192.0	203.1	215.9	207.0	207.5
65°	147.6	159.9	174.3	152.3	138.5
67.5°	119.3	121.9	136.8	106.2	89.7
70°	105.9	105.9	110.1	82.3	68.4
72.5°	93.2	93.2	89.4	66.9	52.4
75°	74.2	74.2	67.6	46.4	31.7
77.5°	57.2	56.6	51.7	34.6	23.0
80°	45.9	45.9	41.7	27.3	18.3
82.5°	35.9	35.9	32.4	21.3	13.7
85°	20.9	20.9	19.2	12.4	7.5
87.5°	7.3	7.3	6.7	4.0	3.3
90°	0.0	0.0	0.0	0.0	0.0
92.5°	14.3	75.7	175.5	51.1	38.5
95°	46.4	184.1	827.5	286.4	176.6
97.5°	85.2	215.7	1274.5	912.0	624.9
100°	112.4	234.4	1371.5	1389.2	1070.1
102.5°	142.3	254.6	1350.1	1778.2	1499.5
105°	189.0	286.7	1239.5	2189.4	2081.3
107.5°	236.5	324.0	1110.4	2305.4	2401.6
110°	269.3	351.3	1036.2	2261.0	2477.2

TEST NUMBER: P521983

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	300.7	378.5	986.3	2156.1	2464.4
115°	351.3	424.6	939.9	1991.1	2338.1
117.5°	395.9	464.6	912.4	1810.7	2178.3
120°	431.6	489.1	909.6	1707.7	2059.9
122.5°	460.1	517.7	902.4	1617.2	1944.3
125°	495.8	549.9	897.1	1488.7	1779.9
127.5°	534.7	585.3	894.2	1411.9	1651.8
130°	554.7	605.2	890.0	1358.4	1567.7
132.5°	576.1	625.2	890.0	1316.7	1509.2
135°	606.4	657.0	886.4	1257.5	1421.4
137.5°	634.9	684.1	886.0	1207.4	1349.0
140°	656.3	706.9	884.6	1165.9	1301.9
142.5°	680.6	722.8	888.9	1132.8	1254.8
145°	715.2	751.8	893.5	1088.4	1186.0
147.5°	744.8	780.4	901.4	1043.5	1127.9
150°	770.5	794.9	904.2	1028.6	1087.9
152.5°	790.4	816.2	907.1	1008.6	1063.7
155°	816.8	836.0	914.9	983.6	1023.7
157.5°	849.6	861.2	916.7	972.3	1000.9
160°	866.8	875.5	923.8	963.6	988.0
162.5°	876.8	886.9	925.3	956.4	975.2
165°	902.4	905.9	925.6	945.6	959.5
167.5°	919.9	916.8	933.8	942.9	948.4
170°	925.6	923.9	931.0	932.9	939.9
172.5°	938.5	932.5	935.3	930.0	935.6
175°	945.2	940.0	936.3	930.8	923.8
177.5°	948.1	939.7	935.3	929.6	931.0
180°	938.1	938.1	938.1	938.1	938.1

(END OF REPORT)