

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521981

Luminaire Tested: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4\_4500K

Issue Date: 5-5-2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P521981  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2009-966-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 5-5-2021  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4\_4500K  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 4500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8383.6 lumens  
Efficiency: N/A  
Efficacy: 114.4 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 73.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P521981

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4\_4500K

### Luminous Intensity Polar Plot



TEST NUMBER: P521981

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4\_4500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32				
1	95	91	87	84	85	82	79	76	65	63	62	50	49	48	36	36	35	29				
2	87	80	74	70	78	72	68	64	58	55	52	45	43	41	33	32	31	25				
3	80	71	64	59	72	64	59	54	52	48	45	40	38	36	30	28	27	22				
4	73	63	56	51	66	57	51	47	47	42	39	37	34	31	27	25	24	20				
5	67	57	49	44	61	52	45	40	42	37	34	33	30	28	25	23	21	18				
6	62	51	44	38	56	47	40	35	38	33	30	30	27	25	23	21	19	16				
7	58	46	39	34	52	42	36	31	35	30	27	28	24	22	21	19	17	15				
8	54	42	35	30	48	39	32	28	32	27	24	26	22	20	20	17	16	13				
9	50	39	32	27	45	35	29	25	29	25	21	24	20	18	18	16	14	12				
10	47	35	29	24	42	33	27	23	27	23	19	22	19	16	17	15	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17103	17103	17103
5°	16889	16828	16926
10°	15956	16101	16475
15°	14730	15072	15748
20°	13376	13879	14798
25°	11998	12652	13786
30°	10727	11429	12737
35°	9381	10059	11497
40°	7896	8522	9953
45°	6516	7078	8310
50°	5440	5931	6923
55°	4618	5089	5717
60°	3947	4412	4563
65°	3144	3711	2947
70°	2787	2897	1799
75°	2581	2349	1102
80°	2375	2162	951
85°	2149	1980	773

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 8310 cd/sqm

TEST NUMBER: P521981

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4\_4500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	170.0	2.0
10°-20°	442.2	5.3
20°-30°	572.8	6.8
30°-40°	560.9	6.7
40°-50°	429.4	5.1
50°-60°	286.1	3.4
60°-70°	156.1	1.9
70°-80°	65.0	0.8
80°-90°	18.4	0.2
90°-100°	416.8	5.0
100°-110°	1186.1	14.1
110°-120°	1136.4	13.6
120°-130°	899.4	10.7
130°-140°	721.9	8.6
140°-150°	565.2	6.7
150°-160°	413.5	4.9
160°-170°	256.2	3.1
170°-180°	86.9	1.0
0°-30°	1185.1	14.1
0°-40°	1746.0	20.8
0°-60°	2461.5	29.4
0°-90°	2701.1	32.2
90°-120°	2739.4	32.7
90°-150°	4925.9	58.8
90°-180°	5682.0	67.8
0°-180°	8383.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1854	1854	1854	1854	1854	
5°	1824	1805	1817	1821	1828	170
15°	1542	1537	1578	1621	1649	431
25°	1179	1182	1243	1297	1354	542
35°	833	837	893	953	1021	518
45°	499	509	542	584	637	389
55°	287	299	316	328	355	260
65°	144	156	170	148	135	150
75°	72	72	66	45	31	77
85°	20	20	19	12	7	22
90°	0	0	0	0	0	3
95°	45	180	807	279	172	52
105°	184	280	1209	2135	2030	195
115°	343	414	916	1942	2280	337
125°	484	536	875	1452	1736	433
135°	591	641	864	1226	1386	456
145°	697	733	871	1061	1157	436
155°	796	815	892	959	998	368
165°	880	883	903	922	936	247
175°	922	917	913	908	901	87
180°	915	915	915	915	915	

TEST NUMBER: P521981

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4\_4500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1853.7	1853.7	1853.7	1853.7	1853.7
2.5°	1858.2	1841.7	1845.8	1845.7	1840.6
5°	1823.6	1805.3	1817.0	1821.3	1827.6
7.5°	1755.9	1742.0	1763.5	1779.4	1792.3
10°	1703.2	1691.2	1718.6	1741.8	1758.5
12.5°	1642.0	1632.0	1665.9	1697.0	1718.8
15°	1542.1	1536.6	1577.9	1620.8	1648.7
17.5°	1435.3	1432.6	1480.0	1530.1	1565.7
20°	1362.4	1361.6	1413.6	1465.8	1507.2
22.5°	1288.9	1290.6	1345.3	1399.6	1446.6
25°	1178.6	1181.7	1242.8	1297.0	1354.2
27.5°	1076.6	1078.0	1141.1	1198.3	1259.4
30°	1006.9	1010.9	1072.8	1132.0	1195.6
32.5°	937.3	941.9	1002.5	1063.7	1128.6
35°	832.9	836.9	893.1	953.2	1020.8
37.5°	725.2	730.6	780.5	837.3	903.8
40°	655.6	663.5	707.6	761.2	826.4
42.5°	588.5	598.4	639.3	690.1	748.9
45°	499.4	508.9	542.5	583.6	636.9
47.5°	422.6	433.6	459.4	494.7	540.2
50°	379.0	389.4	413.2	439.4	482.3
52.5°	340.6	351.0	372.2	392.4	429.0
55°	287.1	299.0	316.4	328.4	355.4
57.5°	243.2	254.6	268.4	273.8	290.2
60°	213.9	226.6	239.1	238.5	247.3
62.5°	187.2	198.1	210.5	201.9	202.4
65°	144.0	155.9	170.0	148.5	135.0
67.5°	116.3	118.9	133.4	103.6	87.5
70°	103.3	103.3	107.4	80.2	66.7
72.5°	90.9	90.9	87.2	65.2	51.1
75°	72.4	72.4	65.9	45.2	30.9
77.5°	55.8	55.2	50.4	33.7	22.4
80°	44.7	44.7	40.7	26.6	17.9
82.5°	35.0	35.0	31.6	20.8	13.3
85°	20.3	20.3	18.7	12.1	7.3
87.5°	7.2	7.2	6.5	3.9	3.3
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.9	73.8	171.1	49.8	37.6
95°	45.2	179.6	807.0	279.3	172.2
97.5°	83.1	210.3	1242.8	889.3	609.4
100°	109.6	228.6	1337.4	1354.7	1043.5
102.5°	138.8	248.3	1316.6	1734.0	1462.3
105°	184.4	279.6	1208.7	2135.1	2029.6
107.5°	230.6	316.0	1082.8	2248.1	2342.0
110°	262.6	342.5	1010.5	2204.9	2415.7

TEST NUMBER: P521981

CATALOG NUMBER: SQ4-WB-125U-075D-92765-1D-UNV-STD-W-4\_4500K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	293.2	369.1	961.8	2102.5	2403.2
115°	342.6	414.0	916.5	1941.7	2280.1
117.5°	386.1	453.1	889.8	1765.8	2124.2
120°	420.9	477.0	887.0	1665.2	2008.8
122.5°	448.7	504.8	880.0	1577.0	1896.1
125°	483.5	536.2	874.8	1451.7	1735.7
127.5°	521.4	570.7	872.0	1376.8	1610.8
130°	540.9	590.2	867.9	1324.7	1528.7
132.5°	561.8	609.7	867.9	1284.0	1471.7
135°	591.3	640.6	864.4	1226.3	1386.1
137.5°	619.1	667.1	864.0	1177.4	1315.5
140°	640.0	689.3	862.6	1137.0	1269.6
142.5°	663.7	704.8	866.8	1104.6	1223.7
145°	697.4	733.1	871.3	1061.3	1156.6
147.5°	726.3	761.0	879.0	1017.6	1099.9
150°	751.3	775.1	881.8	1003.1	1060.9
152.5°	770.8	796.0	884.5	983.5	1037.2
155°	796.5	815.2	892.2	959.2	998.3
157.5°	828.5	839.8	893.9	948.1	976.0
160°	845.2	853.7	900.9	939.7	963.5
162.5°	855.0	864.8	902.3	932.6	951.0
165°	880.0	883.4	902.6	922.1	935.7
167.5°	897.1	894.0	910.6	919.5	924.9
170°	902.6	900.9	907.9	909.7	916.5
172.5°	915.2	909.4	912.0	906.9	912.4
175°	921.8	916.7	913.1	907.7	900.9
177.5°	924.5	916.4	912.0	906.5	907.9
180°	914.8	914.8	914.8	914.8	914.8

(END OF REPORT)