

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P522003

Luminaire Tested: **SQ4-WB-125U-125D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 5/5/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P522003  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,  
Test Lab: INNOVATION CENTER  
Issue Date: 5/5/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-WB-125U-125D-92765-1D-UNV-STD-W-4 (2700K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9411.0 lumens  
Efficiency: N/A  
Efficacy: 97.0 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 97  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P522003

CATALOG NUMBER: SQ4-WB-125U-125D-92765-1D-UNV-STD-W-4 (2700K)

### Luminous Intensity Polar Plot





TEST NUMBER: P522003

CATALOG NUMBER: SQ4-WB-125U-125D-92765-1D-UNV-STD-W-4 (2700K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				
1	97	94	90	87	89	86	83	80	72	70	68	59	57	56	46	46	45	39				
2	90	83	77	73	82	76	72	68	64	61	58	53	50	48	42	41	39	35				
3	82	74	67	62	75	68	62	58	57	53	50	48	45	42	38	36	35	31				
4	76	66	59	53	70	61	55	50	52	47	43	43	40	37	35	33	31	27				
5	70	59	52	46	64	55	49	44	47	42	38	39	36	33	32	30	28	24				
6	65	54	46	41	60	50	43	39	43	38	34	36	32	29	30	27	25	22				
7	60	49	41	36	55	45	39	34	39	34	30	33	29	26	27	25	23	20				
8	56	45	37	32	52	42	35	31	36	31	27	30	27	24	25	23	21	18				
9	52	41	34	29	48	38	32	28	33	28	25	28	25	22	24	21	19	17				
10	49	38	31	26	45	35	29	25	31	26	23	26	23	20	22	19	17	16				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	26319	26319	26319
5°	25990	25898	26048
10°	24555	24778	25352
15°	22668	23194	24234
20°	20585	21359	22773
25°	18463	19470	21216
30°	16509	17589	19602
35°	14436	15480	17693
40°	12151	13116	15316
45°	10027	10894	12788
50°	8372	9127	10653
55°	7107	7832	8799
60°	6075	6790	7021
65°	4836	5711	4536
70°	4289	4456	2768
75°	3971	3615	1697
80°	3655	3326	1461
85°	3313	3049	1196



TEST NUMBER: P522003

CATALOG NUMBER: SQ4-WB-125U-125D-92765-1D-UNV-STD-W-4 (2700K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	261.7	2.8
10°-20°	680.6	7.2
20°-30°	881.5	9.4
30°-40°	863.2	9.2
40°-50°	660.8	7.0
50°-60°	440.3	4.7
60°-70°	240.3	2.6
70°-80°	100.1	1.1
80°-90°	28.3	0.3
90°-100°	385.4	4.1
100°-110°	1096.7	11.7
110°-120°	1050.8	11.2
120°-130°	831.6	8.8
130°-140°	667.5	7.1
140°-150°	522.6	5.6
150°-160°	382.4	4.1
160°-170°	236.8	2.5
170°-180°	80.4	0.9
0°-30°	1823.7	19.4
0°-40°	2687.0	28.6
0°-60°	3788.0	40.3
0°-90°	4156.8	44.2
90°-120°	2532.9	26.9
90°-150°	4554.7	48.4
90°-180°	5254.0	55.8
0°-180°	9411.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2853	2853	2853	2853	2853	
5°	2806	2778	2796	2803	2812	261
15°	2373	2365	2428	2494	2537	663
25°	1814	1819	1913	1996	2084	834
35°	1282	1288	1374	1467	1571	797
45°	768	783	835	898	980	599
55°	442	460	487	505	547	401
65°	222	240	262	229	208	230
75°	111	111	101	70	48	119
85°	31	31	29	19	11	34
90°	0	0	0	0	0	3
95°	42	166	746	258	159	48
105°	170	258	1118	1974	1877	180
115°	317	383	848	1795	2108	312
125°	447	496	809	1342	1605	400
135°	547	592	799	1134	1282	422
145°	645	678	806	981	1069	403
155°	736	754	825	887	923	340
165°	814	817	835	853	865	229
175°	852	848	844	839	833	81
180°	846	846	846	846	846	

TEST NUMBER: P522003

CATALOG NUMBER: SQ4-WB-125U-125D-92765-1D-UNV-STD-W-4 (2700K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2852.6	2852.6	2852.6	2852.6	2852.6
2.5°	2859.6	2834.1	2840.6	2840.4	2832.6
5°	2806.3	2778.1	2796.3	2802.7	2812.5
7.5°	2702.1	2680.8	2713.9	2738.4	2758.2
10°	2621.0	2602.7	2644.8	2680.4	2706.1
12.5°	2526.9	2511.5	2563.7	2611.5	2645.1
15°	2373.2	2364.6	2428.3	2494.3	2537.2
17.5°	2208.7	2204.6	2277.6	2354.7	2409.5
20°	2096.6	2095.4	2175.4	2255.7	2319.4
22.5°	1983.4	1986.1	2070.3	2153.8	2226.2
25°	1813.7	1818.6	1912.6	1995.9	2084.1
27.5°	1656.7	1658.9	1756.1	1844.1	1938.1
30°	1549.6	1555.7	1651.0	1742.1	1840.0
32.5°	1442.4	1449.5	1542.8	1637.0	1736.8
35°	1281.7	1287.8	1374.4	1466.8	1570.9
37.5°	1116.0	1124.3	1201.1	1288.6	1390.9
40°	1008.9	1021.1	1089.0	1171.4	1271.7
42.5°	905.7	920.9	983.8	1062.0	1152.6
45°	768.5	783.2	834.9	898.1	980.1
47.5°	650.4	667.3	707.0	761.4	831.4
50°	583.3	599.2	635.9	676.2	742.2
52.5°	524.2	540.1	572.8	603.8	660.1
55°	441.8	460.2	486.9	505.4	547.0
57.5°	374.3	391.9	413.1	421.4	446.6
60°	329.2	348.8	368.0	367.1	380.5
62.5°	288.1	304.8	323.9	310.7	311.4
65°	221.5	239.9	261.6	228.6	207.8
67.5°	179.0	182.9	205.3	159.4	134.7
70°	159.0	159.0	165.2	123.4	102.6
72.5°	139.9	139.9	134.2	100.4	78.6
75°	111.4	111.4	101.4	69.6	47.6
77.5°	85.9	84.9	77.6	51.9	34.5
80°	68.8	68.8	62.6	41.0	27.5
82.5°	53.8	53.8	48.6	32.0	20.5
85°	31.3	31.3	28.8	18.6	11.3
87.5°	11.0	11.0	10.0	6.0	5.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	12.9	68.2	158.2	46.1	34.7
95°	41.8	166.0	746.2	258.3	159.2
97.5°	76.9	194.5	1149.2	822.3	563.5
100°	101.3	211.4	1236.6	1252.6	964.9
102.5°	128.3	229.6	1217.3	1603.4	1352.1
105°	170.5	258.5	1117.6	1974.1	1876.7
107.5°	213.2	292.2	1001.2	2078.7	2165.5
110°	242.8	316.7	934.3	2038.7	2233.7

TEST NUMBER: P522003

CATALOG NUMBER: SQ4-WB-125U-125D-92765-1D-UNV-STD-W-4 (2700K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	271.1	341.3	889.3	1944.1	2222.1
115°	316.8	382.8	847.5	1795.3	2108.2
117.5°	357.0	419.0	822.7	1632.7	1964.1
120°	389.2	441.0	820.1	1539.7	1857.4
122.5°	414.9	466.8	813.7	1458.2	1753.2
125°	447.1	495.8	808.9	1342.3	1604.9
127.5°	482.1	527.7	806.3	1273.1	1489.4
130°	500.1	545.7	802.4	1224.8	1413.5
132.5°	519.4	563.8	802.4	1187.2	1360.8
135°	546.8	592.4	799.2	1133.9	1281.7
137.5°	572.5	616.8	798.9	1088.7	1216.4
140°	591.8	637.4	797.6	1051.3	1173.9
142.5°	613.7	651.7	801.5	1021.4	1131.5
145°	644.8	677.9	805.7	981.3	1069.4
147.5°	671.5	703.6	812.7	940.9	1017.0
150°	694.7	716.7	815.3	927.5	980.9
152.5°	712.7	736.0	817.9	909.4	959.1
155°	736.5	753.8	825.0	886.9	923.1
157.5°	766.1	776.5	826.6	876.7	902.5
160°	781.5	789.4	833.0	868.9	890.9
162.5°	790.5	799.7	834.3	862.3	879.3
165°	813.7	816.8	834.6	852.6	865.2
167.5°	829.5	826.6	842.0	850.2	855.2
170°	834.6	833.0	839.4	841.2	847.5
172.5°	846.2	840.8	843.3	838.6	843.6
175°	852.3	847.6	844.3	839.3	833.0
177.5°	854.9	847.3	843.3	838.2	839.4
180°	845.9	845.9	845.9	845.9	845.9

(END OF REPORT)