

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P522007

Luminaire Tested: SQ4-WB-125U-125D-92765-1D-UNV-STD-W-4_4500K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P522007
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-WB-125U-125D-92765-1D-UNV-STD-W-4_4500K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 4500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10178.1 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 97.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P522007

CATALOG NUMBER: SQ4-WB-125U-125D-92765-1D-UNV-STD-W-4_4500K

Luminous Intensity Polar Plot



TEST NUMBER: P522007

CATALOG NUMBER: SQ4-WB-125U-125D-92765-1D-UNV-STD-W-4_4500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				
1	97	94	90	87	89	86	83	80	72	70	68	59	57	56	46	46	45	39				
2	90	83	77	73	82	76	72	68	64	61	58	53	50	48	42	41	39	35				
3	82	74	67	62	75	68	62	58	57	53	50	48	45	42	38	36	35	31				
4	76	66	59	53	70	61	55	50	52	47	43	43	40	37	35	33	31	27				
5	70	59	52	46	64	55	49	44	47	42	38	39	36	33	32	30	28	24				
6	65	54	46	41	60	50	43	39	43	38	34	36	32	29	30	27	25	22				
7	60	49	41	36	55	45	39	34	39	34	30	33	29	26	27	25	23	20				
8	56	45	37	32	52	42	35	31	36	31	27	30	27	24	25	23	21	18				
9	52	41	34	29	48	38	32	28	33	28	25	28	25	22	24	21	19	17				
10	49	38	31	26	45	35	29	25	31	26	23	26	23	20	22	19	17	16				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	28464	28464	28464
5°	28108	28008	28171
10°	26557	26798	27419
15°	24515	25085	26210
20°	22263	23100	24628
25°	19968	21057	22945
30°	17854	19022	21200
35°	15613	16741	19135
40°	13141	14184	16565
45°	10845	11781	13831
50°	9054	9871	11523
55°	7687	8471	9516
60°	6569	7344	7593
65°	5231	6176	4905
70°	4637	4821	2994
75°	4296	3911	1832
80°	3958	3597	1583
85°	3578	3292	1291

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 13831 cd/sqm

TEST NUMBER: P522007

CATALOG NUMBER: SQ4-WB-125U-125D-92765-1D-UNV-STD-W-4_4500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	283.0	2.8
10°-20°	736.0	7.2
20°-30°	953.4	9.4
30°-40°	933.6	9.2
40°-50°	714.6	7.0
50°-60°	476.2	4.7
60°-70°	259.8	2.6
70°-80°	108.3	1.1
80°-90°	30.6	0.3
90°-100°	416.8	4.1
100°-110°	1186.1	11.7
110°-120°	1136.4	11.2
120°-130°	899.4	8.8
130°-140°	721.9	7.1
140°-150°	565.2	5.6
150°-160°	413.5	4.1
160°-170°	256.2	2.5
170°-180°	86.9	0.9
0°-30°	1972.4	19.4
0°-40°	2906.0	28.6
0°-60°	4096.8	40.3
0°-90°	4495.6	44.2
90°-120°	2739.4	26.9
90°-150°	4925.9	48.4
90°-180°	5682.0	55.8
0°-180°	10178.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3085	3085	3085	3085	3085	
5°	3035	3005	3024	3031	3042	282
15°	2567	2557	2626	2698	2744	717
25°	1962	1967	2068	2159	2254	902
35°	1386	1393	1486	1586	1699	862
45°	831	847	903	971	1060	648
55°	478	498	527	547	592	433
65°	240	260	283	247	225	249
75°	120	120	110	75	51	129
85°	34	34	31	20	12	37
90°	0	0	0	0	0	4
95°	45	180	807	279	172	52
105°	184	280	1209	2135	2030	195
115°	343	414	916	1942	2280	337
125°	484	536	875	1452	1736	433
135°	591	641	864	1226	1386	456
145°	697	733	871	1061	1157	436
155°	796	815	892	959	998	368
165°	880	883	903	922	936	247
175°	922	917	913	908	901	87
180°	915	915	915	915	915	

TEST NUMBER: P522007

CATALOG NUMBER: SQ4-WB-125U-125D-92765-1D-UNV-STD-W-4_4500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3085.1	3085.1	3085.1	3085.1	3085.1
2.5°	3092.7	3065.2	3072.1	3071.9	3063.4
5°	3035.0	3004.6	3024.2	3031.2	3041.8
7.5°	2922.4	2899.4	2935.1	2961.6	2983.0
10°	2834.7	2814.8	2860.4	2898.9	2926.7
12.5°	2732.9	2716.2	2772.7	2824.4	2860.7
15°	2566.6	2557.4	2626.2	2697.6	2744.0
17.5°	2388.8	2384.3	2463.2	2546.6	2605.9
20°	2267.5	2266.1	2352.7	2439.6	2508.4
22.5°	2145.1	2148.0	2239.0	2329.4	2407.7
25°	1961.5	1966.8	2068.5	2158.6	2253.9
27.5°	1791.8	1794.2	1899.3	1994.4	2096.1
30°	1675.9	1682.5	1785.5	1884.1	1990.0
32.5°	1560.0	1567.7	1668.6	1770.4	1878.4
35°	1386.2	1392.8	1486.4	1586.4	1698.9
37.5°	1207.0	1216.0	1299.0	1393.6	1504.2
40°	1091.1	1104.3	1177.7	1266.8	1375.4
42.5°	979.5	996.0	1064.0	1148.5	1246.5
45°	831.2	847.1	902.9	971.3	1060.0
47.5°	703.4	721.7	764.6	823.4	899.1
50°	630.8	648.0	687.7	731.3	802.8
52.5°	566.9	584.1	619.5	653.1	713.9
55°	477.9	497.7	526.6	546.6	591.6
57.5°	404.8	423.8	446.7	455.7	483.0
60°	356.0	377.2	398.0	397.0	411.5
62.5°	311.6	329.6	350.3	336.0	336.8
65°	239.6	259.5	282.9	247.2	224.7
67.5°	193.6	197.8	222.0	172.4	145.7
70°	171.9	171.9	178.7	133.5	111.0
72.5°	151.3	151.3	145.1	108.6	85.0
75°	120.5	120.5	109.7	75.3	51.4
77.5°	92.9	91.8	83.9	56.2	37.4
80°	74.5	74.5	67.7	44.3	29.8
82.5°	58.2	58.2	52.5	34.6	22.2
85°	33.8	33.8	31.1	20.1	12.2
87.5°	11.9	11.9	10.8	6.5	5.4
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.9	73.8	171.1	49.8	37.6
95°	45.2	179.6	807.0	279.3	172.2
97.5°	83.1	210.3	1242.8	889.3	609.4
100°	109.6	228.6	1337.4	1354.7	1043.5
102.5°	138.8	248.3	1316.6	1734.0	1462.3
105°	184.4	279.6	1208.7	2135.1	2029.6
107.5°	230.6	316.0	1082.8	2248.1	2342.0
110°	262.6	342.5	1010.5	2204.9	2415.7

TEST NUMBER: P522007

CATALOG NUMBER: SQ4-WB-125U-125D-92765-1D-UNV-STD-W-4_4500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	293.2	369.1	961.8	2102.5	2403.2
115°	342.6	414.0	916.5	1941.7	2280.1
117.5°	386.1	453.1	889.8	1765.8	2124.2
120°	420.9	477.0	887.0	1665.2	2008.8
122.5°	448.7	504.8	880.0	1577.0	1896.1
125°	483.5	536.2	874.8	1451.7	1735.7
127.5°	521.4	570.7	872.0	1376.8	1610.8
130°	540.9	590.2	867.9	1324.7	1528.7
132.5°	561.8	609.7	867.9	1284.0	1471.7
135°	591.3	640.6	864.4	1226.3	1386.1
137.5°	619.1	667.1	864.0	1177.4	1315.5
140°	640.0	689.3	862.6	1137.0	1269.6
142.5°	663.7	704.8	866.8	1104.6	1223.7
145°	697.4	733.1	871.3	1061.3	1156.6
147.5°	726.3	761.0	879.0	1017.6	1099.9
150°	751.3	775.1	881.8	1003.1	1060.9
152.5°	770.8	796.0	884.5	983.5	1037.2
155°	796.5	815.2	892.2	959.2	998.3
157.5°	828.5	839.8	893.9	948.1	976.0
160°	845.2	853.7	900.9	939.7	963.5
162.5°	855.0	864.8	902.3	932.6	951.0
165°	880.0	883.4	902.6	922.1	935.7
167.5°	897.1	894.0	910.6	919.5	924.9
170°	902.6	900.9	907.9	909.7	916.5
172.5°	915.2	909.4	912.0	906.9	912.4
175°	921.8	916.7	913.1	907.7	900.9
177.5°	924.5	916.4	912.0	906.5	907.9
180°	914.8	914.8	914.8	914.8	914.8

(END OF REPORT)