

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P522030

Luminaire Tested: SQ4-WB-150U-075D-92765-1D-UNV-STD-W-4_3000K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P522030
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-WB-150U-075D-92765-1D-UNV-STD-W-4_3000K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9012.7 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 83.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P522030

CATALOG NUMBER: SQ4-WB-150U-075D-92765-1D-UNV-STD-W-4_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P522030

CATALOG NUMBER: SQ4-WB-150U-075D-92765-1D-UNV-STD-W-4_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28				
1	94	90	86	83	84	80	78	75	63	61	60	47	46	45	33	32	32	25				
2	86	79	73	69	77	71	66	62	56	53	50	42	41	39	30	29	28	22				
3	79	70	63	58	70	63	57	53	50	46	43	38	36	34	27	26	24	20				
4	72	62	55	50	65	56	50	45	45	41	37	34	32	29	25	23	22	17				
5	66	56	48	43	59	50	44	39	40	36	32	31	28	26	22	21	19	16				
6	61	50	43	37	55	46	39	34	37	32	29	28	25	23	21	19	17	14				
7	57	45	38	33	51	41	35	30	33	29	25	26	23	20	19	17	16	13				
8	53	41	34	29	47	38	31	27	31	26	23	24	21	18	18	16	14	12				
9	49	38	31	26	44	34	28	24	28	24	20	22	19	17	16	14	13	11				
10	46	35	28	23	41	32	26	22	26	21	18	20	17	15	15	13	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16141	16141	16141
5°	15940	15882	15975
10°	15060	15196	15549
15°	13902	14224	14862
20°	12624	13100	13967
25°	11323	11941	13011
30°	10124	10787	12021
35°	8854	9494	10851
40°	7452	8044	9393
45°	6149	6680	7843
50°	5134	5598	6534
55°	4359	4803	5397
60°	3726	4165	4307
65°	2967	3502	2781
70°	2630	2733	1697
75°	2435	2217	1041
80°	2242	2040	898
85°	2032	1874	730

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7843 cd/sqm

TEST NUMBER: P522030

CATALOG NUMBER: SQ4-WB-150U-075D-92765-1D-UNV-STD-W-4_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.5	1.8
10°-20°	417.4	4.6
20°-30°	540.6	6.0
30°-40°	529.4	5.9
40°-50°	405.2	4.5
50°-60°	270.0	3.0
60°-70°	147.4	1.6
70°-80°	61.4	0.7
80°-90°	17.4	0.2
90°-100°	474.1	5.3
100°-110°	1349.1	15.0
110°-120°	1292.6	14.3
120°-130°	1023.0	11.4
130°-140°	821.1	9.1
140°-150°	642.8	7.1
150°-160°	470.4	5.2
160°-170°	291.4	3.2
170°-180°	98.9	1.1
0°-30°	1118.5	12.4
0°-40°	1647.9	18.3
0°-60°	2323.1	25.8
0°-90°	2549.3	28.3
90°-120°	3115.8	34.6
90°-150°	5602.8	62.2
90°-180°	6463.0	71.7
0°-180°	9012.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1750	1750	1750	1750	1750	
5°	1721	1704	1715	1719	1725	160
15°	1456	1450	1489	1530	1556	406
25°	1112	1115	1173	1224	1278	512
35°	786	790	843	900	963	489
45°	471	480	512	551	601	368
55°	271	282	299	310	336	246
65°	136	147	160	140	127	141
75°	68	68	62	43	29	73
85°	19	19	18	11	7	21
90°	0	0	0	0	0	3
95°	51	204	918	318	196	59
105°	210	318	1375	2428	2308	222
115°	390	471	1042	2208	2593	384
125°	550	610	995	1651	1974	492
135°	673	729	983	1395	1577	519
145°	793	834	991	1207	1316	496
155°	906	927	1015	1091	1136	419
165°	1001	1005	1027	1049	1064	281
175°	1048	1043	1038	1032	1025	99
180°	1040	1040	1040	1040	1040	

TEST NUMBER: P522030

CATALOG NUMBER: SQ4-WB-150U-075D-92765-1D-UNV-STD-W-4_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1749.5	1749.5	1749.5	1749.5	1749.5
2.5°	1753.8	1738.2	1742.1	1742.0	1737.2
5°	1721.1	1703.8	1714.9	1718.9	1724.9
7.5°	1657.2	1644.1	1664.4	1679.4	1691.6
10°	1607.5	1596.2	1622.0	1643.9	1659.7
12.5°	1549.7	1540.3	1572.3	1601.6	1622.2
15°	1455.5	1450.2	1489.2	1529.8	1556.0
17.5°	1354.6	1352.0	1396.8	1444.1	1477.7
20°	1285.8	1285.1	1334.2	1383.4	1422.5
22.5°	1216.4	1218.1	1269.7	1320.9	1365.3
25°	1112.3	1115.3	1173.0	1224.1	1278.1
27.5°	1016.1	1017.4	1077.0	1131.0	1188.6
30°	950.3	954.1	1012.5	1068.4	1128.4
32.5°	884.6	889.0	946.2	1003.9	1065.2
35°	786.1	789.8	842.9	899.6	963.4
37.5°	684.4	689.5	736.6	790.3	853.0
40°	618.7	626.2	667.9	718.4	779.9
42.5°	555.5	564.8	603.4	651.3	706.9
45°	471.3	480.3	512.0	550.8	601.1
47.5°	398.9	409.2	433.6	466.9	509.9
50°	357.7	367.5	390.0	414.7	455.2
52.5°	321.5	331.2	351.3	370.3	404.9
55°	271.0	282.2	298.6	309.9	335.5
57.5°	229.5	240.3	253.3	258.4	273.9
60°	201.9	213.9	225.7	225.1	233.4
62.5°	176.7	186.9	198.7	190.5	191.0
65°	135.9	147.1	160.4	140.2	127.4
67.5°	109.8	112.2	125.9	97.8	82.6
70°	97.5	97.5	101.3	75.7	62.9
72.5°	85.8	85.8	82.3	61.6	48.2
75°	68.3	68.3	62.2	42.7	29.2
77.5°	52.7	52.1	47.6	31.8	21.2
80°	42.2	42.2	38.4	25.1	16.9
82.5°	33.0	33.0	29.8	19.6	12.6
85°	19.2	19.2	17.7	11.4	6.9
87.5°	6.8	6.8	6.1	3.7	3.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	15.8	83.9	194.7	56.7	42.7
95°	51.4	204.2	917.9	317.7	195.8
97.5°	94.6	239.2	1413.6	1011.5	693.2
100°	124.6	260.0	1521.2	1540.9	1186.9
102.5°	157.9	282.4	1497.5	1972.3	1663.2
105°	209.7	318.0	1374.8	2428.4	2308.5
107.5°	262.3	359.4	1231.6	2557.0	2663.8
110°	298.7	389.6	1149.3	2507.8	2747.7

TEST NUMBER: P522030

CATALOG NUMBER: SQ4-WB-150U-075D-92765-1D-UNV-STD-W-4_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	333.5	419.8	1093.9	2391.5	2733.4
115°	389.7	470.9	1042.5	2208.5	2593.4
117.5°	439.2	515.4	1012.0	2008.4	2416.1
120°	478.7	542.5	1008.9	1894.1	2284.8
122.5°	510.4	574.2	1001.0	1793.7	2156.6
125°	549.9	609.9	995.0	1651.2	1974.2
127.5°	593.1	649.1	991.9	1566.0	1832.2
130°	615.2	671.3	987.1	1506.7	1738.8
132.5°	638.9	693.5	987.1	1460.4	1673.9
135°	672.6	728.7	983.2	1394.8	1576.6
137.5°	704.2	758.8	982.8	1339.2	1496.3
140°	728.0	784.1	981.2	1293.2	1444.1
142.5°	754.9	801.7	985.9	1256.4	1391.8
145°	793.2	833.9	991.1	1207.2	1315.5
147.5°	826.1	865.5	999.8	1157.4	1251.0
150°	854.6	881.6	1002.9	1140.9	1206.7
152.5°	876.7	905.4	1006.1	1118.7	1179.8
155°	906.0	927.3	1014.8	1091.0	1135.5
157.5°	942.4	955.2	1016.8	1078.4	1110.1
160°	961.4	971.1	1024.7	1068.8	1095.9
162.5°	972.5	983.7	1026.3	1060.8	1081.7
165°	1001.0	1004.8	1026.7	1048.8	1064.3
167.5°	1020.3	1016.9	1035.8	1045.8	1052.0
170°	1026.7	1024.7	1032.6	1034.8	1042.5
172.5°	1040.9	1034.3	1037.4	1031.6	1037.7
175°	1048.4	1042.6	1038.5	1032.4	1024.7
177.5°	1051.6	1042.3	1037.4	1031.1	1032.6
180°	1040.5	1040.5	1040.5	1040.5	1040.5

(END OF REPORT)