

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P522034

Luminaire Tested: SQ4-WB-150U-075D-92765-1D-UNV-STD-W-4_5000K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P522034
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-WB-150U-075D-92765-1D-UNV-STD-W-4_5000K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9655.0 lumens
Efficiency: N/A
Efficacy: 116.5 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P522034

CATALOG NUMBER: SQ4-WB-150U-075D-92765-1D-UNV-STD-W-4_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P522034

CATALOG NUMBER: SQ4-WB-150U-075D-92765-1D-UNV-STD-W-4_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28				
1	94	90	86	83	84	80	78	75	63	61	60	47	46	45	33	32	32	25				
2	86	79	73	69	77	71	66	62	56	53	50	42	41	39	30	29	28	22				
3	79	70	63	58	70	63	57	53	50	46	43	38	36	34	27	26	24	20				
4	72	62	55	50	65	56	50	45	45	41	37	34	32	29	25	23	22	17				
5	66	56	48	43	59	50	44	39	40	36	32	31	28	26	22	21	19	16				
6	61	50	43	37	55	46	39	34	37	32	29	28	25	23	21	19	17	14				
7	57	45	38	33	51	41	35	30	33	29	25	26	23	20	19	17	16	13				
8	53	41	34	29	47	38	31	27	31	26	23	24	21	18	18	16	14	12				
9	49	38	31	26	44	34	28	24	28	24	20	22	19	17	16	14	13	11				
10	46	35	28	23	41	32	26	22	26	21	18	20	17	15	15	13	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17292	17292	17292
5°	17075	17015	17113
10°	16133	16279	16656
15°	14893	15239	15922
20°	13525	14033	14961
25°	12130	12792	13938
30°	10846	11556	12879
35°	9485	10171	11625
40°	7983	8617	10063
45°	6588	7157	8401
50°	5500	5997	7000
55°	4670	5146	5781
60°	3991	4462	4613
65°	3179	3753	2980
70°	2816	2930	1818
75°	2609	2374	1112
80°	2402	2184	962
85°	2181	2001	783

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 8401 cd/sqm

TEST NUMBER: P522034

CATALOG NUMBER: SQ4-WB-150U-075D-92765-1D-UNV-STD-W-4_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.9	1.8
10°-20°	447.1	4.6
20°-30°	579.2	6.0
30°-40°	567.1	5.9
40°-50°	434.1	4.5
50°-60°	289.3	3.0
60°-70°	157.9	1.6
70°-80°	65.8	0.7
80°-90°	18.6	0.2
90°-100°	507.9	5.3
100°-110°	1445.2	15.0
110°-120°	1384.7	14.3
120°-130°	1095.9	11.4
130°-140°	879.7	9.1
140°-150°	688.7	7.1
150°-160°	503.9	5.2
160°-170°	312.1	3.2
170°-180°	105.9	1.1
0°-30°	1198.2	12.4
0°-40°	1765.3	18.3
0°-60°	2488.8	25.8
0°-90°	2731.0	28.3
90°-120°	3337.9	34.6
90°-150°	6002.1	62.2
90°-180°	6924.0	71.7
0°-180°	9655.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1874	1874	1874	1874	1874	
5°	1844	1825	1837	1841	1848	172
15°	1559	1554	1595	1639	1667	435
25°	1192	1195	1257	1311	1369	548
35°	842	846	903	964	1032	524
45°	505	515	548	590	644	394
55°	290	302	320	332	359	263
65°	146	158	172	150	136	151
75°	73	73	67	46	31	78
85°	21	21	19	12	7	22
90°	0	0	0	0	0	3
95°	55	219	983	340	210	63
105°	225	341	1473	2602	2473	238
115°	418	504	1117	2366	2778	411
125°	589	653	1066	1769	2115	527
135°	720	781	1053	1494	1689	556
145°	850	893	1062	1293	1409	531
155°	971	993	1087	1169	1216	449
165°	1072	1076	1100	1124	1140	302
175°	1123	1117	1113	1106	1098	106
180°	1115	1115	1115	1115	1115	

TEST NUMBER: P522034

CATALOG NUMBER: SQ4-WB-150U-075D-92765-1D-UNV-STD-W-4_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1874.2	1874.2	1874.2	1874.2	1874.2
2.5°	1878.8	1862.0	1866.3	1866.1	1861.0
5°	1843.7	1825.2	1837.2	1841.4	1847.8
7.5°	1775.3	1761.3	1783.0	1799.1	1812.2
10°	1722.0	1710.0	1737.6	1761.1	1777.9
12.5°	1660.2	1650.1	1684.4	1715.8	1737.8
15°	1559.2	1553.6	1595.4	1638.8	1666.9
17.5°	1451.1	1448.4	1496.4	1547.0	1583.0
20°	1377.5	1376.7	1429.3	1482.0	1523.8
22.5°	1303.1	1304.9	1360.2	1415.0	1462.7
25°	1191.6	1194.8	1256.6	1311.3	1369.2
27.5°	1088.5	1089.9	1153.8	1211.6	1273.3
30°	1018.1	1022.1	1084.7	1144.5	1208.9
32.5°	947.7	952.4	1013.6	1075.5	1141.1
35°	842.1	846.1	903.0	963.7	1032.1
37.5°	733.2	738.7	789.1	846.6	913.8
40°	662.8	670.9	715.5	769.6	835.5
42.5°	595.1	605.0	646.4	697.7	757.2
45°	504.9	514.6	548.5	590.0	643.9
47.5°	427.3	438.4	464.5	500.2	546.2
50°	383.2	393.7	417.8	444.2	487.7
52.5°	344.4	354.9	376.3	396.7	433.7
55°	290.3	302.4	319.9	332.0	359.4
57.5°	245.9	257.5	271.4	276.9	293.4
60°	216.3	229.1	241.8	241.2	250.0
62.5°	189.3	200.2	212.8	204.1	204.6
65°	145.6	157.6	171.9	150.2	136.5
67.5°	117.6	120.2	134.9	104.7	88.5
70°	104.4	104.4	108.6	81.1	67.4
72.5°	91.9	91.9	88.2	66.0	51.6
75°	73.2	73.2	66.6	45.7	31.2
77.5°	56.4	55.8	51.0	34.1	22.7
80°	45.2	45.2	41.1	26.9	18.1
82.5°	35.4	35.4	31.9	21.0	13.5
85°	20.6	20.6	18.9	12.2	7.4
87.5°	7.2	7.2	6.6	3.9	3.3
90°	0.0	0.0	0.0	0.0	0.0
92.5°	17.0	89.9	208.5	60.7	45.8
95°	55.1	218.8	983.3	340.3	209.8
97.5°	101.3	256.3	1514.4	1083.6	742.6
100°	133.5	278.6	1629.6	1650.7	1271.5
102.5°	169.1	302.6	1604.2	2112.9	1781.8
105°	224.6	340.7	1472.8	2601.5	2473.1
107.5°	281.0	385.0	1319.4	2739.3	2853.7
110°	320.0	417.4	1231.2	2686.6	2943.5

TEST NUMBER: P522034

CATALOG NUMBER: SQ4-WB-150U-075D-92765-1D-UNV-STD-W-4_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	357.3	449.7	1171.9	2561.9	2928.3
115°	417.5	504.5	1116.8	2365.9	2778.2
117.5°	470.5	552.1	1084.2	2151.6	2588.3
120°	512.8	581.2	1080.8	2029.1	2447.6
122.5°	546.7	615.1	1072.3	1921.6	2310.3
125°	589.1	653.4	1065.9	1768.9	2114.9
127.5°	635.3	695.4	1062.5	1677.6	1962.8
130°	659.1	719.1	1057.5	1614.1	1862.7
132.5°	684.5	742.9	1057.5	1564.5	1793.2
135°	720.5	780.6	1053.2	1494.2	1689.0
137.5°	754.4	812.9	1052.8	1434.7	1602.9
140°	779.9	839.9	1051.1	1385.4	1547.0
142.5°	808.7	858.8	1056.2	1346.0	1491.0
145°	849.8	893.3	1061.7	1293.2	1409.2
147.5°	885.0	927.2	1071.0	1239.9	1340.2
150°	915.5	944.5	1074.4	1222.2	1292.7
152.5°	939.2	969.9	1077.8	1198.4	1263.9
155°	970.6	993.4	1087.1	1168.7	1216.4
157.5°	1009.6	1023.2	1089.2	1155.3	1189.3
160°	1029.9	1040.3	1097.7	1145.0	1174.0
162.5°	1041.8	1053.8	1099.4	1136.4	1158.8
165°	1072.3	1076.4	1099.8	1123.5	1140.1
167.5°	1093.1	1089.3	1109.6	1120.3	1127.0
170°	1099.8	1097.8	1106.2	1108.5	1116.8
172.5°	1115.1	1108.1	1111.3	1105.1	1111.7
175°	1123.2	1116.9	1112.6	1106.0	1097.7
177.5°	1126.5	1116.6	1111.3	1104.5	1106.2
180°	1114.7	1114.7	1114.7	1114.7	1114.7

(END OF REPORT)