

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P522055

Luminaire Tested: **SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P522055
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4 (2700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10488.9 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 106.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P522055

CATALOG NUMBER: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4 (2700K)

Luminous Intensity Polar Plot





TEST NUMBER: P522055

CATALOG NUMBER: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4 (2700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40
1	96	92	89	86	88	84	81	79	69	67	65	55	54	53	43	42	41	35
2	88	82	76	72	80	75	70	66	62	58	56	50	48	46	39	37	36	31
3	81	73	66	61	74	67	61	56	55	51	48	45	42	40	35	33	32	27
4	75	65	58	52	68	60	53	49	50	45	42	41	37	35	32	30	28	24
5	69	58	51	45	63	54	47	42	45	40	37	37	34	31	29	27	25	22
6	64	53	45	40	58	49	42	37	41	36	32	34	30	28	27	25	23	20
7	59	48	40	35	54	44	38	33	37	32	29	31	27	25	25	23	21	18
8	55	44	36	32	50	40	34	30	34	29	26	29	25	22	23	21	19	16
9	52	40	33	28	47	37	31	27	32	27	24	26	23	20	22	19	17	15
10	48	37	30	26	44	34	28	24	29	25	21	25	21	19	20	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26319	26319	26319
5°	25990	25898	26048
10°	24555	24778	25352
15°	22668	23194	24234
20°	20585	21359	22773
25°	18463	19470	21216
30°	16509	17589	19602
35°	14436	15480	17693
40°	12151	13116	15316
45°	10027	10894	12788
50°	8372	9127	10653
55°	7107	7832	8799
60°	6075	6790	7021
65°	4836	5711	4536
70°	4289	4456	2768
75°	3971	3615	1697
80°	3655	3326	1461
85°	3313	3049	1196



TEST NUMBER: P522055

CATALOG NUMBER: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4 (2700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.7	2.5
10°-20°	680.6	6.5
20°-30°	881.5	8.4
30°-40°	863.2	8.2
40°-50°	660.8	6.3
50°-60°	440.3	4.2
60°-70°	240.3	2.3
70°-80°	100.1	1.0
80°-90°	28.3	0.3
90°-100°	464.5	4.4
100°-110°	1321.7	12.6
110°-120°	1266.3	12.1
120°-130°	1002.2	9.6
130°-140°	804.5	7.7
140°-150°	629.8	6.0
150°-160°	460.8	4.4
160°-170°	285.4	2.7
170°-180°	96.9	0.9
0°-30°	1823.7	17.4
0°-40°	2687.0	25.6
0°-60°	3788.0	36.1
0°-90°	4156.8	39.6
90°-120°	3052.5	29.1
90°-150°	5489.0	52.3
90°-180°	6332.0	60.4
0°-180°	10488.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2853	2853	2853	2853	2853	
5°	2806	2778	2796	2803	2812	261
15°	2373	2365	2428	2494	2537	663
25°	1814	1819	1913	1996	2084	834
35°	1282	1288	1374	1467	1571	797
45°	768	783	835	898	980	599
55°	442	460	487	505	547	401
65°	222	240	262	229	208	230
75°	111	111	101	70	48	119
85°	31	31	29	19	11	34
90°	0	0	0	0	0	4
95°	50	200	899	311	192	58
105°	205	312	1347	2379	2262	217
115°	382	461	1021	2164	2541	376
125°	539	598	975	1618	1934	482
135°	659	714	963	1366	1545	508
145°	777	817	971	1183	1289	485
155°	888	908	994	1069	1112	410
165°	981	984	1006	1028	1043	276
175°	1027	1022	1018	1012	1004	97
180°	1019	1019	1019	1019	1019	

TEST NUMBER: P522055

CATALOG NUMBER: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2852.6	2852.6	2852.6	2852.6	2852.6
2.5°	2859.6	2834.1	2840.6	2840.4	2832.6
5°	2806.3	2778.1	2796.3	2802.7	2812.5
7.5°	2702.1	2680.8	2713.9	2738.4	2758.2
10°	2621.0	2602.7	2644.8	2680.4	2706.1
12.5°	2526.9	2511.5	2563.7	2611.5	2645.1
15°	2373.2	2364.6	2428.3	2494.3	2537.2
17.5°	2208.7	2204.6	2277.6	2354.7	2409.5
20°	2096.6	2095.4	2175.4	2255.7	2319.4
22.5°	1983.4	1986.1	2070.3	2153.8	2226.2
25°	1813.7	1818.6	1912.6	1995.9	2084.1
27.5°	1656.7	1658.9	1756.1	1844.1	1938.1
30°	1549.6	1555.7	1651.0	1742.1	1840.0
32.5°	1442.4	1449.5	1542.8	1637.0	1736.8
35°	1281.7	1287.8	1374.4	1466.8	1570.9
37.5°	1116.0	1124.3	1201.1	1288.6	1390.9
40°	1008.9	1021.1	1089.0	1171.4	1271.7
42.5°	905.7	920.9	983.8	1062.0	1152.6
45°	768.5	783.2	834.9	898.1	980.1
47.5°	650.4	667.3	707.0	761.4	831.4
50°	583.3	599.2	635.9	676.2	742.2
52.5°	524.2	540.1	572.8	603.8	660.1
55°	441.8	460.2	486.9	505.4	547.0
57.5°	374.3	391.9	413.1	421.4	446.6
60°	329.2	348.8	368.0	367.1	380.5
62.5°	288.1	304.8	323.9	310.7	311.4
65°	221.5	239.9	261.6	228.6	207.8
67.5°	179.0	182.9	205.3	159.4	134.7
70°	159.0	159.0	165.2	123.4	102.6
72.5°	139.9	139.9	134.2	100.4	78.6
75°	111.4	111.4	101.4	69.6	47.6
77.5°	85.9	84.9	77.6	51.9	34.5
80°	68.8	68.8	62.6	41.0	27.5
82.5°	53.8	53.8	48.6	32.0	20.5
85°	31.3	31.3	28.8	18.6	11.3
87.5°	11.0	11.0	10.0	6.0	5.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	15.5	82.2	190.7	55.5	41.9
95°	50.4	200.1	899.2	311.2	191.9
97.5°	92.6	234.4	1384.9	991.0	679.1
100°	122.1	254.7	1490.3	1509.6	1162.8
102.5°	154.7	276.7	1467.1	1932.3	1629.5
105°	205.4	311.5	1346.9	2379.1	2261.7
107.5°	257.0	352.1	1206.6	2505.1	2609.7
110°	292.6	381.7	1126.0	2456.9	2691.9



TEST NUMBER: P522055

CATALOG NUMBER: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	326.7	411.3	1071.7	2342.9	2677.9
115°	381.8	461.4	1021.3	2163.6	2540.7
117.5°	430.2	504.9	991.5	1967.6	2367.1
120°	469.0	531.5	988.4	1855.6	2238.4
122.5°	500.0	562.5	980.6	1757.3	2112.8
125°	538.8	597.5	974.8	1617.7	1934.1
127.5°	581.0	636.0	971.7	1534.2	1795.0
130°	602.7	657.7	967.1	1476.1	1703.5
132.5°	626.0	679.4	967.1	1430.7	1639.9
135°	658.9	713.9	963.2	1366.5	1544.6
137.5°	689.9	743.4	962.8	1312.0	1465.9
140°	713.2	768.1	961.3	1266.9	1414.7
142.5°	739.5	785.4	965.9	1230.9	1363.6
145°	777.1	816.9	970.9	1182.7	1288.8
147.5°	809.3	848.0	979.5	1133.9	1225.6
150°	837.2	863.7	982.6	1117.8	1182.2
152.5°	858.9	887.0	985.7	1095.9	1155.8
155°	887.6	908.5	994.2	1068.8	1112.4
157.5°	923.3	935.8	996.1	1056.5	1087.6
160°	941.9	951.3	1003.9	1047.1	1073.7
162.5°	952.7	963.7	1005.4	1039.2	1059.7
165°	980.6	984.4	1005.8	1027.5	1042.6
167.5°	999.6	996.2	1014.7	1024.6	1030.6
170°	1005.8	1003.9	1011.6	1013.7	1021.3
172.5°	1019.8	1013.3	1016.3	1010.6	1016.7
175°	1027.1	1021.5	1017.5	1011.5	1003.9
177.5°	1030.2	1021.1	1016.3	1010.1	1011.6
180°	1019.4	1019.4	1019.4	1019.4	1019.4

(END OF REPORT)